

# HUBER+SUHNER® DATA SHEET

## Within Series Adaptor: 32\_MMBX-50-0-5/111\_N

Rev.: G



### Description

Adaptor plug/plug  
MMBX plug (male) / MMBX plug (male)  
Slide - snap interface  
Interface standard  
Series MMBX - SUHNER-MMBX



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 12.4 GHz

#### Mechanical Data

Number of matings 100  
Weight 0.0005 kg

#### Environmental Data

Operating Temperature -55 °C to 155 °C  
2002/95/EC (RoHS) compliant

#### Material Data

##### Piece Parts

##### Interface - MMBX plug (male)

|                |                        |
|----------------|------------------------|
| Centre contact | Copper Beryllium Alloy |
| Outer contact  | Bronze                 |
| Body           | Bronze                 |
| Insulator      | PFA / PTFE             |

##### Surface Plating

SUCOPRO Plating  
SUCOPRO Plating  
SUCOPRO Plating

##### Interface - MMBX plug (male)

|                |                        |
|----------------|------------------------|
| Centre contact | Copper Beryllium Alloy |
| Outer contact  | Bronze                 |
| Body           | Bronze                 |
| Insulator      | PFA / PTFE             |

SUCOPRO Plating  
SUCOPRO Plating  
SUCOPRO Plating

#### Related Documents

Outline drawing DOU-00013890

#### Ordering Information

Tray package 32\_MMBX-50-0-5/111\_NY  
Single package 32\_MMBX-50-0-5/111\_NE

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

#### WAIVER

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



**HUBER+SUHNER AG**  
RF Technology  
9100 Herisau, Switzerland  
Phone +41 (0)71 353 41 11  
Fax +41 (0)71 353 45 90  
www.hubersuhner.com

**HUBER+SUHNER – Excellence in Connectivity Solutions**