







RECOMMEND P.C.B. LAYOUT



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: 0.0=±0.4
0.00=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 50mA @12V DC
5. TRAVEL: 0.25±0.1mm
6. OPERATING FORCE: 180±50gf
7. CONTACT RESISTANCE: 100m ohm max.
8. MECHANICAL/ELECTRICAL LIFE: 40,000 CYCLES
9. PACKAGE: BULK 1,000 PER BAG
10. 2002/95/EC (ROHS) COMPLIANT

CIRCUIT: SPST
CONTACT CONFIGURATION



UPDATED NOTES				TITLE			
B	16617	RELEASED FOR PRODUCTION	11/7/06	TN	TL1107AF180BQ		
A	10585	DESCRIPTION	3/28/00	MM	P010381		
REV.	ECN No.	DATE	CHKD	SCALE	DATE	DR	REV
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				5:1	11/7/2006	TN	B