

4


3

2

1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		F1	REVISED PER ECO-06-13762	6/19/06	SS	SRY

- 1 STAINLESS STEEL.
- 2 BRASS.
- 3 1.27um [.000050] MIN TIN-LEAD
OVER 1.27um [.000050] MIN NICKEL.
4. WIRE RANGE: 20-24 AWG.
INSULATION RANGE:
1.52-3.05 [.060-.120] DIA.
- 5 0.38um [.000015] MIN GOLD IN
LOCALIZED GOLD PLATE AREA, OVER
1.27um [.000050] MIN NICKEL.
- 6 0.76um [.000030] MIN GOLD IN
LOCALIZED GOLD PLATE AREA, OVER
1.27um [.000050] MIN NICKEL.
- 7 1.27um [.000050] MIN TIN OVER
1.27um [.000050] MIN NICKEL.



	STRIP	7	213605-7
OBSOLETE	LOOSE PIECE	6	213605-6
OBSOLETE	STRIP	6	213605-5
OBSOLETE	LOOSE PIECE	5	213605-4
OBSOLETE	STRIP	5	213605-3
OBSOLETE	LOOSE PIECE	3	213605-2
	STRIP	3	213605-1
	DESCRIPTION	PIN FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE 05/07/90		tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608				
		CHK R.STONE 5-17-90						
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	—	NAME PIN ASSEMBLY, 5015 SERIES, 20-24 AWG, SPECIAL TYPE III+ —				
		PRODUCT SPEC	—					
	0 PLC ± — 1 PLC ± — 2 PLC ± 0.13 [.005] 3 PLC ± — 4 PLC ± — ANGLES ± —	APPLICATION SPEC	—					
		WEIGHT	—					
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
SPRING:		PIN: SEE TABLE		A3	00779	C-213605	—	
PIN:		CUSTOMER DRAWING				SCALE	SHEET	REV
				4:1	1 OF 1	F1		