




TYCO ELECTRONICS P/N _____ YEAR _____ WEEK _____
 DATE CODE (e.g. 0106)
 XXXXX - X
 XXXXX

7.25

2.00


7X 2.50


3.56

2.54


6.1 TYP

SECTION Z-Z




THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION		DWN 20JUL2007 R. GRZYBOWSKI CHK 20JUL2007 P. DAMATO APVD 20JUL2007 S. FLICKINGER		Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±.5 [.02] 2 PLC ±.25 [.010] 3 PLC ±. 4 PLC ±. ANGLES ±1 FINISH		NAME SOCKET CONNECTOR, RIGHT ANGLE SOLDER TAILS FLATPAQ	
MATERIAL -		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		SIZE A2 CAGE CODE 00779 DRAWING NO C-6646744 RESTRICTED TO -	
CUSTOMER DRAWING		SCALE 3:1		SHEET 1 OF 3 REV A	

LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-



6. SOLDER PIN DETAIL
SCALE 10 : 1



7. SOLDER TERMINATION AREA
SCALE 40:1
RECOMMENDED PRINTED CIRCUIT HOLE
FINISHED HOLE: Ø1.02 [.040]±.08 [.003]
DRILLED HOLE: Ø1.15 [.0453] ±.013 [.0005]
COPPER PLATE: .025 [.0010] MIN (PER SURFACE)
TIN PLATE: .008 [.0003] MIN. (PER SURFACE)