





CKT SIZE	DIM. "A"		DIM. "B" ^(+0.20) _{-0.008}		CKT SIZE	DIM. "A"		DIM. "B" ^(+0.20) _{-0.008}	
2X 1			(2.54)	.100	2X21	(50.80)	2.000	(53.34)	2.100
2X 2	(2.54)	.100	(5.08)	.200	2X22	(53.34)	2.100	(55.88)	2.200
2X 3	(5.08)	.200	(7.62)	.300	2X23	(55.88)	2.200	(58.42)	2.300
2X 4	(7.62)	.300	(10.16)	.400	2X24	(58.42)	2.300	(60.96)	2.400
2X 5	(10.16)	.400	(12.70)	.500	2X25	(60.96)	2.400	(63.50)	2.500
2X 6	(12.70)	.500	(15.24)	.600	2X26	(63.50)	2.500	(66.04)	2.600
2X 7	(15.24)	.600	(17.78)	.700	2X27	(66.04)	2.600	(68.58)	2.700
2X 8	(17.78)	.700	(20.32)	.800	2X28	(68.58)	2.700	(71.12)	2.800
2X 9	(20.32)	.800	(22.86)	.900	2X29	(71.12)	2.800	(73.66)	2.900
2X10	(22.86)	.900	(25.40)	1.000	2X30	(73.66)	2.900	(76.20)	3.000
2X11	(25.40)	1.000	(27.94)	1.100	2X31	(76.20)	3.000	(78.74)	3.100
2X12	(27.94)	1.100	(30.48)	1.200	2X32	(78.74)	3.100	(81.28)	3.200
2X13	(30.48)	1.200	(33.02)	1.300	2X33	(81.28)	3.200	(83.82)	3.300
2X14	(33.02)	1.300	(35.56)	1.400	2X34	(83.82)	3.300	(86.36)	3.400
2X15	(35.56)	1.400	(38.10)	1.500	2X35	(86.36)	3.400	(88.90)	3.500
2X16	(38.10)	1.500	(40.64)	1.600	2X36	(88.90)	3.500	(91.44)	3.600
2X17	(40.64)	1.600	(43.18)	1.700	2X37	(91.44)	3.600	(93.98)	3.700
2X18	(43.18)	1.700	(45.72)	1.800	2X38	(93.98)	3.700	(96.52)	3.800
2X19	(45.72)	1.800	(48.26)	1.900	2X39	(96.52)	3.800	(99.06)	3.900
2X20	(48.26)	1.900	(50.80)	2.000	2X40	(99.06)	3.900	(101.60)	4.000



- NOTES
- PLEASE REFER TO SHT 2 FOR PLATING DETAILS.
 - PLEASE REFER TO SHT 3-8 FOR DIMENSIONS C & D.
 - RECOMMENDED PCB THICKNESS 1.60MM
 - PRODUCT SPECIFICATION: PS-99020-0001

CHANGE DOC. NO EC NO: S2012-0490 DRWN:ATSE CHKD:SKANG APPR:MLONG REV O	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				DRAWN BY DB		DATE 1987/07/16		TITLE C GRID III DUAL ROW STRAIGHT PIN HEADER		
				CHECKED BY DB		DATE 1987/07/16		MOLEX INCORPORATED		
				APPROVED BY MLONG		DATE 2012/02/24		DOCUMENT NO. SD-90131-001		
		ANGULAR ± 3 °		MATERIAL NO.		SEE TABLE		SHEET NO. 1 OF 8		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				



PLATING OPTIONS	PLATING DESCRIPTION
A	3.00µm MIN TIN OVER 1.27MIN NICKEL OVERALL
B	0.38µm MIN GOLD IN SELECTED AREA AND 3.00µm MIN TIN IN SELECTED AREA AND 1.30µm MIN NICKEL OVERALL
C	0.76µm MIN GOLD IN SELECTED AREA AND 3.00µm MIN TIN IN SELECTED AREA AND 1.30µm MIN NICKEL OVERALL
D	0.05-0.10µm GOLD FLASH IN SELECTED AREA AND 3.00µm MIN TIN IN SELECTED AREA AND 1.30µm MIN NICKEL OVERALL
E	0.38µm MIN GOLD IN SELECTED AREA (2 SIDES) AND 3.00µm MIN TIN IN SELECTED AREA AND 1.30µm MIN NICKEL OVERALL
F	0.76µm MIN GOLD IN SELECTED AREA (2 SIDES) AND 3.00µm MIN TIN IN SELECTED AREA AND 1.30µm MIN NICKEL OVERALL
G	0.05-0.10µm GOLD FLASH IN SELECTED AREA (2 SIDES) AND 3.00µm MIN TIN IN SELECTED AREA AND 1.30µm MIN NICKEL OVERALL

CHANGE DOC. NO EC NO: S2012-0490 DRAWN:ATSEE 2011/12/21 CHKD:SKANG 2011/12/28 APPR:MLONG 2012/02/24 O	DESCRIPTION REV	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	C GRID III DUAL ROW STRAIGHT PIN HEADER		
					DRAWN BY DB	DATE 1987/07/16	TITLE					
					CHECKED BY DB	DATE 1987/07/16						
					APPROVED BY MLONG	DATE 2012/02/24						MOLEX INCORPORATED
			ANGULAR ± 3 °		MATERIAL NO.	DOCUMENT NO.	SHEET NO. 2 OF 8					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE			SD-90131-001				

tb_frame_A3_P_AM_T
Rev. F 2009/06/18

tb_frame_A3_P_AM_T
Rev. F 2009/06/18


	10	9	8	7	6	5	4	3	2	1			
F		CIRCUIT SIZE	PLATING TYPE B PART NO.	PLATING TYPE C PART NO.	PLATING TYPE D PART NO.	PLATING TYPE G PART NO.		CIRCUIT SIZE	PLATING TYPE B PART NO.	PLATING TYPE C PART NO.	PLATING TYPE D PART NO.	PLATING TYPE G PART NO.	F
		2 X 1	90131-0281	90131-0441	90131-0601	90131-1081		2 X 1	90131-0201	90131-0361	90131-0521	90131-1001	
		2 X 2	▲ -0282	▲ -0442	▲ -0602	▲ -1082		2 X 2	▲ -0202	▲ -0362	▲ -0522	▲ -1002	
		2 X 3	-0283	-0443	-0603	-1083		2 X 3	-0203	-0363	-0523	-1003	
		2 X 4	-0284	-0444	-0604	-1084		2 X 4	-0204	-0364	-0524	-1004	
		2 X 5	-0285	-0445	-0605	-1085		2 X 5	-0205	-0365	-0525	-1005	
		2 X 6	-0286	-0446	-0606	-1086		2 X 6	-0206	-0366	-0526	-1006	
		2 X 7	-0287	-0447	-0607	-1087		2 X 7	-0207	-0367	-0527	-1007	
		2 X 8	-0288	-0448	-0608	-1088		2 X 8	-0208	-0368	-0528	-1008	
		2 X 9	-0289	-0449	-0609	-1089		2 X 9	-0209	-0369	-0529	-1009	
E		2 X 10	-0290	-0450	-0610	-1090		2 X 10	-0210	-0370	-0530	-1010	
		2 X 11	-0291	-0451	-0611	-1091		2 X 11	-0211	-0371	-0531	-1011	
		2 X 12	-0292	-0452	-0612	-1092		2 X 12	-0212	-0372	-0532	-1012	
		2 X 13	-0293	-0453	-0613	-1093		2 X 13	-0213	-0373	-0533	-1013	
		2 X 14	-0294	-0454	-0614	-1094		2 X 14	-0214	-0374	-0534	-1014	
		2 X 15	-0295	-0455	-0615	-1095		2 X 15	-0215	-0375	-0535	-1015	
		2 X 16	-0296	-0456	-0616	-1096		2 X 16	-0216	-0376	-0536	-1016	
		2 X 17	-0297	-0457	-0617	-1097		2 X 17	-0217	-0377	-0537	-1017	
		2 X 18	-0298	-0458	-0618	-1098		2 X 18	-0218	-0378	-0538	-1018	
		2 X 19	-0299	-0459	-0619	-1099		2 X 19	-0219	-0379	-0539	-1019	
D		2 X 20	-0300	-0460	-0620	-1100		2 X 20	-0220	-0380	-0540	-1020	
		2 X 21	-0301	-0461	-0621	-1101		2 X 21	-0221	-0381	-0541	-1021	
		2 X 22	-0302	-0462	-0622	-1102		2 X 22	-0222	-0382	-0542	-1022	
		2 X 23	-0303	-0463	-0623	-1103		2 X 23	-0223	-0383	-0543	-1023	
		2 X 24	-0304	-0464	-0624	-1104		2 X 24	-0224	-0384	-0544	-1024	
		2 X 25	-0305	-0465	-0625	-1105		2 X 25	-0225	-0385	-0545	-1025	
		2 X 26	-0306	-0466	-0626	-1106		2 X 26	-0226	-0386	-0546	-1026	
		2 X 27	-0307	-0467	-0627	-1107		2 X 27	-0227	-0387	-0547	-1027	
		2 X 28	-0308	-0468	-0628	-1108		2 X 28	-0228	-0388	-0548	-1028	
		2 X 29	-0309	-0469	-0629	-1109		2 X 29	-0229	-0389	-0549	-1029	
C		2 X 30	-0310	-0470	-0630	-1110		2 X 30	-0230	-0390	-0550	-1030	
		2 X 31	-0311	-0471	-0631	-1111		2 X 31	-0231	-0391	-0551	-1031	
		2 X 32	-0312	-0472	-0632	-1112		2 X 32	-0232	-0392	-0552	-1032	
		2 X 33	-0313	-0473	-0633	-1113		2 X 33	-0233	-0393	-0553	-1033	
		2 X 34	-0314	-0474	-0634	-1114		2 X 34	-0234	-0394	-0554	-1034	
		2 X 35	-0315	-0475	-0635	-1115		2 X 35	-0235	-0395	-0555	-1035	
		2 X 36	-0316	-0476	-0636	-1116		2 X 36	-0236	-0396	-0556	-1036	
		2 X 37	-0317	-0477	-0637	-1117		2 X 37	-0237	-0397	-0557	-1037	
		2 X 38	-0318	-0478	-0638	-1118		2 X 38	-0238	-0398	-0558	-1038	
B		2 X 39	▼ -0319	▼ -0479	▼ -0639	▼ -1119		2 X 39	▼ -0239	▼ -0399	▼ -0559	▼ -1039	
		2 X 40	90131-0320	90131-0480	90131-0640	90131-1120		2 X 40	90131-0240	90131-0400	90131-0560	90131-1040	


10		9		8		7		6		5		4		3		2		1					
F		CIRCUIT SIZE		PLATING TYPE B PART NO.		PLATING TYPE C PART NO.		PLATING TYPE D PART NO.		PLATING TYPE G PART NO.		CIRCUIT SIZE		PLATING TYPE B PART NO.		PLATING TYPE C PART NO.		PLATING TYPE D PART NO.		PLATING TYPE G PART NO.		F	
		2 X 1		90131-0241		90131-0401		90131-0561		90131-1041		2 X 1		90131-0321		90131-0481		90131-0641		90131-1121			
E		2 X 2		↑ -0242		↑ -0402		↑ -0562		↑ -1042		2 X 2		↑ -0322		↑ -0482		↑ -0642		↑ -1122		E	
		2 X 3		-0243		-0403		-0563		-1043		2 X 3		-0323		-0483		-0643		-1123			
		2 X 4		-0244		-0404		-0564		-1044		2 X 4		-0324		-0484		-0644		-1124			
		2 X 5		-0245		-0405		-0565		-1045		2 X 5		-0325		-0485		-0645		-1125			
		2 X 6		-0246		-0406		-0566		-1046		2 X 6		-0326		-0486		-0646		-1126			
		2 X 7		-0247		-0407		-0567		-1047		2 X 7		-0327		-0487		-0647		-1127			
		2 X 8		-0248		-0408		-0568		-1048		2 X 8		-0328		-0488		-0648		-1128			
		2 X 9		-0249		-0409		-0569		-1049		2 X 9		-0329		-0489		-0649		-1129			
		2 X 10		-0250		-0410		-0570		-1050		2 X 10		-0330		-0490		-0650		-1130			
		2 X 11		-0251		-0411		-0571		-1051		2 X 11		-0331		-0491		-0651		-1131			
D		2 X 12		-0252		-0412		-0572		-1052		2 X 12		-0332		-0492		-0652		-1132		D	
		2 X 13		-0253		-0413		-0573		-1053		2 X 13		-0333		-0493		-0653		-1133			
		2 X 14		-0254		-0414		-0574		-1054		2 X 14		-0334		-0494		-0654		-1134			
		2 X 15		-0255		-0415		-0575		-1055		2 X 15		-0335		-0495		-0655		-1135			
		2 X 16		-0256		-0416		-0576		-1056		2 X 16		-0336		-0496		-0656		-1136			
		2 X 17		-0257		-0417		-0577		-1057		2 X 17		-0337		-0497		-0657		-1137			
		2 X 18		-0258		-0418		-0578		-1058		2 X 18		-0338		-0498		-0658		-1138			
		2 X 19		-0259		-0419		-0579		-1059		2 X 19		-0339		-0499		-0659		-1139			
		2 X 20		-0260		-0420		-0580		-1060		2 X 20		-0340		-0500		-0660		-1140			
		2 X 21		-0261		-0421		-0581		-1061		2 X 21		-0341		-0501		-0661		-1141			
C		2 X 22		-0262		-0422		-0582		-1062		2 X 22		-0342		-0502		-0662		-1142		C	
		2 X 23		-0263		-0423		-0583		-1063		2 X 23		-0343		-0503		-0663		-1143			
		2 X 24		-0264		-0424		-0584		-1064		2 X 24		-0344		-0504		-0664		-1144			
		2 X 25		-0265		-0425		-0585		-1065		2 X 25		-0345		-0505		-0665		-1145			
		2 X 26		-0266		-0426		-0586		-1066		2 X 26		-0346		-0506		-0666		-1146			
		2 X 27		-0267		-0427		-0587		-1067		2 X 27		-0347		-0507		-0667		-1147			
		2 X 28		-0268		-0428		-0588		-1068		2 X 28		-0348		-0508		-0668		-1148			
		2 X 29		-0269		-0429		-0589		-1069		2 X 29		-0349		-0509		-0669		-1149			
		2 X 30		-0270		-0430		-0590		-1070		2 X 30		-0350		-0510		-0670		-1150			
		2 X 31		-0271		-0431		-0591		-1071		2 X 31		-0351		-0511		-0671		-1151			
B		2 X 32		-0272		-0432		-0592		-1072		2 X 32		-0352		-0512		-0672		-1152		B	
		2 X 33		-0273		-0433		-0593		-1073		2 X 33		-0353		-0513		-0673		-1153			
		2 X 34		-0274		-0434		-0594		-1074		2 X 34		-0354		-0514		-0674		-1154			
		2 X 35		-0275		-0435		-0595		-1075		2 X 35		-0355		-0515		-0675		-1155			
		2 X 36		-0276		-0436		-0596		-1076		2 X 36		-0356		-0516		-0676		-1156			
		2 X 37		-0277		-0437		-0597		-1077		2 X 37		-0357		-0517		-0677		-1157			
		2 X 38		-0278		-0438		-0598		-1078		2 X 38		-0358		-0518		-0678		-1158			
		2 X 39		-0279		-0439		-0599		-1079		2 X 39		-0359		-0519		-0679		-1159			
		2 X 40		90131-0280		90131-0440		90131-0600		90131-1080		2 X 40		90131-0360		90131-0520		90131-0680		90131-1160			
		A		NON-STANDARD PRODUCTS NOT FOR GENERAL RELEASE		CHANGE DOC. NO EC NO: S2012-0490 DRMNAI SEE 2011/12/21 CHKD-SKANG 2011/12/28 APPR:MLONG 2012/02/24		QUALITY SYMBOLS ▽=0 ▽=0 ▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION		C GRID III DUAL ROW STRAIGHT PIN HEADER			
4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- ANGULAR ± 3 °										DRAWN BY DATE DB 1987/07/16 CHECKED BY DATE DB 1987/07/16 APPROVED BY DATE MLONG 2012/02/24		TITLE		DOCUMENT NO.									
A								DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
10		9		8		7		6		5		4		3		2		1					

CIRCUIT SIZE	PLATING TYPE A PART NO.	PIN PART NUMBER	WAFER PART NUMBER	DIM C ^(±0.20) ±.008	DIM D ^(±0.20) ±.008 -.012
2 X 6	90131-3126	90129-2008	90131-0040	(14.60) .575	(2.38) .094
2 X 36	90131-3128	90129-2008	90131-0040	(14.60) .575	(2.38) .094
2 X 40	90131-3127	90129-2008	90131-0040	(14.60) .575	(2.38) .094


STANDARD PRODUCTS

CHANGE DOC. NO EC NO: S2012-0490 DRWN:ATSEE 2011/12/21 CHKD:SKANG 2011/12/28 APPR:MLONG 2012/02/24 O	DESCRIPTION REV	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY DB	DATE 1987/07/16	C GRID III DUAL ROW STRAIGHT PIN HEADER				
			4 PLACES	± ---	± ---	CHECKED BY	DATE					
			3 PLACES	± ---	± ---	DB	1987/07/16					
			2 PLACES	± 0.20	± ---	APPROVED BY		DATE	MOLEX INCORPORATED			
			1 PLACE	± ---	± ---	MLONG		2012/02/24				
			ANGULAR ± 3 °		MATERIAL NO.		DOCUMENT NO.	SHEET NO.				
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-90131-001				8 OF 8	
					SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					






CKT SIZE	A	B
2	5.00	9.90
3	10.00	14.90
4	15.00	19.90



NOTES:
 1. MATERIALS:
 HOUSING: PA 6, UL94 V-2
 COLOUR: SEE SHEET 2
 TERMINAL: PHOSPHOR BRONZE, (0.50)/.020 THICK REF
 PLATING: (2 µm)/79 µm MIN SILVER IN CONTACT AREA
 (0.10 µm)/.004 µm MIN SILVER FLASH ALLOW

- PRODUCT CONFORMS TO SPECIFICATION PS-99020-0037
- ACCEPTS CABLE, PER ES-99036-0010
- SEE SUBSEQUENT SHEETS FOR PART NUMBERS SHOWING THE VARIOUS CODING, KEYING AND LATCHING OPTIONS.
- PACKAGING SPECIFICATION PK-90833-001
- APPLICATION SPECIFICATION AS-99033-0004




KEYING, CODING, & LATCH IDENTIFICATION
 (7 CKT EXAMPLE SHOWN)

ADDED PART NUMBERS		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO: IPG2014-1233		DRAWN: MONAHAN		2014/01/06		MM ONLY		1:1		METRIC		THIRD ANGLE PROJECTION	
CHKD: CHIKO		APPR: STIGLITZ		2014/01/20		DRAWN BY		DATE		TITLE		RAST 5 INDIRECT FEMALE ASSEMBLY 16 AMPS	
REV		DESCRIPTION		REV		CHECKED BY		DATE		MATERIAL NO.		DOCUMENT NO.	
AC		REV		REV		BAGUIRE		2005/01/07		BAGUIRE		2010/10/20	
						4 PLACES ±---		±---		SEE FOLLOWING SHEETS		SD-91779-001	
						3 PLACES ±---		±---		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SHEET NO. 1 OF 5	
						2 PLACES ±0.05		±---					
						1 PLACE ±0.1		±---					
						ANGULAR ±---°		±---					
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							


13	12	11	10	9									
MOLEX PART NO.	HOUSING NO.	CIRCUIT SIZE	COLOUR	POSITION KEYS	CODING KEYS	LATCH POSITION	CONFIGURATION	COLOUR STRIP	REF.				
91779-0001	91779-9001	2	NATURAL	1a, 1b 2a, 2b	01c, d20	1/2		NONE	K00				
91779-0002	91779-9001	2	NATURAL	1b, 2a	01c, d20	1/2		NONE	K01				
91779-0003	91779-9001	2	NATURAL	1a, 2b	d20	1/2		NONE	K05				
91779-0004	91779-9001	2	NATURAL	1a	01c, d20	1/2		NONE	K12				
91779-0005	91779-9001	2	NATURAL	1a, 2b	01c, d20	1/2		BLUE	K48				
91779-0006	91779-9004	2	RED	1a, 1b 2a, 2b	NONE	1/2		NONE	K41				
91779-0007	91779-9001	2	NATURAL	2a	01c	1/2		NONE	K42				
91779-0008	91779-9004	2	RED	1a, 1b 2a, 2b	d20	1/2		NONE	K34				
91779-0009	PART NUMBER OBSOLETE, REPLACED WITH 91779-0006.												
91779-0010	91779-9003	2	BLACK	1a, 1b 2a, 2b	NONE	1/2		NONE	K41				
91779-0011	91779-9001	2	NATURAL	1a	d20	1/2		NONE	K66				
91779-0012	91779-9001	2	NATURAL	1b	01c, d20	1/2		NONE	K16				
91779-0013	91779-9001	2	NATURAL	1a	NONE	1/2		NONE	K70				
91779-0014	91779-9001	2	NATURAL	1b 2a 2b	d20	1/2		NONE	K--				
91779-0015	91779-9001	2	NATURAL	1a, 1b 2a, 2b	d20	1/2		NONE	K34				
91779-0016	91779-9001	2	NATURAL	1a, 1b 2a, 2b	01c	1/2		NONE	K33				
91779-0017	91779-9004	2	RED	1a 1b 2b	NONE	1/2		NONE	K43				
91779-0018	91779-9001	2	NATURAL	1b 2b	01c	1/2		NONE	K09				
91779-0019	91779-9001	2	NATURAL	1b 2b	01c	1/2		GREEN	K--				
91779-0020	91779-9001	2	NATURAL	1a 2b	d20	1/2		GREEN	K--				
91779-0021	91779-9001	2	NATURAL	2a	01c, d20	1/2		BLACK	K--				
91779-0022	91779-9001	2	NATURAL	1b	d20	1/2		RED	K--				
91779-0023	91779-9001	2	NATURAL	1b 2b	01c	1/2		BLUE	K--				

MOLEX PART NO.	HOUSING NO.	CIRCUIT SIZE	COLOUR	POSITION KEYS	CODING KEYS	LATCH POSITION	CONFIGURATION	colour stripe	REF.
91779-0024	91779-9001	2	NATURAL	1b 2b	01c	1/2		ORANGE	K--
91779-0025	91779-9001	2	NATURAL	1a 1b	d20	1/2		NONE	K--
91779-0026	91779-9001	2	NATURAL	1a 2b	01c	1/2		NONE	K--
91779-0027	91779-9003	2	BLACK	1a 2b	NONE	1/2		NONE	K06
91779-0028	91779-9004	2	RED	2a 2b	NONE	1/2		NONE	K31
91779-0029	91779-9001	2	NATURAL	NONE	01c, d20	1/2		NONE	K--
91779-0030	91779-9001	2	NATURAL	1a 2a 2b	01c, d20	1/2		NONE	K62
91779-0031	91779-9001	2	NATURAL	1a 2a	01c, d20	1/2		NONE	K--
91779-0032	91779-9001	2	NATURAL	1b 2b	01c, d20	1/2		NONE	K--
91779-0033	91779-9001	2	NATURAL	1a, 1b 2a, 2b	01c, d20	1/2		RED	K09
91779-0034	91779-9001	2	NATURAL	1a, 1b 2a, 2b	01c, d20	1/2		GREEN	K--
91779-0035	91779-9001	2	NATURAL	2b	NONE	1/2		NONE	K--
91779-0036	91779-9001	2	NATURAL	1a, 1b 2a, 2b	NONE	1/2		NONE	K41
91779-0038	91779-9001	2	NATURAL	1b	NONE	1/2		NONE	K--



SEE SHEET 1 EC NO: IPG2014-4233 DRAWN: MONAHAN 2014/01/06 CHKD: CHIKO APPR: STIGLITZ 2014/01/20 AC	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.05 ± --- 1 PLACE ± 0.1 ± --- ANGULAR ± ---°	DIMENSION STYLE MM ONLY DRAWN BY DATE GMCSWEEN 2004/10/14 CHECKED BY DATE BMAGUIE 2005/01/07 APPROVED BY DATE BMAGUIE 2010/10/20 MATERIAL NO.	SCALE 2:1 DESIGN UNITS METRIC THIRD ANGLE PROJECTION	TITLE RAST 5 INDIRECT FEMALE ASSEMBLY 16 AMPS MOLEX INCORPORATED SD-91779-001 SHEET NO. 2 OF 5
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				
	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
	REV				
	DESCRIPTION				

CIRCUIT 2 CONTIN'D									
MOLEX PART NO.	HOUSING NO.	CIRCUIT SIZE	COLOUR	POSITION KEYS	CODING KEYS	LATCH POSITION	CONFIGURATION	COLOUR STRIPE	REF.
91779-0039	91779-9001	2	NATURAL	1a 2b	NONE	1/2		NONE	K06



SEE SHEET 1 EC NO: IPG2014-4233 DRAWN: MONAHAN 2014/01/06 CHKD: APPR: STRIFFLIN 2014/01/20 AC	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY	DATE	TITLE RAST 5 INDIRECT FEMALE ASSEMBLY 16 AMPS molex			
			4 PLACES	± ---	± ---	GMSWEEN	2004/10/14				
			3 PLACES	± ---	± ---	CHECKED BY	DATE	DOCUMENT NO. SD-91779-001			
			2 PLACES	± 0.05	± ---	BMAGUIE	2005/01/07				
			1 PLACE	± 0.1	± ---	APPROVED BY	DATE	SHEET NO. 3 OF 5			
0 PLACE	±	±	BMAGUIE	2010/10/20							
			ANGULAR ± --- °		MATERIAL NO.						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLES								
			SIZE A2		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

