

# RED INDICATES ORIGINAL


DWG  
SIZE  
C

DATA CONTAINED IN THIS DOCUMENT IS  
PROPRIETARY TO TROMPETER ELECTRONICS INC.  
AND SHALL NOT BE DISCLOSED, COPIED OR USED  
FOR REPRODUCTION OR MANUFACTURE WITHOUT  
EXPRESS WRITTEN PERMISSION.

| REVISIONS |       |                                                                                               | 105-0999 |          | SH      |
|-----------|-------|-----------------------------------------------------------------------------------------------|----------|----------|---------|
| REV       | ECO   | DESCRIPTION                                                                                   | DWN      | APPROVED | DATE    |
| B         | 10736 | DIM .56 $\pm$ .03 WAS .555<br>$\pm$ .010; DIM .290 $\pm$ .010 WAS<br>.290 $\pm$ .005; SEE ECO | DKC      | BMI      | 6/28/94 |


| DASH<br>NO | MODEL NUMBER      | DESCRIPTION          | DASH<br>NO | MODEL NUMBER       | DESCRIPTION           |
|------------|-------------------|----------------------|------------|--------------------|-----------------------|
| -1         | TNHF1-1- $\Delta$ | TERM (NO CHAIN)      | -8         | TNHF1-8- $\Delta$  | TERM 4.0 BRASS CHAIN  |
| -2         | TNHF1-2- $\Delta$ | TERM 2.5 BRASS CHAIN | -9         | TNHF1-9- $\Delta$  | TERM 4.0 NYLON CHAIN  |
| -3         | TNHF1-3- $\Delta$ | TERM 2.5 NYLON CHAIN | -10        | TNHF1-10- $\Delta$ | TERM 10.0 BRASS CHAIN |
| -4         | TNHF1-4- $\Delta$ | TERM 3.0 BRASS CHAIN | -11        | TNHF1-11- $\Delta$ | TERM 10.0 NYLON CHAIN |
| -5         | TNHF1-5- $\Delta$ | TERM 3.0 NYLON CHAIN | -12        | TNHF1-12- $\Delta$ | TERM 2.5 SST ROPE     |
| -6         | TNHF1-6- $\Delta$ | TERM 6.0 BRASS CHAIN | -13        | TNHF1-13- $\Delta$ | TERM 3.0 SST ROPE     |
| -7         | TNHF1-7- $\Delta$ | TERM 6.0 NYLON CHAIN | -14        | TNHF1-14- $\Delta$ | TERM 6.0 SST ROPE     |

| INCH | MM    | INCH  | MM     |
|------|-------|-------|--------|
| .005 | 0.13  | .56   | 14.22  |
| .010 | 0.25  | .645  | 16.38  |
| .030 | 0.76  | 1.542 | 39.17  |
| .082 | 1.58  | 2.5   | 63.50  |
| .140 | 3.55  | 3.0   | 76.20  |
| .200 | 5.08  | 4.0   | 101.60 |
| .25  | 6.35  | 6.0   | 152.40 |
| .406 | 10.31 | 10.0  | 254.00 |




.4375-28UNEF-2A

-1 SHOWN  
NO CHAIN/ROPE OR  
MOUNTING LUG



.4375-28UNEF-2A

-2 THRU -11 SHOWN  
STANDARD CHAIN AND  
MOUNTING LUG



-12-THRU  
-14-SHOWN

5. EXAMPLE OF COMPLETE MODEL NO:  $\Delta$   
TNHF1 - 2 -  $\Delta$


BASIC MODEL NO  $\Delta$  CHAIN/ROPE MATL AND LENGTH  
TNHF1 (50 OHM) (SEE TABLE)  
UTNHF1 (75 OHM)

4. TERMINATED FEMALE COAXIAL TNC TYPE RECEPTACLE WITH  
OR WITHOUT CHAIN OR JACKETED STAINLESS STEEL ROPE  
AND MOUNTING LUG OPTION

$\Delta$  RESISTANCE VALUE IN OHMS (1/2W, 1%) S = CONTACT  
SHORTED TO CASE (NO RESISTOR)

2. FINISH: TFS-1A (NICKEL)

1. ALL DIM ARE IN INCHES



| QTY                  | DESCRIPTION                 | PART NUMBER   | ITEM         |
|----------------------|-----------------------------|---------------|--------------|
| TOL UNLESS SPECIFIED | TROMPETER ELECTRONICS, INC. | TNHF1/UTNHF1  |              |
| .XX $\pm$ .005       |                             |               |              |
| .XXX $\pm$ .005      |                             |               |              |
| .XXXX $\pm$ .005     |                             |               |              |
| ANGLES               |                             |               |              |
| DWN DKC 8-14-94      | MATERIAL                    | CODE IDENT    | DRAWING NO.  |
| CHK BMI 6-28-99      |                             | 14949         | 105-0999     |
| ENGR                 |                             |               | REV B        |
| APPR BMI 6/22/94     | SCALE 2/1                   | DATE 10-16-79 | SHEET 1 OF 2 |

NEXT ASSY