



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	WIRE SIZE		DIMENSIONS in. [mm]				
	AWG	mm ²	L ± .03 [0,8]	B ± .01 [0,3]	C ± .015 [0,4]	D ± .01 [0,3]	E ± .01 [0,3]
P18-P47*	#22-18	0,5-1,0	.75 [19,1]	.07 [1,8]	.49 [12,4]	.14 [3,6]	.06 [1,5]
P14-P47*	#16-14	1,5-2,5	.75 [19,1]	.07 [1,8]	.49 [12,4]	.16 [4,1]	.08 [2,0]
P10-P55	#12-10	4,0-6,0	.79 [20,1]	.11 [2,8]	.55 [14,0]	.22 [5,6]	.15 [3,8]



NOTES:

- USED FOR:
 - SOLID OR STRANDED COPPER WIRE
 - 302°F [150°C] MAX. OPERATING TEMPERATURE
- INSTALLATION TOOLS:
 - PANDUIT APPROVED: CT-100A, CT-160, CT-200, CT-260, CT-1570, CT-600-A (CT-570CH), CT-2500 (CT-2570CH)
- WIRE STRIP LENGTH: 9/32" ^{+1/32}/₀ [7,1^{+0,8}/₀]
- MATERIAL:
 - STAMPING: .03" [0,8] THK COPPER, TIN PLATED
- SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



E52164

06	09.19.12	JBN	LCA	VMB	ADDED METRIC EQUIVALENT. REVISED NOTES. UPDATED TO CURRENT STANDARDS.	A41334
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE PIN TERMINAL, NON-INSULATED,			
CUSTOMER DRAWING			
ITEM REVISION NAME N41334BA/06		PANDUIT	
DATASET FILE NAME N41334BA_DC/06A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.13] .xx ± .01 [.25] ANGLES ± 5 °		MATERIAL: SEE NOTES	
THIRD ANGLE PROJECTION 		DRAWING NUMBER: A41334	
DRAWN BY DAW	DATE -	CHK RLS	SCALE N.T.S.
SHEET 1 OF 1			SIZE A