

スパークギャップ SPARK GAPS

OPERATING TEMP. -30~+85°C



特長 FEATURES

- 自己消火性樹脂を用い、安全性が高い
- もれ電流が極めて小さい
- 静電容量が極めて小さい
- Very safe due to self-extinguishing resin
- Leakage current is very small.
- Electrostatic capacitance is very small.

用途 APPLICATIONS

- CRT周辺の異常電圧吸収
- Used to absorb abnormal voltages in the periphery of a CRT

形名表記法 ORDERING CODE

1

形式

AG	スパークギャップ
----	----------

2

外径形状

15	外形寸法毎の各タイプ
20	

3

樹脂材料

P	アルキド樹脂
---	--------

4

被覆状態

△	樹脂キャップなし
C	樹脂キャップ付

△=スペース

5

公称放電開始電圧 [VDC]

122	1200
492	4900

6

放電電圧許容差 [V]

F	±500
G	±800

7

包装

△ー	20 タイプ単品(袋詰め)
Sー	15 タイプ単品(袋詰め)
Bー	15 タイプテーピング品

△=スペース

8

リード形状 [mm]

	形状	間隔	径	長さ
H3D	Hフォーミング	6.4	0.65	5.0±0.8
L3N	ストレート	6.4	0.65	24以上
K2M	Kフォーミング	5.0	0.60	20以上
K2U	Kフォーミング	5.0	0.60	5.0±1
K4M	Kフォーミング	6.4	0.60	20以上
K4U	Kフォーミング	6.4	0.60	5.0±1

A	G	1	5	P	C	1	2	2	F	S	—	K	2	M	
1		2		3		4		5		6		7		8	
1															
Type															
AG		Spark gaps													
2															
External dimension															
15		Type by external dimension													
20															
3															
Resin material															
P		Alkyd resin													
4															
Coating conditions															
△		without resin cap													
C		with resin cap													
		△=Blank space													
6															
Discharge voltage															
Tolerance [V]															
F		±500													
G		±800													
8															
Lead configuration [mm]															
	Lead type		Lead space		Diameter		Length								
H3D		H-formed		6.4		0.65		5.0±0.8							
L3N		Straight		6.4		0.65		24Min.							
K2M		K-formed		5.0		0.60		20Min.							
K2U		K-formed		5.0		0.60		5.0±1							
K4M		K-formed		6.4		0.60		20Min.							
K4U		K-formed		6.4		0.60		5.0±1							
7															
Packaging															
△—		Type 20, bulk													
S—		Type 15, bulk													
B—		Type 15, taped													
		△=Blank space													

