




PRODUCT NUMBER
SEE TABLE



SEE SHEET 3 FOR
LOCATOR/HOLDDOWN
VARIATIONS

.014 [0.36]
AT TIPS



mat'l. code -				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE					
ltr		ecn no		dr		date		tolerances unless otherwise specified				title			
L		J10329		CRG		6/6/01		angles		linear		.XX±.01/0.3			
M		M05-0123		MHT		6/6/05						.XXX±.005/0.13			
N		M06-0225		ERE		06/12/06		0±2°				.XXXX±.0020/0.051		scale 4:1	
P		M06-0370		MHT		9/26/06		dr		M. CORNMAN		6/6/95			
R		M09-0058		MHT		4/04/09		enrg		D. WHITING		6/6/95			
S		N10-0122		YO		5/10/10		chr		D. WHITING		6/6/95			
T		ELX-N-009749		YO		1/31/12		appd		D. WHITING		6/6/95			
sheet		revision		T		T		T		T		T		T	
index		sheet		1		2		3		4		5		6	

dwg no		sheet 1 of 6		size	
95776				A3	
type		Product		Customer Drawing	




FCIconnect.com


Copyright FCI

PRODUCT NUMBER
SEE TABLE

SIZE	DIM H	DIM J	DIM K	DIM L
2X5	.275/6.99	.200/5.08	.372/9.45	.320/8.13
2X10	.525/13.34	.450/11.43	.622/15.80	.570/14.48
2X15	.775/19.68	.700/17.78	.872/22.15	.820/20.83
2X20	1.025/26.03	.950/24.13	1.122/28.50	1.070/27.18
2X25	1.275/32.38	1.200/30.48	1.372/34.85	1.320/33.53
2X30	1.525/38.74	1.450/36.83	1.622/41.20	1.570/39.88
2X35	1.775/45.08	1.700/43.18	1.872/47.55	1.820/46.23
2X40	2.025/51.43	1.950/49.53	2.122/53.90	2.070/52.58
2X45	2.275/57.78	2.200/55.88	2.372/60.25	2.320/58.93
2X50	2.525/64.14	2.450/62.23	2.622/66.60	2.570/65.28



SECTION X-X
ROTATED 90° CW




SECTION Y-Y

mat'l. code -				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family RIBCAGE			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		scale 4:1	title		
T					angles	linear		RIBCAGE III T/M VERT. HEADER ASS'Y		
					0.002	.XX±.01/0.3 .XXX±.005/0.13 .XXXX±.0020/0.051				
					dr	M. CORNMAN 6/6/95				
					enr	D. WHITING 6/6/95	FCI	dwg no		sheet 2 of 6
					chr	D. WHITING 6/6/95		95776		size A3
					appd	D. WHITING 6/6/95		type Product Customer Drawing		
sheet index	revision sheet									


PRODUCT NUMBER
SEE TABLE

LOCATOR/HOLDDOWN VARIATIONS


STYLE
1





STYLE
2




STYLE
4



STYLE
6



STYLE
7




mat'l. code -				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection ISO 1101	product family RIBCAGE			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		INCH/MM	title		
T					angles	linear		RIBCAGE III T/M VERT. HEADER ASS'Y		
					0.002	.XXX ± .005 / 0.13	scale 4:1	dwg no		
						.XXX ± .0020 / 0.051		sheet 3 of 6		
					dr	M. CORNMANN	6/6/95	size		
					enr	D. WHITING	6/6/95	95776		
					chr	D. WHITING	6/6/95	A3		
					appd	D. WHITING	6/6/95	type Product Customer Drawing		
sheet index	revision sheet									


PRODUCT NUMBER
SEE TABLE

RECOMMENDED P. C. B. LAYOUT


STYLE
1




STYLE
6




STYLE
2



STYLE
7



STYLE
4




mat'l. code				surface	tolerance	projection	product family		
-				ISO 1302 ✓	ISO 406 ISO 1101		RIBCAGE		
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title		
T					angles	linear	RIBCAGE III T/M		
					0.002?		VERT. HEADER ASS'Y		
							dwg no		
					dr	M. CORNMEN	6/6/95	sheet 4 of 6	size
					enr	D. WHITING	6/6/95	95776	A3
					chr	D. WHITING	6/6/95	type	
					appd	D. WHITING	6/6/95	Product Customer Drawing	
sheet	revision								
index	sheet								


PRODUCT NUMBER
SEE TABLE

RECOMMENDED P. C. B. LAYOUT


STYLE
1




STYLE
2



STYLE
4



STYLE
6



mat'l. code				surface	tolerance	projection	product family		
-				ISO 1302 ☒	ISO 406 ISO 1101		RIBCAGE		
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title		
T					angles	linear	RIBCAGE III T/M		
					0.002?		VERT. HEADER ASS'Y		
							dwg no		
					dr	M. CORNMAN	6/6/95	sheet 5 of 6	size
					enr	D. WHITING	6/6/95	95776	A3
					chr	D. WHITING	6/6/95	type	
					appd	D. WHITING	6/6/95	Product Customer Drawing	
sheet	revision								
index	sheet								

