


PART NUMBER	MATERIAL	"A" HEIGHT +/- .062	IMPRINT AREA "B" +/- .062	VERTICAL REPEAT "C" +/- .062	LABELS PER ROW	STANDARD PKG. QTY.
S150X225TAT	GMT1	2.25 [57.2]	0.75 [19.1]	2.50 [63.5]	2	5000
S150X150VATY	GMV16 OR GMV17	1.50 [38.1]	0.50 [12.7]	1.75 [44.45]		5000
S150X225VATY		2.25 [57.2]	0.75 [19.1]	2.50 [63.5]		5000
S150X400VATY		4.00 [101.6]	1.00 [25.4]	4.25 [114.3]		2500

6

NOTE:

1. MILLIMETER ARE IN [].



CAD FILENAME/LAYERS

I00701MV_DC_C10438/07G

6	10/25/11	RVU		"GMV16 OR GMV17" WAS "GMV".	6548	R					PANDUIT CORP. TINLEY PARK, ILLINOIS
5	12/10/09	RVU	MSAD	ADD +/- .062 AND UPDATE ALL STANDARD TOLERANCES.	5469	R					CUSTOMER DRAWING OPTIMUM SELF-LAM.
4	6/23/08	RVU	MSAD	REMOVED NOTES 2. ADD TOL. ON TITLE AREA. 2 DECIAL PLCS.	5469	R					S150X***VATY
3	5/14/08	RVU	RVU	CHANGE FORMAT 'B' TO 'A'.	5440	R					THERMAL TRANSFER PRINTABLE LABELS
2	4/18/08	RVU	DWY	GMV16 WAS GMV3. CHANGE TOL. FROM +/- .031 TO +/- .050. TITLE TOL. TO INCREASE WITH +/- .050 AND .010.	5400	R					UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XXX) ± .025 (.XX) ± .062 ANGLES ±
1	5/25/07	RVU	DWY	ADDED NEW PART, S150X225TAT. FOR S150X400VATY, STD. PKG. QTY. WAS 5000.	5020	R					UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
0	8-4-06	RVU	DWY	DRAWING RELEASE.	4620	R					SCALE NTS
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP			DRAWING NO. C10438

DRAWN BY

RVU

DATE

8-4-06

CHK'D

MAT'L:

SEE TABLE

DRAWING NO.

C10438

DWG
A
SIZE