





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B4	REVISED PER ECR-15-012073	13AUG2015	NK	WW
	B6	ECR-16-016334	18NOV2016	FV	RR
	B7	ECR-17-009651	19JUL2017	RS	DC



ISO VIEW



- 1 WIRE RANGE : STRANDED 0.22-0.35 mm₂ (INS. DIA. 1.30±0.1)
- 2 MATING PART: TAB HEADER P/N 829866;
PCB FRAME P/N 964575 (PCB THK 1.5±0.14 COPPER CLADDING INCLUDED)
SEE PRODUCT SPEC. 108-18056 FOR FRAME APPLICATION
- 3 KEYING RIBS TO BE REMOVED BY TERMINATION MACHINE
- 4 CUT OFF DIMENSION DUE TO PRODUCTION PROCESS
- 5 CIRCUIT No. IDENTIFICATION
- 6 TE TRADEMARK (OPTIONAL POSITION)
- 7 TAMPOGRAPHIC COLOUR CODE AREA
(P/Ns IDENTIFICATION BEFORE CRIMPING)
- 8 CAVITIES 1 AND 3 LOADED WITH CONTACT
- 9 PBT GF
- 10 PBT GF, UL94-V0 & GWEPT 750 NO-FLAME, NATURAL

BLUE	3	5.0	9.9	3-284970-3	3-2311509-3
GREEN				2-284970-3	2-2311509-3
BROWN				1-284970-3	1-2311509-3
-				0-284970-3	2311509-3
COLOUR CODE 7	HSG POS.	DIM. A	DIM. B	9 TE P/N 8	10 TE P/N 8

-	-	-	-	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. FABRIS 17 MAY 05	TE Connectivity DUOPLUG 2.5 FEMALE CONNECTOR STANDARD VERSION, 2 POS. (HIGHER COVER RETENTION)		
SEE TABLE	PH. BRONZE, TIN PLATED	IDC RECEPTACLE CONTACT	2		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ±1° FINISH -	CHK -			
	PBT GLASS FIBER FILLED	FEMALE HOUSING	1			APVD G. TURCO 17 MAY 05			
						PRODUCT SPEC 108-18056 APPLICATION SPEC 114-18049-1			
Q.TY	MATERIAL	DESCRIPTION	ITEM	MATERIAL SEE TABLE		WEIGHT -	SIZE A100779	CAGE CODE C=284970	RESTRICTED TO -
REVISIONE DELL'ASSEMBLATO (REVISION OF EACH ASSY NO)				CUSTOMER DRAWING			SCALE 5:1	SHEET 1	OF 1
ELENCO DEI COMPONENTI (PARTS LIST)							REV B7		