

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

49760A Molded Cable Assemblies - D-Subminiature Assembly



For more Information
please call

1-800-Belden1



General Description:

50-position shielded D-Sub, for high-density applications where assembly is exposed to high noise environment, polyethylene insulation, foil plus braid shield, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material	Dia. (in.)
50	26	7x34	TC - Tinned Copper	.019

Total Number of Conductors: 50

Number of Pins: 50

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PE - Polyethylene	0.01

Connector Characteristics

Connector Characteristics - First End # of Connector Contacts/positions: 50

Connector Characteristics - First End Connector Gender: Male

Connector Characteristics - First End Connector Shielding Type: Metal Backshells

Connector Characteristics - First End Connector Type: D-Sub

Connector Characteristics - First End Overmold Color: Chrome

Connector Characteristics - First End Overmold Compound Material: PVC

Connector Characteristics - First End Overmold Type: 50 Position D-Sub

Connector Characteristics - First End Retention Hardware: Thumbscrew

Connector Characteristics - Second End # of Connector Contacts/positions: 50

Connector Characteristics - Second End Connector Gender: Male

Connector Characteristics - Second End Connector Shielding Type: Metal Backshells

Connector Characteristics - Second End Connector Type: D-Sub

Connector Characteristics - Second End Overmold Color: Chrome

Connector Characteristics - Second End Overmold Compound Material: PVC

Connector Characteristics - Second End Overmold Type: 50 Position D-Sub

Connector Characteristics - Second End Retention Hardware: Thumbscrew

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	90

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
22	7x30	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.049

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

49760A Molded Cable Assemblies - D-Subminiature Assembly

Overall Cable

Overall Nominal Diameter: 0.535 in.

Assembly Dimensional

Assembly Dimensional Length: 5

Wiring

Wiring: Wiring: Point to Point. Pin #1 on end 1 to pin #1 on end 2. Pin #2 to pin #2, etc. Cable shield connected to connector shell.

Mechanical Characteristics (Overall)

UL Temperature Rating: 80°C (UL AWM Style 2919)

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CM (cable only)

AWM Specification: UL Style 2919 (30 V 80°C) (cable only)

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 05/01/2006

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Max. Operating Voltage - UL:

Voltage

30 V RMS (UL AWM Style 2919)

Notes (Overall)

Notes: Molded handles are 100% shielded to guard against EMI/RFI and assist in FCC compliance. All connectors tin-plated and male connectors have detents to allow for a positive shield to ground connection.

Notes (Cont'd.): Wiring is point-to-point with the shield to connector shell. Jack screw retention on both connectors.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
49760A 060S2	1 EA	0.520 LB	CHROME		50 POS SHD D-SUB RI37943

Revision Number: 1 Revision Date: 09-19-2008

© 2015 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.