






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		A	INITIAL RELEASE	20APR2014	CW	SH
			B	ADD-3	25OCT2016	PP	SH



SCALE 5:1

SCALE 4:1


- 1 MATERIAL: 0.25mm THICK STAINLESS STEEL.
- 2 FINISH: NICKEL, NON PLATED EDGES PERMISSIBLE.
3. MATES WITH SFP MSA COMPLIANT TRANSCEIVERS.
- 4 PADS AND VIAS CHASSIS GROUND.
- 5 DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
6. MINIMUM PC BOARD THICKNESS:
SINGLE SIDED = 1.50 mm
- 7 REFERENCE APPLICATION SPEC. 114-13120, HOLE A, FOR
RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS(EXCEPT IMMERSION SILVER PLATING).
- 8 REFERENCE APPLICATION SPEC. 114-13120, HOLE C, FOR
RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS(EXCEPT IMMERSION SILVER PLATING).
- 9.THE RECOMMENDED DIMENSIONS FOR HOLES ON PAGE 2/2 ARE NOT COMPATIBLE WITH IMMERSION SILVER PLATING HOLES
BECAUSE OF OVERLARGE INSERTION FORCE.




WITHOUT KICK-OUT SPRING(PAGE 2)	2227023-3
WITH KICK-OUT SPRING(PAGE 1)	2227023-1
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009		DWN C. VALENTINE CHK M. SCHMITT APVD W. SCHMITT	07NOV2012 07NOV2012 07NOV2012	 TE Connectivity				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SFP, 1X1 SINGLE PIECE CAGE, PRESS FIT	SIZE A1	CAGE CODE 00779	DRAWING NO C=2227023	RESTRICTED TO -
		0 PLC ± 1 PLC ±0.2 2 PLC ±0.1 3 PLC ±0.1 4 PLC ± ANGLES ± FINISH -						
MATERIAL -		CUSTOMER DRAWING		SCALE 6:1		SHEET 1 OF 3		REV B





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
		-	-	SEE SHEET 1	-	-



SCALE 5:1



SCALE 4:1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. VALENTIN CHK M. SCHMITT APVD M. SCHMITT	07NOV2012 07NOV2012 07NOV2012	 TE Connectivity			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:			NAME SFP, 1X1 SINGLE PIECE CAGE, PRESS FIT - SIZE CAGE CODE DRAWING NO A100779C=2227023		
mm		0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES	± ±0.2 ±0.1 ±0.1 ± ±	RESTRICTED TO - - - - -			
MATERIAL		FINISH				Customer Drawing	
-		-					SCALE 6:1 SHEET 2 OF 3 REV B
-		-					
-		-					

