

|                          |                     |
|--------------------------|---------------------|
| L53HDTNR254, L53HDTNR5/7 | BRIGHT RED          |
| L53IDTNR254, L53IDTNR5/7 | HIGH EFFICIENCY RED |
| L53GDTNR254, L53GDTNR5/7 | GREEN               |
| L53YDTNR254, L53YDTNR5/7 | YELLOW              |
| L53ADTNR254, L53ADTNR5/7 | YELLOW              |

### Features

- FOR THE USE OF AUTOMATIC INSERTION MACHINE.
- 5mm FORMED LEAD AND 2.54mm STRAIGHT LEAD.
- SPACING AVAILABLE.
- RECTANGULAR LED LAMPS ALSO AVAILABLE IN TAPE & REEL PACKAGE.
- AMMO PACKS ALSO AVAILABLE.

### Description


The Bright Red source color devices are made with Gallium Phosphide Red Light Emitting Diode.

The High Efficiency Red source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Orange Light Emitting Diode.

The Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.

The Yellow source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Yellow Light Emitting Diode.

### Package Dimensions



## Selection Guide

| Part No.                   | Dice                            | Lens Type       | Iv (mcd)<br>@ 10 mA |      | Viewing<br>Angle |
|----------------------------|---------------------------------|-----------------|---------------------|------|------------------|
|                            |                                 |                 | Min.                | Typ. | 2θ1/2            |
| L53HDTNR254<br>L53HDTNR5/7 | BRIGHT RED (GaP)                | RED DIFFUSED    | 2                   | 5    | 60°              |
| L53IDTNR254<br>L53IDTNR5/7 | HIGH EFFICIENCY RED (GaAsP/GaP) | RED DIFFUSED    | 8                   | 25   | 60°              |
| L53GDTNR254<br>L53GDTNR5/7 | GREEN (GaP)                     | GREEN DIFFUSED  | 5                   | 20   | 60°              |
| L53YDTNR254<br>L53YDTNR5/7 | YELLOW (GaAsP/GaP)              | YELLOW DIFFUSED | 5                   | 20   | 60°              |
| L53ADTNR254<br>L53ADTNR5/7 | YELLOW (GaAsP/GaP)              | AMBER DIFFUSED  | 5                   | 20   | 60°              |

Note:

1. θ1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.

## Electrical / Optical Characteristics at T<sub>A</sub>=25°C


| Symbol            | Parameter               | Device                                               | Typ.                      | Max.                     | Units | Test Conditions |
|-------------------|-------------------------|------------------------------------------------------|---------------------------|--------------------------|-------|-----------------|
| λ <sub>peak</sub> | Peak Wavelength         | Bright Red<br>High Efficiency Red<br>Green<br>Yellow | 700<br>627<br>565<br>590  |                          | nm    | IF=20mA         |
| λ <sub>D</sub>    | Dominate Wavelength     | Bright Red<br>High Efficiency Red<br>Green<br>Yellow | 660<br>625<br>568<br>588  |                          | nm    | IF=20mA         |
| Δλ <sub>1/2</sub> | Spectral Line Halfwidth | Bright Red<br>High Efficiency Red<br>Green<br>Yellow | 45<br>45<br>30<br>35      |                          | nm    | IF=20mA         |
| C                 | Capacitance             | Bright Red<br>High Efficiency Red<br>Green<br>Yellow | 40<br>15<br>15<br>20      |                          | pF    | VF=0V;f=1MHz    |
| V <sub>F</sub>    | Forward Voltage         | Bright Red<br>High Efficiency Red<br>Green<br>Yellow | 2.25<br>2.0<br>2.2<br>2.1 | 2.5<br>2.5<br>2.5<br>2.5 | V     | IF=20mA         |
| I <sub>R</sub>    | Reverse Current         | All                                                  |                           | 10                       | μA    | VR = 5V         |

## Absolute Maximum Ratings at $T_A=25^{\circ}\text{C}$





| Parameter                     | Bright Red                                     | High Efficiency Red | Green | Yellow | Units |
|-------------------------------|------------------------------------------------|---------------------|-------|--------|-------|
| Power dissipation             | 120                                            | 105                 | 105   | 105    | mW    |
| DC Forward Current            | 25                                             | 30                  | 25    | 30     | mA    |
| Peak Forward Current [1]      | 120                                            | 160                 | 140   | 140    | mA    |
| Reverse Voltage               | 5                                              | 5                   | 5     | 5      | V     |
| Operating/Storage Temperature | $-40^{\circ}\text{C}$ To $+85^{\circ}\text{C}$ |                     |       |        |       |
| Lead Solder Temperature [2]   | 260 $^{\circ}\text{C}$ For 5 Seconds           |                     |       |        |       |

Notes:





- 1/10 Duty Cycle, 0.1ms Pulse Width.
- 4mm below package base.







## Bright Red L53HDTNR254, L53HDTNR5/7







## High Efficiency Red L53IDTNR254, L53IDTNR5/7




## Green L53GDTNR254, L53GDTNR5/7



Yellow L53YDTNR254, L53ADTNR254, L53YDTNR5/7, L53ADTNR5/7



Reel Dimensions



ANODE LEAD  
LEAVES THE REEL FIRST

