

MODELS | RCM3100 | RCM3110 |

MODELS | RCM3100 | RCM3110 |

- Powerful Rabbit® 3000 microprocessor at 29.4 MHz
- Low power 3.3 V operation
- Low-EMI (typically <10 dB μ V/m @ 3 m)
- Up to 512K Flash/512K SRAM
- 54 digital I/O
- 6 serial ports (IrDA, SDLC/HDLC, Async, SPI)
- Low power “sleepy” modes (< 2mA)

- Easy plug-in module for quick development
- Low cost embedded control
- Industry proven integrated development environment
- Abundant samples and libraries
- Easily links to multiple serial devices

- Device intelligence
- Embedded control
- Sensor reading
- Serial device coordinator
- GPS/AVL applications



Available in two models, the RCM3100 operates at 29.4 MHz, 3.3 V (with 5 V-tolerant I/O) The RCM3100 is equipped with up to 512K each of Flash and SRAM, low-EMI features, quadrature encoder inputs, PWM outputs, and pulse capture and measurement capabilities. Two 34-pin connection headers provide 54 digital I/O shared with the 6 serial ports and alternate I/O features, configured for 8 data lines and 6 address lines (shared with parallel I/O). The RCM3100 is pin compatible with the Ethernet RCM3000, facilitating

RABBIT
Semiconductor

www.rabbit.com

Developing with RabbitCores

The RabbitCore family of microprocessor core modules is designed to facilitate rapid development of embedded systems. RabbitCores mounts on a user-designed motherboard and acts as the controlling microprocessor for the user's system. Small in size, packed with powerful features, and armed with the Dynamic C software with sample libraries, these core modules give designers a complete package for control and communication.

Dynamic C Add-on Modules

Dynamic C Add-on modules provide added functionality and customization to your embedded applications. Software is available via download or CD-ROM.



Advanced Encryption Standard

128-bit encryption for transfer of sensitive data



Point-to-Point Protocol

TCP/IP functionality for serial and PPPoE connections



Library Encryption Executable


Program to encrypt Dynamic C library source files

µC/OS-II Real-Time Kernel

Real-time preemptive, prioritized operating system

Rabbit Field Utility (RFU)

Source code for the Rabbit Field Utility



RCM3100 RabbitCore Specifications		
Feature	RCM3100	RCM3110
Microprocessor	Rabbit® 3000 at 29.4 MHz	
EMI Reduction	Spectrum spreader for reduced EMI (radiated emissions)	
Flash Memory	512K (2 × 256K)	256K
SRAM	512K	128K
Backup Battery	Connection for user-supplied backup battery to (support RTC and SRAM)	
General-Purpose I/O	z54 parallel digital I/O lines: • 46 configurable I/O • 4 fixed inputs • 4 fixed outputs	
Additional Digital Inputs	2 startup mode, reset in	
Additional Digital Outputs	Status, reset out	
Auxiliary I/O Bus	8 data lines and 6 address lines (shared with I/O) plus I/O read/write	
Serial Ports	6 shared high-speed, CMOS-compatible ports: • 6 configurable as asynchronous (with IrDA), 4 as clocked serial (SPI), and 2 as SDLC/HDLC (with IrDA) • 1 asynchronous clocked serial port dedicated for programming support for MIR/SIR IrDA transceiver	
Serial Rate	Max. asynchronous baud rate = CLK/8	
Slave Interface	A slave port allows the RCM3100 to be used as a master or as an intelligent peripheral device with Rabbit-based or any other type of processor	
Real-Time Clock	Yes	
Timers	Ten 8-bit timers (6 cascadable from the first), one 10-bit timer with 2 match registers	
Watchdog/Supervisor	Yes	
Pulse-Width Modulators	10-bit free-running counter and four pulse-width registers	
Input Capture	2-channel input capture can be used to time input signals from various port pins	
Quadrature Decoder	2-channel quadrature decoder accepts inputs from external incremental encoder modules	
Power	3.15 V to 3.45 V DC 75 mA @ 3.3 V	
Operating Temperature	−40°C to +85°C	
Humidity	5% to 95%, non-condensing	
Connectors (for connection to headers J4 and J5)	Two 2 × 17, 2 mm pitch	
Board Size	1.850" × 1.650" × 0.55" (47 mm × 42 mm × 14 mm)	
Pricing		
Pricing (qty. 1/100/1000 Part Number)	\$65 / 50 / 43 20-101-0517	\$45 / 35 / 29 20-101-0518
Development Kit Part Number	\$239 U.S. 101-0533 Int'l 101-0534	

RCM3100 Development Kit comes complete with:

- RCM3100 RabbitCore Module
- Prototyping Board
- Serial cable for programming and debugging
- Dynamic C® integrated development software
- Getting Started Instructions
- Complete product documentation on CD including the Rabbit 3000 reference manual
- AC adapter (U.S. only)
- Rabbit 3000 pin specifications poster