

### Is Now Part of



## ON Semiconductor®

# To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (\_), the underscore (\_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (\_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at <a href="www.onsemi.com">www.onsemi.com</a>. Please email any questions regarding the system integration to Fairchild <a href="guestions@onsemi.com">guestions@onsemi.com</a>.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officer



March 2015

# FAN431A Programmable Shunt Regulator

#### **Features**

- Programmable Output Voltage to 36 V
- Low Dynamic Output Impedance: 0.2  $\Omega$  (Typical)
- Sink Current Capability: 1.0 to 100 mA
- Equivalent Full-Range Temperature Coefficient of 50 ppm/°C (Typical)
- Temperature Compensated for Operation Over Full Rated Operating Temperature Range
- · Low Output Noise Voltage
- · Fast Turn-on Response

### Description

The FAN431A is a three-terminal output adjustable regulator with thermal stability over the full operating temperature range. The output voltage can be set to any value between  $V_{REF}$  (approximately 2.5 V) and 36 V with two external resistors. This device has a typical dynamic output impedance of 0.2  $\Omega$ . Active output circuit provides a sharp turn-on characteristic, making this device excellent replacements for zener diodes in many applications.



### **Ordering Information**

Part Number	Operating Temperature Range	Output Voltage Tolerance	Top Mark	Package	Packing Method
FAN431AZXA	-25 to +85°C	1%	FAN431A	TO-92 3L	Ammo

### **Block Diagram**




Figure 1. Block Diagram

### **Absolute Maximum Ratings**

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only. Values are at T<sub>A</sub> = 25°C unless otherwise noted.

Symbol	Parameter	Value	Unit
V <sub>KA</sub>	Cathode Voltage	37	V
I <sub>KA</sub>	Cathode current Range (Continuous)	-100 to +150	mA
I <sub>REF</sub>	Reference Input Current Range	-0.05 to +10.00	mA
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient <sup>(1,2)</sup> Z Suffix Package	132	°C/W
P <sub>D</sub>	Power Dissipation <sup>(3,4)</sup> Z Suffix Package	940	mW
TJ	Junction Temperature	150	°C
T <sub>OPR</sub>	Operating Temperature Range	-25 to +85	°C
T <sub>STG</sub>	Storage Temperature Range	-65 to +150	°C

### Notes:

- 1. Thermal resistance test board
  - Size: 1.6 mm x 76.2 mm x 114.3 mm (1S0P)
  - JEDEC Standard: JESD51-3, JESD51-7.
- 2. Assume no ambient airflow.
- 3.  $T_{JMAX}$  = 150 $^{\circ}$ C, Ratings apply to ambient temperature at 25 $^{\circ}$ C. 4. Power dissipation calculation:  $P_D$  = ( $T_J$   $T_A$ ) /  $R_{\theta JA}$ .

### **Recommended Operating Conditions**

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to Absolute Maximum Ratings.

Symbol	Parameter	Min.	Max.	Unit
$V_{KA}$	Cathode Voltage	$V_{REF}$	36	V
I <sub>KA</sub>	Cathode Current	1.0	100	mA

### Electrical Characteristics(5)

Values are at  $T_A = 25$ °C unless otherwise noted.

Symbol	Parameter	Conditions		FAN431A			Unit
Symbol	raiailletei			Min.	Тур.	Max.	Onit
V <sub>REF</sub>	Reference Input Voltage	$V_{KA} = V_{REF}, I_{KA} =$	10 mA	2.470	2.495	2.520	V
$\Delta V_{REF} / \Delta T$	Deviation of Reference Input Voltage Over- Temperature	$V_{KA} = V_{REF}, I_{KA} = T_{MIN} \le T_A \le T_{MAX}$	10 mA,		4.5	17.0	mV
	Ratio of Change in		$\Delta V_{KA} = 10V - V_{REF}$		-1.0	-2.7	
ΔV <sub>REF</sub> / ΔV <sub>KA</sub>	· · <del>-</del> ·	$I_{KA} = 10 \text{ mA}$ $\Delta V_{KA} = 36 \text{ V}$	ΔV <sub>KA</sub> = 36 V - 10 V		-0.5	-2.0	mV/V
I <sub>REF</sub>	Reference Input Current	$I_{KA}$ = 10 mA, $R_1$ = 10 kΩ, $R_2$ = ∞			1.5	4.0	μΑ
$\Delta I_{REF}/\Delta T$	Deviation of Reference Input Current Over Full Temperature Range	I <sub>KA</sub> = 10 mA, R <sub>1</sub> = T <sub>A</sub> = Full Range	10 kΩ, R <sub>2</sub> = ∞,		0.4	1.2	μА
I <sub>KA(MIN)</sub>	Minimum Cathode Current for Regulation	V <sub>KA</sub> = V <sub>REF</sub>			0.45	1.00	mA
I <sub>KA(OFF)</sub>	Off-Stage Cathode Current	V <sub>KA</sub> = 36 V, V <sub>REF</sub>	= 0		0.05	1.00	μА
Z <sub>KA</sub>	Dynamic Impedance	$V_{KA} = V_{REF}$ , $I_{KA} = 1 \text{ to } 100 \text{ mA}$	, f≥1.0 kHz	/	0.15	0.50	Ω

#### Note:

5.  $T_{MIN} = -25^{\circ}C$ ,  $T_{MAX} = +85^{\circ}C$ .

### **Test Circuits**




Figure 2. Test Circuit for V<sub>KA</sub>= V<sub>REF</sub>




Figure 3. Test Circuit for  $V_{KA} \ge V_{REF}$ 




Figure 4. Test Circuit for I<sub>KA(OFF)</sub>

## **Typical Applications**




Figure 5. Shunt Regulator




Figure 6. Output Control for Three-Terminal Fixed Regulator




Figure 7. High-Current Shunt Regulator




Figure 8. Current Limit or Current Source




Figure 9. Constant-Current Sink

### **Typical Performance Characteristics**




Figure 10. Cathode Current vs. Cathode Voltage




Figure 11. Cathode Current vs. Cathode Voltage




Figure 12. OFF-State Cathode Current vs.
Ambient Temperature




Figure 13. Reference Input Current vs.
Ambient Temperature




Figure 14. Frequency vs. Small Signal Voltage Amplification




Figure 15. Pulse Response

### **Typical Performance Characteristics** (Continued)




Figure 16. Stability Boundary Conditions




Figure 17. Anode-Reference Diode Curve




Figure 18. Reference-Cathode Diode Curve






Figure 19. Reference Input Voltage vs. Ambient Temperature

### **Physical Dimensions**





NOTES: UNLESS OTHERWISE SPECIFIED

- DRAWING CONFORMS TO JEDEC MS-013, VARIATION AC. ALL DIMENSIONS ARE IN MILLIMETERS. DRAWING CONFORMS TO ASME Y14.5M-2009. DRAWING FILENAME: MKT-ZAO3FREV3. FAIRCHILD SEMICONDUCTOR.

Figure 20. 3-Lead, TO-92, Molded, 0.200 in Line Spacing Lead Form





#### TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

F-PFS™ AccuPower™ AttitudeEngine™ FRFET<sup>®</sup> Awinda® AX-CAP®\* Global Power Resource SM GreenBridge™

BitSiC™ Green FPS™ Build it Now™ Green FPS™ e-Series™

CorePLUS™ Gmax™ CorePOWER™ GTO™  $CROSSVOLT^{\text{\tiny TM}}$ IntelliMAX™ CTL™ ISOPI ANAR™

Current Transfer Logic™ Making Small Speakers Sound Louder **DEUXPEED**® and Better™

MicroPak2™

Dual Cool™ MegaBuck™ EcoSPARK® MICROCOUPLER™ EfficientMax™ MicroFET™ ESBC™ MicroPak™

MillerDrive™ Fairchild® MotionMax™ Fairchild Semiconductor® MotionGrid® FACT Quiet Series™ MTi<sup>®</sup> FACT® FAST® MTx® MVN® FastvCore™ mWSaver® FETBench™ OptoHiT™ OPTOLOGIC® OPTOPLANAR®

® PowerTrench® PowerXS™

Programmable Active Droop™

**QFET**  $QS^{TM}$ Quiet Series™ RapidConfigure™

Saving our world, 1mW/W/kW at a time™

SignalWise™ SmartMax™ SMART START™

Solutions for Your Success™

STEALTH™ SuperFET<sup>®</sup> SuperSOT™-3 SuperSOT™-6 SuperSOT™-8 SupreMOS<sup>®</sup> SyncFET™ Sync-Lock™

TinyBoost<sup>®</sup> TinyBuck<sup>®</sup> TinyCalc™ TinyLogic<sup>®</sup> TINYOPTO™ TinyPower™ TinyPWM™ TinvWire™ TranSiC™

TriFault Detect™ TRUECURRENT®\* μSerDes™

UHC<sup>®</sup> Ultra FRFET™ UniFET™  $VCX^{TM}$ VisualMax™ VoltagePlus™ XS™ Xsens™ 仙童™

#### DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. TO OBTAIN THE LATEST, MOST UP-TO-DATE DATASHEET AND PRODUCT INFORMATION, VISIT OUR WEBSITE FAIRCHILDSEMI.COM. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

#### LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- 2. A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

#### ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.fairchildsemi.com,

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors

#### PRODUCT STATUS DEFINITIONS

Definition of Terms				
<b>Datasheet Identification</b>	Product Status	Definition		
Advance Information	Formative / In Design	Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.		
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.		
No Identification Needed Full Production Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.				
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.		

Rev. 173

<sup>\*</sup> Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdt/Patent-Marking.pdf">www.onsemi.com/site/pdt/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and exp

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative