

1 DIMENSIONS IN BRACKETS ARE IN INCHES.

2 PRODUCT PROVIDED IN STRIP FORM, BREAKS MAY BE PRESENT.



3 THE $\frac{1.40}{1.27} \left[\frac{.055}{.050} \right]$ DIMENSION MUST BE MAINTAINED BY THE APPLICATOR CUT-OFF TO ENSURE THE PROPER LOCKING FUNCTION OF THE RECEPTACLE.

4 LUBRICANT APPLIED AFTER TIN PLATING

5 STRESS RELIEVED

6 PRELIMINARY – NOT FOR PRODUCTION

7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



SECTION C-C

- | | | | | |
|--|--|---------------------------|---------------|---|
|  OBSOLETE | PRE-TIN | 2.29-3.94 [.090-.155] DIA | [#18-#14] AWG | 63097-5 |
|  OBSOLETE | TIN PLATE | 2.29-3.94 [.090-.155] DIA | [#18-#14] AWG |   63097-4 |
|  OBSOLETE |  TIN 0.002032 [.000080] MIN | 2.29-3.94 [.090-.155] DIA | [#18-#14] AWG | 63097-3 |
| | - | 2.29-3.94 [.090-.155] DIA | [#18-#14] AWG | 63097-2 |
| | TIN PLATE | 2.29-3.94 [.090-.155] DIA | [#18-#14] AWG | 63097-1 |
| | FINISH | INSULATION RANGE | WIRE SIZE | PART NO. |

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 7/28/86 CHK JR RUTH G YETTER 1/15/87 APVD J GILLESPIE 1/15/87 PRODUCT SPEC APPLICATION SPEC 114-2074 WEIGHT -		 TE Connectivity RECEPTACLE, POSITIVE LOCK, .250 SERIES -			
DIMENSIONS: mm [INCHES] 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± ± -		NAME SIZE CAGE CODE DRAWING NO A2 00779 C-63097		RESTRICTED TO -	
MATERIAL BRASS		FINISH SEE TABLE		SCALE 5:1 SHEET 1 OF 1 REV AG			
CUSTOMER DRAWING							