


CKCL44X7R1E103M085AA

Applications		Commercial Grade
Feature		4 in 1 Array
Series	CKCL44(2012) [EIA CC0805]	



Size	
Length(L)	2.00mm +/-0.15mm
Width(W)	1.25mm +/-0.15mm
Thickness(T)	0.85mm +/-0.15mm
Terminal Width(C)	0.25mm Min.
Terminal Spacing(P)	0.50mm Min.

Electrical Characteristics	
Capacitance	10nF +/-20%
Rated Voltage	25Vdc
Temperature Characteristic	X7R(+/-15%)
Dissipation Factor	3% Max.
Insulation Resistance	10000MΩ Min.

Other	
Soldering Method	Reflow
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	4000 Pcs Min.

CKCL44X7R1E103M085AA

Characteristic Graphs

