


SMD Power Inductor CDEP145



Description

- Ferrite core construction.
- Magnetically shielded.
- L × W × H: 14.9 × 14.9 × 6.0 mm Max.
- Product weight: 3.8g(Ref.)
- Moisture Sensitivity Level: 1
- RoHS compliance.

Environmental Data

- Operating temperature range: -40°C~+105°C (including coil's self temperature rise)
- Storage temperature range: -40°C~+105°C
- Solder reflow temperature: 260 °C peak.


Packaging

- Carrier tape and reel packaging
- 13.0" diameter reel
- 500pcs per reel


Applications

- Ideally used in personal computer CPU power supply.


Dimension - [mm]



Land pattern and Schematics - [mm]



SMD Power Inductor CDEP145



Electrical Characteristics

Electrical Characteristics- standard type

PART NO.	STAMP	INDUCTANCE [WITHIN] ※1	D.C.R. (mΩ) [MAX.] (Typ.) (at 20°C)	SATURATION CURRENT (A) ※2		TEMPERATURE RISE CURRENT (A) ※3
				(at 20°C)	(at 105°C)	
CDEP145NP-0R6MC-170	0R6M	0.68 μH ± 20%	1.7(1.4)	30.0	25.6	23.0
CDEP145NP-1R5MC-170	1R5M	1.5 μH ± 20%	3.0(2.5)	19.8	17.0	19.5
CDEP145NP-2R7MC-170	2R7M	2.7 μH ± 20%	4.6(3.8)	15.2	13.0	15.0
CDEP145NP-4R2MC-170	4R2M	4.2 μH ± 20%	7.4(6.2)	12.3	10.6	12.0
CDEP145NP-6R1MC-170	6R1M	6.1 μH ± 20%	10.8(9.0)	10.4	8.8	9.5

Electrical Characteristics- high power type

PART NO.	STAMP	INDUCTANCE [WITHIN] ※1	D.C.R. (mΩ) [MAX.] (Typ.) (at 20°C)	SATURATION CURRENT (A) ※2		TEMPERATURE RISE CURRENT (A) ※3
				(at 20°C)	(at 105°C)	
CDEP145NP-0R5MC-140	0R5M	0.56 μH ± 20%	1.7(1.4)	36.0	31.2	23.0
CDEP145NP-1R2MC-140	1R2M	1.2 μH ± 20%	3.0(2.5)	25.0	20.8	19.5
CDEP145NP-2R2MC-140	2R2M	2.2 μH ± 20%	4.6(3.8)	19.2	16.0	15.0
CDEP145NP-3R5MC-140	3R5M	3.5 μH ± 20%	7.4(6.2)	15.4	13.0	12.0
CDEP145NP-5R0MC-140	5R0M	5.0 μH ± 20%	10.8(9.0)	13.1	10.8	9.5

※1. Measuring condition: at 100kHz.

※2. Saturation current: The value of D.C. current when the inductance decreases to 75% of its nominal value.











※3. Temperature rise current: The value of D.C. current when the temperature rise is Δt=40°C (Ta=20°C).

SMD Power Inductor CDEP145



Saturation Current & Temperature Rise Graph



— L (20°C) — L (105°C) — ΔT



SMD Power Inductor CDEP145



Solder Reflow Condition



Please refer to the sales offices on our website - <http://www.sumida.com>

Hong Kong

Tel. +852-2880-6781
FAX. +852-2565-9600
sales@hk.sumida.com

Saitama(Japan)

Tel. +81-48-691-7300
FAX. +81-48-691-7340
sales@jp.sumida.com

Chicago

Tel. +1-847-545-6700
FAX. +1-847-545-6720
sales@us.sumida.com

Shanghai

Tel. +86-21-5836-3299
FAX. +86-21-5836-3266
shanghai.sales@cn.sumida.com

Seoul

Tel. +82-2-6237-0777
FAX. +82-2-6237-0778
sales@kr.sumida.com

Oberzell

Tel. +49-8591-937-0
FAX. +49-8591-937-103
contact@eu.sumida.com

Shenzhen

Tel. +86-755-8291-0228
FAX. +86-755-8291-0338
shenzhen.sales@cn.sumida.com

Singapore

Tel. +65-6296-3388
FAX. +65-6841-4426
sales@sg.sumida.com

Neumarkt

Tel. +49-9181-4509-110
FAX. +49-9181-4509-310
info@eu.sumida.com

Taipei

Tel. +886-2-8751-2737
FAX. +886-2-8751-2738
sales@tw.sumida.com

San Jose

Tel. +1-408-321-9660
FAX. +1-408-321-9308
sales@us.sumida.com