



FCIconnect.com

Copyright FCI

PRODUCT NO.
SEE TABLE

COMPANY LOGO

R.065 [1.65]
REF

-A-

R.065 [1.65]
REF

-B-

.435±.010 [11.05±0.25]

.002/1

.050 [1.27]

.125±.010 [3.17±0.25]

B2

B1

.155 [3.94]

.100 [2.54]

A1

A2

.100 [2.54]

DIM D

DIM G

DIM E

⌀ .020/.51 M A-B S

OVERALL LENGTH

DIM L

⌀ .020/.51 M A-B S

NOTE 2

.15 [3.8]

NOTE 1

.003/1

.550 [13.97]
REF

.515±.010 [13.08±0.25]

TAIL LENGTH

.192 [4.88] MAX

.162 [4.12] MIN

.025 [0.64]

REF

⌀ .025/0.64 M

AT TIPS

.350 [8.89]
REFMATING LENGTH
.318±.010 [8.08±0.25]

.09 [2.3]

TAIL LENGTH
.177 [4.49]
REF.056 [1.42]
REF.034 [0.86]
2X

⌀ .025±.001 [0.64±0.03]

⌀ .015/.38 M A-B S

AT TIPS

SECTION Y-Y

mat'l. code				surface	tolerance	projection	product family			
				ISO 1302 ✓	ISO 406 ISO 1101		HEADERS			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title			
A	RELEASED	MRC		2/6/91	angles	.XX±.01/.3	VERTICAL 2 ROW GUIDE PIN (SLOTTED)			
B	V20484	JWB		5/14/92	linear	.XXX±.005/.13	HEADER W/SPECIAL RETENTION FEATURE			
C	V50832	MSC		8/08/95	0°±2°	.XXXX±.0020/.051	scale 2:1			
D	M05-0089	MHT		5/26/05	dr	M. CORNMANN	2/6/91	dwg no		
E	M07-0116	AGS		2/25/07	enr	S. AURAND	2/6/91	sheet 1 of 6 size		
					chr	S. AURAND	2/6/91	87253 A3		
					appd	S. AURAND	2/6/91	type Product Customer Drawing		
sheet	revision	E	E	E	E	E	E			
index	sheet	1	2	3	4	5	6			

form: A3

PDM: Rev:E

STATUS Released

Printed: Oct 13, 2010

PRODUCT NO. NOTE 4, 5	SIZE NOTE 4	PLATING REF NOTE 6	KINK POS.
87253-005 THRU 87253-050	2 X 5 THRU 2 X 50	30u"/0.76u Au	NOTE 3
87253-105 THRU 87253-150	2 X 5 THRU 2 X 50	15u"/0.38u Au	NOTE 3
87253-205 THRU 87253-250	2 X 5 THRU 2 X 50	30u"/0.76u GXT OVER 50u"/1.27u Ni	NOTE 3
87253-305 THRU 87253-350	2 X 5 THRU 2 X 50	15u"/0.38u GXT OVER 50u"/1.27u Ni	NOTE 3

NOTES:

- ① MOLDING MATERIAL: 20% MIN GLASS FLLD.
POLYESTER PER UL 94 V-0 COLOR-BLACK.
- ② PIN RETENTION TO BE 3 LBS / 1.36 KG
MIN PER PIN IN EITHER DIRECTION.
- ③ RETENTION FEATURE (KINK) LOCATED
TWO PAIRS EACH END 2X25 AND LARGER.
RETENTION FEATURE (KINK) LOCATED ON
2 PAIR OF PINS IN THE CENTER OF PARTS
SMALLER THAN 2X25.
- ④ -XXX REPRESENTS NO. OF COLUMNS
(i.e. 30u"/0.76u Au 2 x 5 PART IS -005)
-X01 THRU -X04 ARE NOT AVAILABLE,
-X05 THRU -X50 ARE AVAILABLE.
-X51 THRU -X00 ARE NOT AVAILABLE.
- ⑤ ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- ⑥ PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.
- ⑦ THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND
OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
8. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm
MINIMUM THICK CIRCUIT BOARD. SEE APLICATION NOTES/PROCEDURES
IF THEY ARE AVAILABLE.

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HEADERS
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
E					angles .XX±.01/.3	INCH/MM	VERTICAL 2 ROW GUIDE PIN (SLOTTED)
					linear .XXX±.005/.13		HEADER W/SPECIAL RETENTION FEATURE
					0°±2' .XXXX±.0020/.051	scale 2:1	
			dr	M. CORNMAN	2/6/91	FCI	dwg no
			enr	S. AURAND	2/6/91		sheet2 of 6
			chr	S. AURAND	2/6/91		size
			appd	S. AURAND	2/6/91		A3
sheet	revision						type Product Customer Drawing
index	sheet						



FCIconnect.com

Copyright FCI

PRODUCT NO. NOTE 5		SIZE	OVERALL LENGTH DIM L	DIM D	DIM E	DIM G
87253-X01		U N A V A I L A B L E				
	-X02					
	-X03					
	-X04	U N A V A I L A B L E				
	-X05	2 X 5	.88/22.35	.400/10.16	.80/20.32	.77/19.55
	-X06	2 X 6	.98/24.89	.500/12.70	.90/22.86	.87/22.09
	-X07	2 X 7	1.08/27.43	.600/15.24	1.00/25.40	.97/24.63
	-X08	2 X 8	1.18/29.97	.700/17.78	1.10/27.94	1.07/27.17
	-X09	2 X 9	1.28/32.51	.800/20.32	1.20/30.48	1.17/29.71
	-X10	2 X 10	1.38/35.05	.900/22.86	1.30/33.02	1.27/32.25
	-X11	2 X 11	1.48/37.59	1.000/25.40	1.40/35.56	1.37/34.79
	-X12	2 X 12	1.58/40.13	1.100/27.94	1.50/38.10	1.47/37.33
	-X13	2 X 13	1.68/42.67	1.200/30.48	1.60/40.64	1.57/39.87
	-X14	2 X 14	1.78/45.21	1.300/33.02	1.70/43.18	1.67/42.41
	-X15	2 X 15	1.88/47.75	1.400/35.56	1.80/45.72	1.77/44.95
	-X16	2 X 16	1.98/50.29	1.500/38.10	1.90/48.26	1.87/47.49
	-X17	2 X 17	2.08/52.83	1.600/40.64	2.00/50.80	1.97/50.03
	-X18	2 X 18	2.18/55.37	1.700/43.18	2.10/53.34	2.07/52.57
	-X19	2 X 19	2.28/57.91	1.800/45.72	2.20/55.88	2.17/55.11
	-X20	2 X 20	2.38/60.45	1.900/48.26	2.30/58.42	2.27/57.65
	-X21	2 X 21	2.48/62.99	2.000/50.80	2.40/60.96	2.37/60.19
	-X22	2 X 22	2.58/65.53	2.100/53.34	2.50/63.50	2.47/62.73
	-X23	2 X 23	2.68/68.07	2.200/55.88	2.60/66.04	2.57/65.27
	-X24	2 X 24	2.78/70.61	2.300/58.42	2.70/68.58	2.67/67.81
	87253-X25	2 X 25	2.88/73.15	2.400/60.96	2.80/71.12	2.77/70.35

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family HEADERS
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
E					angles	.XX±.01/.3	VERTICAL 2 ROW GUIDE PIN (SLOTTED)
					linear	.XXX±.005/.13	HEADER W/SPECIAL RETENTION FEATURE
					0°±2'	.XXXX±.0020/.051	scale 2:1
					dr	M. CORNMAN 2/6/91	dwg no
					enr	S. AURAND 2/6/91	sheet 3 of 6
					chr	S. AURAND 2/6/91	size A3
					appd	S. AURAND 2/6/91	type Product Customer Drawing
sheet index	revision sheet						



FCIconnect.com

Copyright FCI

PRODUCT NO. NOTE 5		SIZE	OVERALL LENGTH DIM L	DIM D	DIM E	DIM G
87253-X26		2 X 26	2.98/75.69	2.500/63.50	2.90/73.66	2.87/72.89
-X27		2 X 27	3.08/78.23	2.600/66.04	3.00/76.20	2.97/75.43
-X28		2 X 28	3.18/80.77	2.700/68.58	3.10/78.74	3.07/77.97
-X29		2 X 29	3.28/83.31	2.800/71.12	3.20/81.28	3.17/80.51
-X30		2 X 30	3.38/85.85	2.900/73.66	3.30/83.82	3.27/83.05
-X31		2 X 31	3.48/88.39	3.000/76.20	3.40/86.36	3.37/85.59
-X32		2 X 32	3.58/90.93	3.100/78.74	3.50/88.90	3.47/88.13
-X33		2 X 33	3.68/93.47	3.200/81.28	3.60/91.44	3.57/90.67
-X34		2 X 34	3.78/96.01	3.300/83.82	3.70/93.98	3.67/93.21
-X35		2 X 35	3.88/98.55	3.400/86.36	3.80/96.52	3.77/95.75
-X36		2 X 36	3.98/101.09	3.500/88.90	3.90/99.06	3.87/98.29
-X37		2 X 37	4.08/103.63	3.600/91.44	4.00/101.60	3.97/100.83
-X38		2 X 38	4.18/106.17	3.700/93.98	4.10/104.14	4.07/103.37
-X39		2 X 39	4.28/108.71	3.800/96.52	4.20/106.68	4.17/105.91
-X40		2 X 40	4.38/111.25	3.900/99.06	4.30/109.22	4.27/108.45
-X41		2 X 41	4.48/113.79	4.000/101.60	4.40/111.76	4.37/110.99
-X42		2 X 42	4.58/116.33	4.100/104.14	4.50/114.30	4.47/113.53
-X43		2 X 43	4.68/118.87	4.200/106.68	4.60/116.84	4.57/116.07
-X44		2 X 44	4.78/121.41	4.300/109.22	4.70/119.38	4.67/118.61
-X45		2 X 45	4.88/123.95	4.400/111.76	4.80/121.92	4.77/121.15
-X46		2 X 46	4.98/126.49	4.500/114.30	4.90/124.46	4.87/123.69
-X47		2 X 47	5.08/129.03	4.600/116.84	5.00/127.00	4.97/126.23
-X48		2 X 48	5.18/131.57	4.700/119.38	5.10/129.54	5.07/128.77
-X49		2 X 49	5.28/134.11	4.800/121.92	5.20/132.08	5.17/131.31
87253-X50		2 X 50	5.38/136.65	4.900/124.46	5.30/134.62	5.27/133.85

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family HEADERS
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
E					angles .XX±.01/.3	INCH/MM	VERTICAL 2 ROW GUIDE PIN (SLOTTED)
					linear .XXX±.005/.13		HEADER W/SPECIAL RETENTION FEATURE
					0°±2' .XXXX±.0020/.051	scale 2:1	
					dr M. CORNMAN 2/6/91		dwg no
					enr S. AURAND 2/6/91		sheet 4 of 6
					chr S. AURAND 2/6/91		size A3
					appd S. AURAND 2/6/91		
sheet index	revision sheet						type Product Customer Drawing

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NO.	SIZE	DIM L	DIM D	DIM E	DIM G
87253-X51		D I S C O N T I N U E D			
-X52		D I S C O N T I N U E D			
-X53		D I S C O N T I N U E D			
-X54		D I S C O N T I N U E D			
-X55		D I S C O N T I N U E D			
-X56		D I S C O N T I N U E D			
-X57		D I S C O N T I N U E D			
-X58		D I S C O N T I N U E D			
-X59		D I S C O N T I N U E D			
-X60		D I S C O N T I N U E D			
-X61		D I S C O N T I N U E D			
-X62		D I S C O N T I N U E D			
-X63		D I S C O N T I N U E D			
-X64		D I S C O N T I N U E D			
-X65		D I S C O N T I N U E D			
-X66		D I S C O N T I N U E D			
-X67		D I S C O N T I N U E D			
-X68		D I S C O N T I N U E D			
-X69		D I S C O N T I N U E D			
-X70		D I S C O N T I N U E D			
-X71		D I S C O N T I N U E D			
-X72		D I S C O N T I N U E D			
-X73		D I S C O N T I N U E D			
-X74		D I S C O N T I N U E D			
87253-X75		D I S C O N T I N U E D			

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HEADERS	
ltr	ecn no	dr	date	tolerances unless otherwise specified					
E				angles	linear		.XX±.01/.3		INCH/MM
				0°±2'			.XXX±.005/.13		
							.XXXX±.0020/.051		scale 2:1
				dr	M. CORNMAN	2/6/91			
				enr	S. AURAND	2/6/91			
				chr	S. AURAND	2/6/91			
				appd	S. AURAND	2/6/91			
sheet index	revision sheet								

title		VERTICAL 2 ROW GUIDE PIN (SLOTTED)	
HEADER W/SPECIAL RETENTION FEATURE			
dwg no	87253	sheet 5 of 6	size A3
type	Product Customer Drawing		

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NO.	SIZE	DIM L	DIM D	DIM E	DIM G
87253-X76		D I S C O N T I N U E D			
-X77		D I S C O N T I N U E D			
-X78		D I S C O N T I N U E D			
-X79		D I S C O N T I N U E D			
-X80		D I S C O N T I N U E D			
-X81		D I S C O N T I N U E D			
-X82		D I S C O N T I N U E D			
-X83		D I S C O N T I N U E D			
-X84		D I S C O N T I N U E D			
-X85		D I S C O N T I N U E D			
-X86		D I S C O N T I N U E D			
-X87		D I S C O N T I N U E D			
-X88		D I S C O N T I N U E D			
-X89		D I S C O N T I N U E D			
-X90		D I S C O N T I N U E D			
-X91		D I S C O N T I N U E D			
-X92		D I S C O N T I N U E D			
-X93		D I S C O N T I N U E D			
-X94		D I S C O N T I N U E D			
-X95		D I S C O N T I N U E D			
-X96		D I S C O N T I N U E D			
-X97		D I S C O N T I N U E D			
-X98		D I S C O N T I N U E D			
-X99		D I S C O N T I N U E D			
87253-X00		D I S C O N T I N U E D			

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family HEADERS
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
E					angles	.XX±.01/.3	VERTICAL 2 ROW GUIDE PIN (SLOTTED)
					linear	.XXX±.005/.13	HEADER W/SPECIAL RETENTION FEATURE
					0°±2'	.XXXX±.0020/.051	scale 2:1
					dr	M. CORNMAN 2/6/91	dwg no
					enr	S. AURAND 2/6/91	sheet6 of 6 size
					chr	S. AURAND 2/6/91	87253 A3
					appd	S. AURAND 2/6/91	type Product Customer Drawing
sheet index	revision sheet						

form: A3