


PART
NAME

UTILIBOX (STYLE D)

PART
No.

CU-742 & CU-744

MATERIAL: HIGH-IMPACT POLYSTYRENECOLOR: BLACKFINISH: SMOOTH, MATTEFOUR (4) #4 x 0.562" LG. SCREWS
SUPPLIED FOR ASSEMBLY.NOTE: ALL DIMENSIONS HAVE ± 0.010 TOLERANCE
UNLESS OTHERWISE SPECIFIED.

PART No.	A	B
CU-742	1.000	0.900
CU-744	1.600	1.500

PART
NAME




PLASTIBOX (STYLE A)

PART
No.

PT-11284 & PS-11285

MATERIAL: HIGH-IMPACT ABSCOLOR: BLACK OR GRAYFINISH: PREFIX PS- TEXTURED BODY WITH SMOOTH TOP INSERT.
PREFIX PT- TEXTURED BODY WITH TEXTURED TOP.SIX (6) #4 x 0.375" LG. SCREWS
SUPPLIED FOR ASSEMBLING TOP.

FOUR (4) NON-SKID PUSH-ON FEET SUPPLIED.

MOUNTING BOSSES USE EITHER M2.5 METRIC
OR #4 STD. SHEET METAL SCREWS
x 0.188" LG. (NOT SUPPLIED)*-USABLE AREA ON COVER ALSO
AVAILABLE FOR CUSTOM MOLDING.NOTE: ALL DIMENSIONS HAVE ± 0.015 TOLERANCE
UNLESS OTHERWISE SPECIFIED.MOUNTING BOSSES USE EITHER M2.5 METRIC
OR #4 STD. SHEET METAL SCREWS
x 0.250" LG. (NOT SUPPLIED)