


REVISIONS				DOC. NO. SPC-FD04, Total Pages: 2 Effective: 7/15/97. DCP No: 229 Supersedes DCP No: 103					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
136	A	Released	J.W.M.	12/22/97	J.C.	1/12/98	B.B.	1/12/98	



NOTES:

Bare Part:

1. Material: Nylon insulated copper
2. Finish: Electro-Tin Plate
3. Butted Seam

Tubing:

1. Multiple wall polyolefin
2. Meltable, integral inner wall
3. 275° F (135°C) Shrink temperature
4. -67°F (-55°C) to 230°F (110°C) Cont. Operating Temperature
5. Tensile strength: 2200 PSI
6. Ultimate elongation: 500%
7. Secant modulus, 2%: 27,000 PSI
8. Specific Gravity: 1.00 Max
9. Longitudinal Change: 5%
10. Dielectric Strength: 1000 V/Mil
11. Volume Resistivity: 10^{15} Ohm-cm
12. Non-corrosive
13. Water absorption: <0.1%
14. Tubing Color: Red
15. Packs of 25

SPC-FD04-DWG

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

Unless Otherwise Specified: Dimensions are shown for reference only!	DRAWN BY:	DATE:	DRAWING TITLE:			
	Jeff McVicker	12/22/97	Fully Insulated Quick Disconnect (Male)			
	CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE	REV
	JOHN COLE	1/12/98	A	1674	92N3595.dwg	A
	APPROVED BY:	DATE:	SCALE: NTS		U.O.M.: INCHES [mm]	SHEET: 1 OF 1
	BRETT BRAATZ	1/12/98				