


Xinger®



Ultra Low Profile 0404 Balun 50Ω to 100Ω Balanced

Description

The BD1416N50100AHF is a low profile sub-miniature unbalanced to balanced transformer designed for differential inputs and output locations on modern chipsets specifically in the GPS, GLONASS, WiMAX 1.5 (legacy TDM) and US DVB-H space and in an easy to use surface mount package. The BD1416N50100AHF is ideal for high volume manufacturing and delivers higher performance than traditional ceramic baluns. The BD1416N50100AHF has an unbalanced port impedance of 50Ω and a 50Ω balanced port impedance. This transformation enables single ended signals to be applied to differential ports on modern integrated chipsets. The output ports have equal amplitude (-3dB) with 180 degree phase differential. The BD1416N50100AHF is available on tape and reel for pick and place high volume manufacturing.

Detailed Electrical Specifications: Specifications subject to change without notice.


Features:

- 1400 – 1600 MHz
- 0.57 mm Height Profile
- 50 Ohm to 2 x 50 Ohm
- Low Insertion Loss
- Class Leading CMRR
- Targeted At GPS, GLONASS, WiMAX 1.5 (legacy TDM) & US DVB-H Markets
- Surface Mountable
- Tape & Reel
- Non-Conductive Top Surface
- RoHS Compliant
- Halogen Free


Parameter	ROOM (25°C)			Unit
	Min.	Typ.	Max	
Frequency	1400		1600	MHz
Unbalanced Port Impedance		50		Ω
Balanced Port Impedance		100		Ω
Return Loss	14	18		dB
Insertion Loss*		0.7	0.9	dB
Amplitude Balance		0.8	1.2	dB
Phase Balance		4	9	Degrees
CMRR		26		dB
Power Handling @85C			0.75	Watts
Power Handling @105C			0.45	Watts
Operating Temperature	-55		+105	°C

* Insertion Loss stated at room temperature (Insertion Loss is approximately 0.1 dB higher at +85 °C) Outline Drawing


Top View (Near-side)



Side View



Bottom View (Far-side)




Dimensions are in Millimeters
Mechanical Outline

Pin	Designation
1	GND / DC Feed + RF GND
2	Unbalanced Port
3	Balanced Port
4	Balanced Port


Tolerances are Non-Cumulative

Typical Performance: 1300 MHz. to 1700 MHz.


Insertion Loss




Return Loss-Input




Amplitude Balance



Phase Balance




CMRR




Wide Band Performance: 10 MHz. to 8010 MHz.


Insertion Loss




Return Loss-Input




Amplitude Balance



Phase Balance



CMRR




Mounting Configuration:

In order for Xinger surface mount components to work optimally, the proper impedance transmission lines must be used to connect to the RF ports. If this condition is not satisfied, insertion loss, Isolation and VSWR may not meet published specifications.


All of the Xinger components are constructed from organic PTFE based composites which possess excellent electrical and mechanical stability. Xinger components are compliant to a variety of ROHS and Green standards and ready for Pb-free soldering processes. Pads are Gold plated with a Nickel barrier.

An example of the PCB footprint used in the testing of these parts is shown below. In specific designs, the transmission line widths need to be adjusted to the unique dielectric coefficients and thicknesses as well as varying pick and place equipment tolerances.



Packaging and Ordering Information

Parts are available in reel and are packaged per EIA 481-D. Parts are oriented in tape and reel as shown below. Minimum order quantities are 4000 per reel.



Direction of
Part Feed
(Unloading)





TABLE 1		
QUANTITY/REEL	REEL DIMENSIONS mm	
4000	øA	177.80
	B	8.00
	øC	50.80
	øD	13.00