

Header - PTSM 0,5/ 5-HH0-2,5-SMD R32 - 1808226

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Header, Nominal current: 6 A, Rated voltage (III/2): 160 V, Number of positions: 5, Pitch: 2.5 mm, Color: black, Contact surface: Tin, Assembly: SMD/THT/THR



Key commercial data

Packing unit	1 pc
Minimum order quantity	600 pc
Weight per Piece (excluding packing)	1.57 GRM
Custom tariff number	85369010
Country of origin	Germany

Technical data

Dimensions

Length	7.5 mm
Height	5 mm
Pitch	2.5 mm
Dimension a	10 mm

General

Range of articles	PTSM 0,5/...-HH-SMD
Insulating material group	IIIa
Rated surge voltage (III/3)	2.5 kV
Rated surge voltage (III/2)	2.5 kV
Rated surge voltage (II/2)	2.5 kV
Rated voltage (III/3)	50 V
Rated voltage (III/2)	160 V
Rated voltage (II/2)	160 V
Connection in acc. with standard	EN-VDE

Header - PTSM 0,5/ 5-HH0-2,5-SMD R32 - 1808226

Technical data

General

Nominal current I_N	6 A
Maximum load current	6 A
Insulating material	LCP
Inflammability class according to UL 94	V0
Color	black
Number of positions	5

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27141190
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

GOST / UL Recognized / UL Recognized

Header - PTSM 0,5/ 5-HH0-2,5-SMD R32 - 1808226

Approvals

Ex Approvals

Approvals submitted

Approval details

GOST

UL Recognized


	B
Nominal current IN	5 A
Nominal voltage UN	150 V

UL Recognized

	B
Nominal current IN	5 A
Nominal voltage UN	150 V

Drawings

Drilling diagram



Dimensioned drawing

