



### FEATURES:

- Alligator Test Adapter has been designed to IEC 1010, which is the latest International Safety Standard.
- Snaps onto Pomona's DMM Probes with .080" (2 mm) O.D. Tips.
- Pin tip jack at the adapter end is recessed for added insulation protection
- Adapter converts a DMM probe tip to alligators for ease of testing.
- Medium Alligator features a jaw opening of up to 0.30" (8 mm).

### MATERIALS:

Body: Steel, Nickel Plated

Insulation: Polypropylene, Fire Retardant, UL94 V-2 Rated, Color: One Red, One Black

Spring: Music Wire

### RATING:

IEC 1010-2-031, Category II, P2 Compliant

Operating Voltage: 300 VRMS/DC

Current: 5 Amperes.

### ORDERING INFORMATION: Model 6264-\*

\* = Color, -0 Black, -2 Red

Alligator Adapter is also included in many of Pomona's DMM Test Kits.

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02$ " (.51 mm), .xxx =  $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[6264-0](#) [6264-2](#) [6264-02](#)