

Surface Mount Multilayer Ceramic Chip Capacitors for High Frequency



FEATURES

- Case size 0402, 0603, 0805
- High frequency
- Ultra-stable dielectric material
- Non-magnetic copper termination "C"
- Lead (Pb)-free terminations code "X"
- Tin/lead termination code "L"
- Surface mount, wet build process
- Reliable Noble Metal Electrode (NME) system
- Made with a combination of design, materials and tight process control to achieve very high field reliability
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



Available
RoHS*
Available
HALOGEN
FREE
GREEN
(5-2008)
Available

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details.

APPLICATIONS

- RF and microwave
- Broadband communication
- Satellite communication
- Base stations
- Medical instrumentation and test
- Military devices (radar, communication, etc.)
- Wireless devices

ELECTRICAL SPECIFICATIONS

Note

- Electrical characteristics at 25 °C unless otherwise specified

Operating Temperature: -55 °C to +125 °C

Capacitance Range:

0402: 0.1 pF to 82 pF

0603: 0.1 pF to 470 pF

0805: 0.1 pF to 1.5 nF

Voltage Rating: 25 V_{DC} to 250 V_{DC}

Temperature Coefficient of Capacitance (TCC):

C0G (D): 0 ppm/°C ± 30 ppm/°C from -55 °C to +125 °C with zero (0) V_{DC} applied

Dissipation Factor (DF):

C0G (D): 0.05 % max. at 1.0 V_{RMS} and 1 MHz
for values ≤ 1000 pF

C0G (D): 0.05 % max. at 1.0 V_{RMS} and 1 kHz
for values > 1000 pF

Aging Rate: 0 % maximum per decade

Insulation Resistance (IR):

at +25 °C and rated voltage 100 000 MΩ minimum or 1000 ΩF, whichever is less

at +125 °C and rated voltage 10 000 MΩ minimum or 100 ΩF, whichever is less

Dielectric Strength Test:

performed per method 103 of EIA-198-2-E.

Applied test voltages:

≤ 200 V_{DC}-rated: min. 250 % of rated voltage

> 200 V_{DC}-rated: min. 200 % of rated voltage

QUICK REFERENCE DATA

DIELECTRIC	CASE	MAXIMUM VOLTAGE (V)	CAPACITANCE	
			MINIMUM	MAXIMUM
D = HIFREQ	0402	200	0.1 pF	82 pF
	0603	250	0.1 pF	470 pF
	0805	250	0.1 pF	1.5 nF

Note

- For values below 0.4 pF, contact mlccrf@vishay.com

ORDERING INFORMATION

VJ0603	D	1R0	B	X	B	A	C
CASE CODE	DIELECTRIC	CAPACITANCE NOMINAL CODE	CAPACITANCE TOLERANCE	TERMINATION	DC VOLTAGE RATING ⁽¹⁾	MARKING	PACKAGING
0402 0603 0805	D = HIFREQ	Expressed in picofarads (pF). The first two digits are significant, the third is a multiplier. An "R" indicates a decimal point. Examples: 1R0 = 1.0 pF	V = ± 0.05 pF B = ± 0.10 pF C = ± 0.25 pF D = ± 0.50 pF F = ± 1 % G = ± 2 % J = ± 5 % K = ± 10 % M = ± 20 % Note Details see "Selection Chart"	C = non-magnetic copper barrier 100 % tin plate matte finish E = AgPd ⁽²⁾ X = Ni barrier 100 % tin plate matte finish L = Ni barrier with tin lead plated finish min. 4 % lead	X = 25 V A = 50 V B = 100 V C = 200 V P = 250 V	A = no marking	T = 7" reel/plastic tape C = 7" reel/paper tape O = 7" reel/flamed paper tape J = 7" reel (low quantity) R = 11 1/4"/13" reel/plastic tape P = 11 1/4"/13" reel/paper tape I = 11 1/4"/13" reel/flamed paper tape B = bulk Note "I" and "O" is used for "E"/"N" termination code


Notes

- DC voltage rating should not be exceeded in application
- Termination code "E" is for conductive epoxy assembly

ENVIRONMENTAL STATUS

TERMINATION CODE	TERMINATION DESCRIPTION	RoHS COMPLIANT	VISHAY GREEN
C	Non-magnetic copper barrier 100 % tin plated matte finish	Yes	Yes
X	Ni barrier 100 % tin plated matte finish	Yes	Yes
E	AgPd	Yes	Yes
L	Ni barrier 100 % tin plated matte finish min. 4 % lead	No	No

DIMENSIONS in inches (millimeters)



CASE CODE	STYLE	LENGTH (L)	WIDTH (W)	MAXIMUM THICKNESS (T)	TERMINATIONS PAD (P)	
					MINIMUM	MAXIMUM ⁽¹⁾
0402	VJ0402	0.040 $\pm$ 0.004 (1.02 $\pm$ 0.10)	0.020 $\pm$ 0.004 (0.51 $\pm$ 0.10)	0.021 (0.61)	0.004 (0.10)	0.016 (0.41)
0603	VJ0603	0.063 $\pm$ 0.006 (1.60 $\pm$ 0.15)	0.031 $\pm$ 0.005 (0.80 $\pm$ 0.12)	0.037 (0.94)	0.012 (0.30)	0.018 (0.46)
0805	VJ0805	0.079 $\pm$ 0.008 (2.00 $\pm$ 0.20)	0.049 $\pm$ 0.008 (1.25 $\pm$ 0.20)	0.057 (1.45)	0.010 (0.25)	0.028 (0.71)

Note

- For Cu termination "C" add 0.01 mm to maximum pad terminations



SELECTION CHART						
DIELECTRIC (VISHAY CODE)		C0G (D)				TOLERANCE
STYLE		VJ0402				
CASE CODE		0402				
VOLTAGE (V _{DC})		25	50	100	200	
VOLTAGE CODE		X	A	B	C	
CAP. CODE	CAP.					
0R1	0.1 pF	..	..	..	..	V, B, C, D ⁽¹⁾
0R2	0.2 pF	..	..	..	..	V, B, C, D ⁽¹⁾
0R3	0.3 pF	..	..	..	..	V, B, C, D ⁽¹⁾
0R4	0.4 pF	..	..	..	..	V, B, C, D
0R5	0.5 pF	..	..	..	..	V, B, C, D
0R6	0.6 pF	..	..	..	..	V, B, C, D
0R7	0.7 pF	..	..	..	..	V, B, C, D
0R8	0.8 pF	..	..	..	..	V, B, C, D
0R9	0.9 pF	..	..	..	..	V, B, C, D
1R0	1.0 pF	..	..	..	..	V, B, C, D
1R1	1.1 pF	..	..	..	..	B, C, D
1R2	1.2 pF	..	..	..	..	B, C, D
1R3	1.3 pF	..	..	..	..	B, C, D
1R4	1.4 pF	..	..	..	..	B, C, D
1R5	1.5 pF	..	..	..	..	B, C, D
1R6	1.6 pF	..	..	..	..	B, C, D
1R7	1.7 pF	..	..	..	..	B, C, D
1R8	1.8 pF	..	..	..	..	B, C, D
1R9	1.9 pF	..	..	..	..	B, C, D
2R0	2.0 pF	..	..	..	..	B, C, D
2R1	2.1 pF	..	..	..	..	B, C, D
2R2	2.2 pF	..	..	..	..	B, C, D
2R4	2.4 pF	..	..	..	..	B, C, D
2R7	2.7 pF	..	..	..	..	B, C, D
3R0	3.0 pF	..	..	..	..	B, C, D
3R3	3.3 pF	..	..	..	..	B, C, D
3R6	3.6 pF	..	..	..	..	B, C, D
3R9	3.9 pF	..	..	..	..	B, C, D
4R3	4.3 pF	..	..	..	..	B, C, D
4R7	4.7 pF	..	..	..	..	B, C, D
5R1	5.1 pF	..	..	..	..	B, C, D
5R6	5.6 pF	..	..	..	..	B, C, D
6R2	6.2 pF	..	..	..	..	B, C, D
6R8	6.8 pF	..	..	..	..	B, C, D
7R5	7.5 pF	..	..	..	..	B, C, D
8R2	8.2 pF	..	..	..	..	B, C, D
9R1	9.1 pF	..	..	..	..	B, C, D
100	10 pF	..	..	..	..	F, G, J, K, M
110	11 pF	..	..	..	..	F, G, J, K, M
120	12 pF	..	..	..	..	F, G, J, K, M
130	13 pF	..	..	..	..	F, G, J, K, M
150	15 pF	..	..	..	..	F, G, J, K, M
180	18 pF	..	..	..	..	F, G, J, K, M
200	20 pF	..	..	..	..	F, G, J, K, M
220	22 pF	..	..	..	..	F, G, J, K, M
240	24 pF	..	..	..	..	F, G, J, K, M
270	27 pF	..	..	..	..	F, G, J, K, M
300	30 pF	..	..			F, G, J, K, M
330	33 pF	..	..			F, G, J, K, M
360	36 pF	..	..			F, G, J, K, M
390	39 pF	..	..			F, G, J, K, M
430	43 pF	..	..			F, G, J, K, M
470	47 pF	..	..			F, G, J, K, M
510	51 pF	..	..			F, G, J, K, M
560	56 pF	..	..			F, G, J, K, M
620	62 pF	..				F, G, J, K, M
680	68 pF	..				F, G, J, K, M
750	75 pF	..				F, G, J, K, M
820	82 pF	..				F, G, J, K, M
910	91 pF					
101	100 pF					
111	110 pF					
121	120 pF					

Notes

RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"

.. Paper carrier

⁽¹⁾ For values below 0.4 pF and tolerance ± 0.05 pF, contact mlccrf@vishay.com



SELECTION CHART							
DIELECTRIC (VISHAY CODE)		C0G (D)					TOLERANCE
STYLE		VJ0603					
CASE CODE		0603					
VOLTAGE (V _{DC})		25	50	100	200	250	
VOLTAGE CODE		X	A	B	C	P	
CAP. CODE	CAP.						
0R1	0.1 pF	••	••	••	••	••	V, B, C, D ⁽¹⁾
0R2	0.2 pF	••	••	••	••	••	V, B, C, D ⁽¹⁾
0R3	0.3 pF	••	••	••	••	••	V, B, C, D ⁽¹⁾
0R4	0.4 pF	••	••	••	••	••	V, B, C, D
0R5	0.5 pF	••	••	••	••	••	V, B, C, D
0R6	0.6 pF	••	••	••	••	••	V, B, C, D
0R7	0.7 pF	••	••	••	••	••	V, B, C, D
0R8	0.8 pF	••	••	••	••	••	V, B, C, D
0R9	0.9 pF	••	••	••	••	••	V, B, C, D
1R0	1.0 pF	••	••	••	••	••	B, C, D
1R1	1.1 pF	••	••	••	••	••	B, C, D
1R2	1.2 pF	••	••	••	••	••	B, C, D
1R3	1.3 pF	••	••	••	••	••	B, C, D
1R4	1.4 pF	••	••	••	••	••	B, C, D
1R5	1.5 pF	••	••	••	••	••	B, C, D
1R6	1.6 pF	••	••	••	••	••	B, C, D
1R7	1.7 pF	••	••	••	••	••	B, C, D
1R8	1.8 pF	••	••	••	••	••	B, C, D
1R9	1.9 pF	••	••	••	••	••	B, C, D
2R0	2.0 pF	••	••	••	••	••	B, C, D
2R1	2.1 pF	••	••	••	••	••	B, C, D
2R2	2.2 pF	••	••	••	••	••	B, C, D
2R4	2.4 pF	••	••	••	••	••	B, C, D
2R7	2.7 pF	••	••	••	••	••	B, C, D
3R0	3.0 pF	••	••	••	••	••	B, C, D
3R3	3.3 pF	••	••	••	••	••	B, C, D
3R6	3.6 pF	••	••	••	••	••	B, C, D
3R9	3.9 pF	••	••	••	••	••	B, C, D
4R3	4.3 pF	••	••	••	••	••	B, C, D
4R7	4.7 pF	••	••	••	••	••	B, C, D
5R1	5.1 pF	••	••	••	••	••	B, C, D
5R6	5.6 pF	••	••	••	••	••	B, C, D
6R2	6.2 pF	••	••	••	••	••	B, C, D
6R8	6.8 pF	••	••	••	••	••	B, C, D
7R5	7.5 pF	••	••	••	••	••	B, C, D
8R2	8.2 pF	••	••	••	••	••	B, C, D
9R1	9.1 pF	••	••	••	••	••	B, C, D
100	10 pF	••	••	••	••	••	F, G, J, K, M
110	11 pF	••	••	••	••	••	F, G, J, K, M
120	12 pF	••	••	••	••	••	F, G, J, K, M
130	13 pF	••	••	••	••	••	F, G, J, K, M
150	15 pF	••	••	••	••	••	F, G, J, K, M
180	18 pF	••	••	••	••	••	F, G, J, K, M
200	20 pF	••	••	••	••	••	F, G, J, K, M
220	22 pF	••	••	••	••	••	F, G, J, K, M
240	24 pF	••	••	••	••	••	F, G, J, K, M
270	27 pF	••	••	••	••	••	F, G, J, K, M
300	30 pF	••	••	••	••	••	F, G, J, K, M
330	33 pF	••	••	••	••	••	F, G, J, K, M
360	36 pF	••	••	••	••	••	F, G, J, K, M
390	39 pF	••	••	••	••	••	F, G, J, K, M
430	43 pF	••	••	••	••	••	F, G, J, K, M
470	47 pF	••	••	••	••	••	F, G, J, K, M
510	51 pF	••	••	••	••	••	F, G, J, K, M
560	56 pF	••	••	••	••	••	F, G, J, K, M
620	62 pF	•	•	•	•	•	F, G, J, K, M
680	68 pF	•	•	•	•	•	F, G, J, K, M
750	75 pF	•	•	•	•	•	F, G, J, K, M
820	82 pF	•	•	•	•	•	F, G, J, K, M
910	91 pF	•	•	•	•	•	F, G, J, K, M

Notes

• RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"

•• Paper carrier • Plastic carrier tape

⁽¹⁾ For values below 0.4 pF and tolerance ± 0.05 pF, contact mlccrf@vishay.com



SELECTION CHART							
DIELECTRIC (VISHAY CODE)		C0G (D)					TOLERANCE
STYLE		VJ0603					
CASE CODE		0603					
VOLTAGE (V _{DC})		25	50	100	200	250	
VOLTAGE CODE		X	A	B	C	P	
CAP. CODE	CAP.						
101	100 pF	•	•	•	•	•	F, G, J, K, M
111	110 pF	•	•	•			F, G, J, K, M
121	120 pF	•	•	•			F, G, J, K, M
131	130 pF	•	•	•			F, G, J, K, M
151	150 pF	•	•	•			F, G, J, K, M
181	180 pF	•	•				F, G, J, K, M
201	200 pF	•	•				F, G, J, K, M
221	220 pF	•	•				F, G, J, K, M
241	240 pF	•	•				F, G, J, K, M
271	270 pF	•	•				F, G, J, K, M
301	300 pF	•	•				F, G, J, K, M
331	330 pF	•	•				F, G, J, K, M
361	360 pF	•					F, G, J, K, M
391	390 pF	•					F, G, J, K, M
431	430 pF	•					F, G, J, K, M
471	470 pF	•					F, G, J, K, M
511	510 pF						
561	560 pF						
621	620 pF						
681	680 pF						
751	750 pF						
821	820 pF						
911	910 pF						
102	1.0 nF						
112	1.1 nF						
122	1.2 nF						
132	1.3 nF						
152	1.5 nF						
182	1.8 nF						

Notes

• RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"

• Paper carrier • Plastic carrier tape

(1) For values below 0.4 pF and tolerance ± 0.05 pF, contact mlccrf@vishay.com



SELECTION CHART							
DIELECTRIC (VISHAY CODE)		C0G (D)					TOLERANCE
STYLE		VJ0805					
CASE CODE		0805					
VOLTAGE (V _{DC})		25	50	100	200	250	
VOLTAGE CODE		X	A	B	C	P	
CAP. CODE	CAP.						
0R1	0.1 pF	••	••	••	••	••	V, B, C, D ⁽¹⁾
0R2	0.2 pF	••	••	••	••	••	V, B, C, D ⁽¹⁾
0R3	0.3 pF	••	••	••	••	••	V, B, C, D ⁽¹⁾
0R4	0.4 pF	••	••	••	••	••	V, B, C, D
0R5	0.5 pF	••	••	••	••	••	V, B, C, D
0R6	0.6 pF	••	••	••	••	••	V, B, C, D
0R7	0.7 pF	••	••	••	••	••	V, B, C, D
0R8	0.8 pF	••	••	••	••	••	V, B, C, D
0R9	0.9 pF	••	••	••	••	••	V, B, C, D
1R0	1.0 pF	••	••	••	••	••	B, C, D
1R1	1.1 pF	••	••	••	••	••	B, C, D
1R2	1.2 pF	••	••	••	••	••	B, C, D
1R3	1.3 pF	••	••	••	••	••	B, C, D
1R4	1.4 pF	••	••	••	••	••	B, C, D
1R5	1.5 pF	••	••	••	••	••	B, C, D
1R6	1.6 pF	••	••	••	••	••	B, C, D
1R7	1.7 pF	••	••	••	••	••	B, C, D
1R8	1.8 pF	••	••	••	••	••	B, C, D
1R9	1.9 pF	••	••	••	••	••	B, C, D
2R0	2.0 pF	••	••	••	••	••	B, C, D
2R1	2.1 pF	••	••	••	••	••	B, C, D
2R2	2.2 pF	••	••	••	••	••	B, C, D
2R4	2.4 pF	••	••	••	••	••	B, C, D
2R7	2.7 pF	••	••	••	••	••	B, C, D
3R0	3.0 pF	••	••	••	••	••	B, C, D
3R3	3.3 pF	••	••	••	••	••	B, C, D
3R6	3.6 pF	••	••	••	••	••	B, C, D
3R9	3.9 pF	••	••	••	••	••	B, C, D
4R3	4.3 pF	••	••	••	••	••	B, C, D
4R7	4.7 pF	••	••	••	••	••	B, C, D
5R1	5.1 pF	••	••	••	••	••	B, C, D
5R6	5.6 pF	••	••	••	••	••	B, C, D
6R2	6.2 pF	••	••	••	••	••	B, C, D
6R8	6.8 pF	••	••	••	••	••	B, C, D
7R5	7.5 pF	••	••	••	••	••	B, C, D
8R2	8.2 pF	••	••	••	••	••	B, C, D
9R1	9.1 pF	••	••	••	••	••	B, C, D

Notes

•• RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"

•• Paper carrier • Plastic carrier tape

⁽¹⁾ For values below 0.4 pF and tolerance ± 0.05 pF, contact mlccrf@vishay.com



SELECTION CHART							
DIELECTRIC (VISHAY CODE)		C0G (D)					TOLERANCE
STYLE		VJ0805					
CASE CODE		0805					
VOLTAGE (V _{DC})		25	50	100	200	250	
VOLTAGE CODE		X	A	B	C	P	
CAP. CODE	CAP.						
100	10 pF	••	••	••	••	••	F, G, J, K, M
110	11 pF	••	••	••	••	••	F, G, J, K, M
120	12 pF	••	••	••	••	••	F, G, J, K, M
130	13 pF	••	••	••	••	••	F, G, J, K, M
150	15 pF	••	••	••	••	••	F, G, J, K, M
180	18 pF	••	••	••	••	••	F, G, J, K, M
200	20 pF	••	••	••	••	••	F, G, J, K, M
220	22 pF	••	••	••	••	••	F, G, J, K, M
240	24 pF	••	••	••	••	••	F, G, J, K, M
270	27 pF	••	••	••	••	••	F, G, J, K, M
300	30 pF	••	••	••	••	••	F, G, J, K, M
330	33 pF	••	••	••	••	••	F, G, J, K, M
360	36 pF	••	••	••	••	••	F, G, J, K, M
390	39 pF	••	••	••	••	••	F, G, J, K, M
430	43 pF	••	••	••	••	••	F, G, J, K, M
470	47 pF	••	••	••	••	••	F, G, J, K, M
510	51 pF	••	••	••	••	••	F, G, J, K, M
560	56 pF	••	••	••	••	••	F, G, J, K, M
620	62 pF	••	••	••	••	••	F, G, J, K, M
680	68 pF	••	••	••	••	••	F, G, J, K, M
750	75 pF	••	••	••	••	••	F, G, J, K, M
820	82 pF	••	••	••	••	••	F, G, J, K, M
910	91 pF	••	••	••	••	••	F, G, J, K, M
101	100 pF	•	•	•	•	•	F, G, J, K, M
111	110 pF	•	•	•	•	•	F, G, J, K, M
121	120 pF	•	•	•	•	•	F, G, J, K, M
131	130 pF	•	•	•	•	•	F, G, J, K, M
151	150 pF	•	•	•	•	•	F, G, J, K, M
181	180 pF	•	•	•	•	•	F, G, J, K, M
201	200 pF	•	•	•	•	•	F, G, J, K, M
221	220 pF	•	•	•	•	•	F, G, J, K, M
241	240 pF	•	•	•	•	•	F, G, J, K, M
271	270 pF	•	•	•	•	•	F, G, J, K, M
301	300 pF	•	•	•	•	•	F, G, J, K, M
331	330 pF	•	•	•	•	•	F, G, J, K, M
361	360 pF	•	•	•	•		F, G, J, K, M
391	390 pF	•	•	•	•		F, G, J, K, M
431	430 pF	•	•	•			F, G, J, K, M
471	470 pF	•	•	•			F, G, J, K, M
511	510 pF	•	•	•			F, G, J, K, M
561	560 pF	•	•	•			F, G, J, K, M
621	620 pF	•	•	•			F, G, J, K, M
681	680 pF	•	•	•			F, G, J, K, M
751	750 pF	•	•				F, G, J, K, M
821	820 pF	•	•				F, G, J, K, M
911	910 pF	•	•				F, G, J, K, M
102	1.0 nF	•	•				F, G, J, K, M
112	1.1 nF	•					F, G, J, K, M
122	1.2 nF	•					F, G, J, K, M
132	1.3 nF	•					F, G, J, K, M
152	1.5 nF	•					F, G, J, K, M
182	1.8 nF						

Notes








• RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"

•• Paper carrier • Plastic carrier tape

(1) For values below 0.4 pF and tolerance ± 0.05 pF, contact mlccrf@vishay.com









HIGH FREQ DIELECTRIC - TYPICAL PARAMETERS





HIGH FREQ DIELECTRIC - TYPICAL PARAMETERS



**STANDARD PACKAGING QUANTITIES (1)(2)(3)**

CASE CODE	TAPE SIZE	7" REEL QUANTITIES			11 1/4" AND 13" REEL QUANTITIES	
		PAPER TAPE PACKAGING CODE "C"/"O"	PLASTIC TAPE PACKAGING CODE "T"	LOW QUANTITY "J" (5)	PAPER TAPE PACKAGING CODE "P"/"I"	PLASTIC TAPE PACKAGING CODE "R"
0402	8 mm	5000	n/a	1000	10 000	n/a
0603 (4)	8 mm	4000	4000	1000	10 000	10 000
0805 (4)	8 mm	3000	3000	1000	10 000	10 000

Notes

- (1) Vishay Vitramon uses embossed plastic carrier tape
(2) REFERENCE: EIA standard RS 481 - "Taping of Surface Mount Components for Automatic Placement"
(3) n/a = not available
(4) Packaging "C"/"P"/"O"/"I" and "T"/"R" or lower quantities can depend from product thickness
(5) Paper/plastic tape used by availability

STORAGE AND HANDLING CONDITIONS

- (1) Store the components at 5 °C to +40 °C ambient temperature and ≤ 70 % relative humidity conditions.
(2) The product is recommended to be used within a time-frame of 2 years after shipment (1 year for copper).
Check solderability in case extended shelf life beyond the expiry date is needed.

Precautions:

- Do not store products in an environment containing corrosive elements, especially where chloride gas, sulfide gas, acid, alkali, salt or the like are present. This may cause corrosion or oxidization of the terminations, which can easily lead to poor soldering.
- Store products on the shelf and avoid exposure to moisture or dust.
- Do not expose products to excessive shock, vibration, direct sunlight and so on.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.