


MICRO SWITCH

FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91928

SWITCH - ENCLOSED

CATALOG LISTING
622EN73-6





STAINLESS STEEL RIVET

ROLLER TO BE POSITIONED AT $\pm 2^\circ$ WITH
RESPECT TO KEYWAY

ELECTRICAL WIRES ON CENTERLINE
WITH KEYWAY WITHIN $\pm 6^\circ$

(6) NO. 20 WIRE LEAD PER MIL-W-22759/7 MARKED
WITH CIRCUIT IDENTIFICATION AND WIRE GAGE
(1-20, 2-20, ETC) PER MIL-W-5088



NOTES

- 1 - CORROSION RESISTANT STEEL ENCLOSURE
- 2 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 4
- 3 - COINCIDENCE OF OPERATING AND RELEASING POINTS:
.010 OF PLUNGER TRAVEL
- 4 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN
ON NAMEPLATE
- 5 - ELECTRICAL RATINGS APPLY AS SPECIFIED IN MIL-
PRF-8805/43 UP TO 185°F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA
OPERATING FORCE ----- 6-12 LB	CONTACT ARRANGEMENT S P D T (2)
FULL OVERTRAVEL FORCE ----- 30 LB MAX	28 VDC
RELEASE FORCE ----- 4 LB MIN	LOAD
PRETRAVEL ----- .040 MAX	SEA LEVEL 50,000 FT.
DIFFERENTIAL TRAVEL ----- .020 MAX	RES 7 7
OVERTRAVEL ----- .125 MIN	IND 4 2.5
	MOTOR 4

SCALE	FULL
DO NOT SCALE PRINT	
TOLERANCES	
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE:	
NO PLACES	IN
ONE PLACE	IN
TWO PLACES	IN
THREE PLACES	IN
ANGLES	IN
DESIGN UNITS	SI METRIC
THIRD ANGLE PROJECTION	
WEIGHT	8.0 OZ MAX

RASTER

622EN73-6

M

DRAWING
NUMBER

ISSUE

CMH

09 APR 09

CHECK

REPLACES

09 APR 09

REVISIONS

A C046610

D J W

22 OCT 79

B OBS DWG

CO-4748

G J W

24 MAR 80

C RE-IN

PR-9260

G J W

18 AUG 80

D C049806C

K A G

25 SEP 81

E C057370

J A P

14 MAY 85

F 0051009

S J K

09 APR 09

FO-52851-B

D J W

22 OCT 79

CHECK

09 APR 09

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[622EN73-6](#)