


CASE FINISH	CURRENT (AMPS)	WORKING VOLTAGE				MAXIMUM DC RESISTANCE (OHMS)	MAXIMUM VOLTAGE DROP		MINIMUM CAPACITANCE (uF)	MIN. INSERTION LOSS PER MIL-STD-220, FULL LOAD, +25°C												
		-55°C to +85°C		-55°C to +125°C			DC	AC		14	30	50	75	100	150	300	500	1	10	100	1	10
		AC	DC	AC	DC					KHz	KHz	KHz	KHz	KHz	KHz	KHz	KHz	MHz	MHz	MHz	GHz	GHz
SOLDER	15	- - -	100	- - -	70	0.005	0.075	- - -	0.7	--	10	--	--	20	24	30	--	40	52	70	70	--

PART MARKING:
9053-100-0008 (FAIRVIEW)
9053-100-0008M (MEXICO)
SCI DATE CODE


PACKAGE MARKING:
STANDARD

MARKING NOTES:
N/A



MTG. HARDWARE

SCHEMATIC



NOTES:
1) MOUNTING TORQUE NOT TO EXCEED 7 in-lbs.

										04	03	REV.	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES [MILLIMETERS] DO NOT SCALE THIRD ANGLE PROJECTION	TOLERANCES UNLESS OTHERWISE SPECIFIED Dec. .x ± .x Dec. .xx ± .xx Dec. .xxx ± .010 [.25] Angles ± 0° 30"		SPECTRUM CONTROL INC.		FAIRVIEW PENNSYLVANIA	
										CN 41061-ENG	CN 178555	CHANGE NOTICE NO.		Dwn. Hassett		Date 4-17-08		Description LOW PASS EMI FILTER	
														CODE IDENT. NO. 0LSP2		Engr. Devine		9053-100-0008	
														Sheet 1 of 1					

