

PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
F	DCN 34664	10/06	JMC
G	DCN 38051	03/11	PJS
H	DCN 38193	04/11	FED

MATERIAL:

BODIES, INSERTS, & COUPLING NUT:

STAINLESS STEEL PER AMS-5640,
ALLOY UNS S30300, TYPE 1

LOCK RING &
CONTACTS:

BERYLLIUM COPPER PER ASTM B196,
ALLOY No. UNS C17300, TD04

SLEEVE:

BRASS PER ASTM B16, ALLOY UNS No. C36000

BEADS:

ULTEM 1000

BELLOWS SPRINGS:

ELECTRO-DEPOSITED GOLD OVER NICKEL

GASKET:

SILICONE RUBBER PER A-A-59588,
CLASS 2B, GRADE 50/60

RESISTOR ELEMENT:

ALUMINUM NITRIDE SUBSTRATE WITH
TANTALUM NITRIDE RESISTOR:
GOLD PLATED TERMINATIONS

FINISH:

BODIES, INSERTS, & COUPLING NUT:

PASSIVATED PER AMS-2700, TYPE 2

CONTACTS:

GOLD PER ASTM B488, TYPE I,
CODE C, CLASS 0.51; OVER NICKEL
PER AMS-QQ-N-290, CLASS 1, .00005" MIN.

SLEEVE:

GOLD PER ASTM B 488, TYPE II,
CODE C, CLASS 1.27; OVER NICKEL
PER AMS-QQ-N-290, CLASS 1, .00005" MIN.

PERFORMANCE:

IMPEDANCE:
FREQ. RANGE:
VSWR:

50 OHMS
DC TO 40.0 GHz
1.30:1 MAX. DC TO 26.5 GHz
1.40:1 MAX. 26.5 TO 40.0 GHz

OPERATING TEMP.:
AVG. POWER:


0.5 WATT (POWER INPUT DERATED LINEARLY
FROM 25°C TO 0.25 WATTS AT 135°C)
100 WATTS (PEAK POWER FOR A DUTY CYCLE
OF 5X10-4 MAXIMUM PULSE DURATION OF
5 MICROSECONDS)

PEAK POWER:

100 WATTS (PEAK POWER FOR A DUTY CYCLE
OF 5×10^{-4} MAXIMUM PULSE DURATION OF
5 MICROSECONDS)

ENGAGEMENT/
DISENGAGEMENT:

2 IN-LBS



dB VALUE TO "XX" NUMBER CHART

	ATTENUATION ACCURACY	
dB VALUE	DC-26.5 GHz	26.5-40.0 GHz
0-6 dB	±0.5 dB	±0.8 dB
6.25-10 dB	±0.6 dB	±0.8 dB
10.25-20 dB	±0.6 dB	±1.0 dB

dB VALUE	XX	dB VALUE	XX	dB VALUE	XX	dB VALUE	XX
.25	40	5.25	50	10.25	60	15.25	70
.5	00	5.5	25	10.5	30	15.5	35
.75	41	5.75	51	10.75	61	15.75	71
1	01	6	06	11	11	16	16
1.25	42	6.25	52	11.25	62	16.25	72
1.5	21	6.5	26	11.5	31	16.5	36
1.75	43	6.75	53	11.75	63	16.75	73
2	02	7	07	12	12	17	17
2.25	44	7.25	54	12.25	64	17.25	74
2.5	22	7.5	27	12.5	32	17.5	37
2.75	45	7.75	55	12.75	65	17.75	75
3	03	8	08	13	13	18	18
3.25	46	8.25	56	13.25	66	18.25	76
3.5	23	8.5	28	13.5	33	18.5	38
3.75	47	8.75	57	13.75	67	18.75	77
4	04	9	09	14	14	19	19
4.25	48	9.25	58	14.25	68	19.25	78
4.5	24	9.5	29	14.5	34	19.5	39
4.75	49	9.75	59	14.75	69	19.75	79
5	05	10	10	15	15	20	20

MATERIAL:	SEE NOTES		DIMENSIONS ARE IN INCHES TOLERANCES:		UNLESS OTHERWISE SPECIFIED		SV Microwave, Inc. 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409			
FINISH:	SEE NOTES		FRACTIONAL: $\pm 1/64$ ANGULAR: $X^\circ \pm 1^\circ 0'$ $X^\circ X' \pm 15'$		1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA. 'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS		TITLE: SVK JACK TO PLUG DC-40.0 GHz ATTENUATOR			
SURFACE AREA:	N/A		DECIMAL: .X $\pm .030$ $.XX \pm .010$ $.XXX \pm .005$ INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994				SIZE CAGE CODE DWG. NO. B 95077 SF0915-6200-XX			
PROPRIETARY THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.			THIRD ANGLE PROJECTION		DRAWN: MGT 05/27/04		SCALE: 4:1			
					CHECKED: DWC 11/14/01		SHEET 1 OF 1			
					APPROVED: DWC 11/14/01					