

## 19" RACK CASES

### FEATURES

- Conforms to IEC 297-1, DIN 41494
- Simple design for total access
- Three depth variations
- Three height variations
- Numerous configurations for total flexibility
- Slide mounting facility


### APPLICATIONS

19" rack cases are designed to offer a simple solution to many 19" mounting applications, notably for those involving audio and radio equipment. The design allows numerous combinations to be assembled according to the application and hence offers total flexibility for the design engineer, using common piece parts. It also allows the case to be presented in a number of attractive finishes for individual product tailoring.

For rack configuration guide see page 5.46

### MATERIAL SPECIFICATION

- Top and base : 0.9mm RAL 7035 painted steel
- Front panels : 3mm anodised aluminium (black or clear) or painted steel  
1.6mm RAL 7035
- Rear panels : 1.2mm RAL 7035 painted steel
- Handles : ABS RAL 7035 or black and clear/black .  
Anodised aluminium extrusion.




| Height of unit | A      | B     | Dept of unit | C     | D*    | E     | F     |
|----------------|--------|-------|--------------|-------|-------|-------|-------|
| 1U             | 44,45  | 34,00 | 250          | 252,0 | 249,0 | 229,0 | 292,0 |
| 2U             | 88,9   | 78,0  | 350          | 352,0 | 349,0 | 329,0 | 392,0 |
| 3U             | 133,35 | 122,0 | 450          | 452,0 | 449,0 | 429,0 | 492,0 |

\* Assuming 2mm E/panel thickness

# 19" RACK CASES


## HOW TO CONFIGURE THE RACK CASE

Since it is generally accepted that the case will consist of a top, base, front and rear, the following example illustrates how to select the configuration which best suits you.




### ▲ THE TOP

This is available in 3 depths of 250mm, 350mm and 450mm in a ventilated and unventilated version and is simply attached to the case by means of two fastenings at the front.




### ▲ HANDLES

These are available in 1U, 2U and 3U versions and can be either black or grey. They attach to the case using 4 fixing screws through the front panel fixing centres.




### ▲ REAR PANELS

These are available in RAL 7035 painted steel and are attached to the base by 4 screw fixings. There are 3 height variations of 1U, 2U and 3U and all are removable.



### ▲ THE BASE

This is available in 3 depths of 250mm, 350mm and 450mm and three heights of 1U, 2U and 3U. It is also available in ventilated and unventilated versions. The base also has provision for the attachment of slides.




### ▲ FRONT PANELS

These are available in anodised aluminium (black or clear) and are attached to the base by means of 4 screw fixings. There are 3 height variations of 1U, 2U and 3U and all will accept front panel handles.

**Delivery:** Please note that all units will be supplied assembled.

## GENERAL ASSEMBLY



## 19" RACK CASES PART SELECTOR CHART

### Ordering information

| Front panels           | 1U          | 2U          | 3U          |
|------------------------|-------------|-------------|-------------|
| Painted steel (grey)   | 503-232969L | 503-232972L | 503-232975E |
| Black anodise          | 503-232970D | 503-232973J | 503-232976C |
| Clear anodise          | 503-232971B | 503-232974G | 503-232977A |
| Rear panels            | 1U          | 2U          | 3U          |
| RAL 7035 painted steel | 503-232984D | 503-232985B | 503-232986L |
| Top covers             | 250mm       | 350mm       | 450mm       |
| Ventilated             | 503-232963A | 503-232965H | 503-232967D |
| Unventilated           | 503-232964K | 503-232966F | 503-232968B |
| Base 1U                | 250mm       | 350mm       | 450mm       |
| Ventilated             | 503-232945C | 503-232951H | 503-232957G |
| Unventilated           | 503-232946A | 503-232952F | 503-232958E |
| Base 2U                | 250mm       | 350mm       | 450mm       |
| Ventilated             | 503-232947K | 503-232953D | 503-232959C |
| Unventilated           | 503-232948H | 503-232954B | 503-232960G |
| Base 3U                | 250mm       | 350mm       | 450mm       |
| Ventilated             | 503-232949F | 503-232955L | 503-232961E |
| Unventilated           | 503-232950K | 503-232956J | 503-232962C |
| Handles                | 1U          | 2U          | 3U          |
| Black                  | 503-232978K | 503-232980A | 503-232982H |
| Grey                   | 503-232979H | 503-232981K | 503-232983F |

**Note:** Care should be taken with 1U and 2U 450mm deep versions not to excessively weight load the unit without the use of additional chassis supports.

## CONFIGURATED PART NUMBERS:

So that specific permutations can be provided, it is now possible to configure exact requirements using the chart below. Each digit of the order code represents an available option for example, part number 519-110111 represents a 1U rack case, 250mm deep with a plain top cover and base, clear anodised front panel and grey handles. Configured units will be supplied assembled.

## RACK CASE CODE GENERATOR

519-11

X

X

X

X

| Height | Depth |   |
|--------|-------|---|
| 1U     | 250   | 0 |
| 2U     | 250   | 1 |
| 3U     | 250   | 2 |
| 1U     | 350   | 3 |
| 2U     | 350   | 4 |
| 3U     | 350   | 5 |
| 1U     | 450   | 6 |
| 2U     | 450   | 7 |
| 3U     | 450   | 8 |

|                                |
|--------------------------------|
| 0 = Vented top & base          |
| 1 = Unvented top & base        |
| 2 = Vented top / unvented base |
| 3 = Unvented top / vented base |
| 4 = Vented base only           |
| 5 = Unvented base only         |

|                              |
|------------------------------|
| 0 = No handles or rear panel |
| 1 = R/panel & grey handle    |
| 2 = R/panel & black handle   |
| 3 = Grey handles only        |
| 4 = Black handlers only      |
| 5 = R/panel only             |

|                                |
|--------------------------------|
| 0 = No front panel             |
| 1 = Clear anodised front panel |
| 2 = Black anodised front panel |
| 3 = Grey painted front panel   |