

TOSHIBA CMOS DIGITAL INTEGRATED CIRCUIT SILICON MONOLITHIC

TC74HCT540AP, TC74HCT540AF, TC74HCT540AFW
TC74HCT541AP, TC74HCT541AF, TC74HCT541AFW

OCTAL BUS BUFFER WITH TTL INPUT LEVEL

TC74HCT540AP/AF/AFW INVERTING, 3-STATE OUTPUTS

TC74HCT541AP/AF/AFW NON-INVERTING, 3-STATE OUTPUTS

(Note) The JEDEC SOP (FW) is not available in Japan.

The TC74HCT540A / TC74HCT541A are high speed CMOS OCTAL BUS BUFFERs fabricated with silicon gate C²MOS technology.

These devices may be used as a level converter for interfacing TTL or NMOS to High Speed CMOS. The inputs are compatible with TTL, NMOS and CMOS output voltage levels.

They achieve the high speed operation similar to equivalent LSTTL while maintaining the CMOS low power dissipation.


The TC74HCT540A is an inverting type, and the TC74HCT541A is a non-inverting type.

When either $\overline{G}1$ or $\overline{G}2$ are high, the terminal outputs are in the high-impedance state.


All inputs are equipped with protection circuits against static discharge or transient excess voltage.

FEATURES :


- High Speed..... $t_{pd} = 10\text{ns}$ (typ.) at $V_{CC} = 5\text{V}$
- Low Power Dissipation..... $I_{CC} = 4\mu\text{A}$ (Max.) at $T_a = 25^\circ\text{C}$
- Compatible with TTL outputs ... $V_{IL} = 0.8\text{V}$ (Max.)
 $V_{IH} = 2.0\text{V}$ (Min.)
- Wide Interfacing ability.....LSTTL, NMOS, CMOS
- Output Drive Capability 15 LSTTL Loads
- Symmetrical Output Impedance... $|I_{OH}| = |I_{OL}| = 6\text{mA}$ (Min.)
- Balanced Propagation Delays..... $t_{PLH} \approx t_{PHL}$
- Pin and Function Compatible with 74LS540/541



P (DIP20-P-300-2.54A)
Weight : 1.30g (Typ.)



F (SOP20-P-300-1.27)
Weight : 0.22g (Typ.)




FW (SOL20-P-300-1.27)
Weight : 0.46g (Typ.)

TRUTH TABLE


INPUTS			OUTPUTS	
$\overline{G}1$	$\overline{G}2$	A_n	Y_n^*	$\overline{Y}_n^*$
H	X	X	Z	Z
X	H	X	Z	Z
L	L	H	H	L
L	L	L	L	H

X : Don't Care

Z : High Impedance

* : Y_n HCT541A $\overline{Y}_n$ HCT540A**PIN ASSIGNMENT**

(TOP VIEW)



The diagram shows the logic for two 8-bit bus buffers, TC74HCT540A and TC74HCT541A. Both chips have an internal AND gate and an EN pin. The inputs are G1, G2, and A1-A8. The outputs are Y1-Y8. The TC74HCT540A is a non-inverting buffer, while the TC74HCT541A is an inverting buffer.

TC74HCT540A

Inputs: $\overline{G1}$ (1), $\overline{G2}$ (19), A1 (2), A2 (3), A3 (4), A4 (5), A5 (6), A6 (7), A7 (8), A8 (9).

Outputs: $\overline{Y1}$ (18), $\overline{Y2}$ (17), $\overline{Y3}$ (16), $\overline{Y4}$ (15), $\overline{Y5}$ (14), $\overline{Y6}$ (13), $\overline{Y7}$ (12), $\overline{Y8}$ (11).

TC74HCT541A

Inputs: $\overline{G1}$ (1), $\overline{G2}$ (19), A1 (2), A2 (3), A3 (4), A4 (5), A5 (6), A6 (7), A7 (8), A8 (9).

Outputs: Y1 (18), Y2 (17), Y3 (16), Y4 (15), Y5 (14), Y6 (13), Y7 (12), Y8 (11).

ABSOLUTE MAXIMUM RATINGS

PARAMETER	SYMBOL	VALUE	UNIT
Supply Voltage Range	V_{CC}	$-0.5 \sim 7$	V
DC Input Voltage	V_{IN}	$-0.5 \sim V_{CC} + 0.5$	V
DC Output Voltage	V_{OUT}	$-0.5 \sim V_{CC} + 0.5$	V
Input Diode Current	I_{IK}	± 20	mA
Output Diode Current	I_{OK}	± 20	mA
DC Output Current	I_{OUT}	± 35	mA
DC V_{CC} /Ground Current	I_{CC}	± 75	mA
Power Dissipation	P_D	500 (DIP)* / 180 (SOP)	mW
Storage Temperature	T_{stg}	$-65 \sim 150$	$^{\circ}\text{C}$

*500mW in the range of $T_a = -40^{\circ}\text{C} \sim 65^{\circ}\text{C}$. From $T_a = 65^{\circ}\text{C}$ to 85°C a derating factor of $-10\text{mW}/^{\circ}\text{C}$ shall be applied until 300mW.

RECOMMENDED OPERATING CONDITIONS

PARAMETER	SYMBOL	VALUE	UNIT
Supply Voltage	V_{CC}	4.5~5.5	V
Input Voltage	V_{IN}	$0 \sim V_{CC}$	V
Output Voltage	V_{OUT}	$0 \sim V_{CC}$	V
Operating Temperature	T_{opr}	$-40 \sim 85$	$^{\circ}\text{C}$
Input Rise and Fall Time	t_r, t_f	0~500	ns

DC ELECTRICAL CHARACTERISTICS

PARAMETER	SYMBOL	TEST CONDITION	V_{CC} (V)	$T_a = 25^{\circ}\text{C}$			$T_a = -40 \sim 85^{\circ}\text{C}$		UNIT
				MIN.	TYP.	MAX.	MIN.	MAX.	
High - Level Input Voltage	V_{IH}		4.5 5.5	2.0	—	—	2.0	—	V
Low - Level Input Voltage	V_{IL}		4.5 5.5	—	—	0.8	—	0.8	V
High - Level Output Voltage	V_{OH}	$V_{IN} = V_{IH} \text{ or } V_{IL}$	$I_{OH} = -20 \mu\text{A}$	4.5	4.4	4.5	—	4.4	V
			$I_{OH} = -6 \text{ mA}$	4.5	4.18	4.31	—	4.13	
Low - Level Output Voltage	V_{OL}	$V_{IN} = V_{IH} \text{ or } V_{IL}$	$I_{OL} = 20 \mu\text{A}$	4.5	—	0.0	0.1	—	V
			$I_{OL} = 6 \text{ mA}$	4.5	—	0.17	0.26	—	
3 - State Output Off - State Current	I_{OZ}	$V_{IN} = V_{IH} \text{ or } V_{IL}$ $V_{OUT} = V_{CC} \text{ or GND}$	5.5	—	—	± 0.5	—	± 5.0	μA
Input Leakage Current	I_{IN}	$V_{IN} = V_{CC} \text{ or GND}$	5.5	—	—	± 0.1	—	± 1.0	μA
Quiescent Supply Current	I_{CC}	$V_{IN} = V_{CC} \text{ or GND}$	5.5	—	—	4.0	—	40.0	
	I_C	Per input: $V_{IN} = 0.5\text{V or } 2.4\text{V}$ Other input: $V_{CC} \text{ or GND}$	5.5	—	—	2.0	—	2.9	mA

AC ELECTRICAL CHARACTERISTICS (Input $t_r = t_f = 6\text{ns}$)

PARAMETER	SYMBOL	TEST CONDITION	CL (pF)	V _{CC} (V)	Ta = 25°C			Ta = -40~85°C		UNIT
					MIN.	TYP.	MAX.	MIN.	MAX.	
Output Transition Time	t_{TLH} t_{THL}		50	4.5 5.5	— —	7 6	12 11	— —	15 14	ns
Propagation Delay Time (TC74HCT540A)	t_{PLH}		50	4.5 5.5	— —	12 9	20 18	— —	25 23	
	t_{PHL}		150	4.5 5.5	— —	17 14	26 24	— —	33 30	
Propagation Delay Time (TC74HCT541A)	t_{PLH}		50	4.5 5.5	— —	14 11	23 21	— —	29 27	
	t_{PHL}		150	4.5 5.5	— —	19 16	29 27	— —	36 33	
Output Enable time	t_{pZL} t_{pZH}	$R_L = 1\text{k}\Omega$	50	4.5 5.5	— —	18 16	30 27	— —	38 35	
			150	4.5 5.5	— —	23 21	36 33	— —	45 41	
Output Disable time	t_{pLZ} t_{pHZ}	$R_L = 1\text{k}\Omega$	50	4.5 5.5	— —	18 16	30 27	— —	38 35	
Input Capacitance	C_{IN}				—	5	10	—	10	pF
Output Capacitance	C_{OUT}				—	10	—	—	—	
Power Dissipation Capacitance	$C_{PD} (1)$	TC74HCT540A			—	35	—	—	—	
		TC74HCT541A			—	31	—	—	—	


Note (1) C_{PD} is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load.

Average operating current can be obtained by the equation :

$$I_{CC}(\text{opr}) = C_{PD} \cdot V_{CC} \cdot f_{IN} + I_{CC} / 8 \text{ (per bit)}$$

DIP 20PIN PACKAGE DIMENSIONS (DIP20-P-300-2.54A)


Unit in mm



Weight : 1.30g (Typ.)

SOP 20PIN (200mil BODY) PACKAGE DIMENSIONS (SOP20-P-300-1.27)

Unit in mm




Weight : 0.22g (Typ.)

SOP 20PIN (300mil BODY) PACKAGE DIMENSIONS (SOL20-P-300-1.27)

Unit in mm

(Note) This package is not available in Japan.



Weight : 0.46g (Typ.)

RESTRICTIONS ON PRODUCT USE

000707EBA

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property. In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The products described in this document are subject to the foreign exchange and foreign trade laws.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.