

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
BD	35		M1	REVISED PER ECO-11-004917	11MAR11	RK	HMR

1. PLUG MATES WITH RECEPTACLE 208495.
2. THIS PLUG ACCEPTS THREE (3) TYPE XII FEMALE CONTACTS.
MAXIMUM WIRE INSULATION DIAMETER = .220.
3. AMP PART NUMBER AND DATE CODE TO BE LOCATED
ON COUPLING RING.

4 MAJOR KEYS IN METAL SHELL PLUG AND PLUG
LOCATED 180° (OPPOSITE) FROM EACH OTHER.

DETENT
MATERIAL: THERMOPLASTIC
COLOR: BLACK

TETRASEAL, SEE TABLE
MATERIAL: FLOUROCARBON

RETAINER RING
MATERIAL: STAINLESS STEEL

RETAINER RING
MATERIAL: STAINLESS STEEL

PLUG HOUSING, STD SEX
ARRANGEMENT 17-3
MATERIAL: THERMOPLASTIC
COLOR: BLACK



PLUG SHELL
MATERIAL: ZINC ALLOY
FINISH: NICKEL PER QQ-N-290

1-3/16 - 18 UNEF-2A
THREAD

±.010
.380


1.805 MAX

COUPLING RING
MATERIAL: ZINC ALLOY
FINISH: NICKEL PER QQ-N-290



DETAIL A

OBSOLETE	DETAIL A	NO	208494-4
	AS SHOWN	YES	208494-3
	AS SHOWN	NO	208494-1
KEYING		TETRASEAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL 7-2-92		 TE Connectivity			
DIMENSIONS: INCHES		CHK R.STONE 12-29-92					
		APVD K.BEAVER 12-29-92		NAME PLUG ASSEMBLY, STANDARD SEX, SERIES 3, 22-3, CMC			
		PRODUCT SPEC 108-10040					
		APPLICATION SPEC —					
MATERIAL SEE CALLOUT		FINISH SEE CALLOUT		SIZE A2	CAGE CODE 00779	DRAWING NO C-208494	RESTRICTED TO —
		CUSTOMER DRAWING		SCALE 2:1		SHEET 1 of 1	REV M1