




1 MATERIAL:
HOUSING - NYLON, BLACK, UL94V-0.
OVERMOLDED TERMINAL ARRAY - PBT, BROWN.
TERMINALS-.013 [0.33] THICK PHOS BRONZE
PLATED WITH .000050 [1.27μm] THICK HARD
GOLD IN LOCALIZED AREA AND .000150 [3.81μm]
THICK TIN-LEAD IN SOLDER AREA OVER .000050
[1.27μm] THICK NICKEL UNDERPLATE.
SHIELD-.010 [0.254] THICK COPPER ALLOY
PLATED WITH .000080 [2.03μm] MINIMUM
TIN-LEAD OVER .000100 [2.54μm] MINIMUM
COPPER.


2 JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.

3. ALL DIMENSIONS SHOWN ARE NOMINAL UNLESS OTHERWISE SPECIFIED.

4. ALL DIMENSIONS SHOWN IN BRACKETS [] ARE IN MILLIMETERS.


△ THIS HOLE IS NEEDED FOR -1 ONLY.

△ THIS TAB REMOVED ON -2.



SUGGESTED PC BOARD LAYOUT
COMPONENT SIDE
SEE APPLICATION SPECIFICATION

WITHOUT REAR PC BOARD GROUND TAB	406491-2
WITH REAR PC BOARD GROUND TAB	406491-1
DESCRIPTION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN 13MAR92 V. SLACK		AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES [mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED.		AMP	
		0 PLC ±- 1 PLC ±- 2 PLC ±.01 [0.254] 3 PLC ±.005 [0.127] 4 PLC ±- ANGLES ±-		NAME MODULAR JACK ASSEMBLY, PANEL GROUND, 8 PORT, 8 POSITION, RIGHT ANGLE, SHIELDED, CATEGORY 5	
MATERIAL		FINISH		SIZE A2	
				CAGE CODE 00779	
WEIGHT -		CUSTOMER DRAWING		DRAWING NO C=406491	
				SCALE 2.1 SHEET 1 OF 1 REV A	