


LOC		DIST		REVISIONS			
F	LTR	DESCRIPTION		DATE	DWN	APVD	
F		OBSOLETE: -1 PER 0S11-0143-02		11FEB2003	DD	KK	




DETAIL C	DETAIL A	NON-BUFFERED DRAM, 3.3 VOLT	390040-6
DETAIL B	DETAIL A	SYNC DRAM, 3.3 VOLT	390040-5
DETAIL A	DETAIL A	STD DRAM, 3.3 VOLT	390040-4
DETAIL A	DETAIL B	STD DRAM, 5 VOLT	390040-1
KEY #1	KEY #2	PART DESCRIPTION	PART NUMBER

OBSOLETE

- FOR OPTIMUM PERFORMANCE, CONTACT PAD PLATING SHOULD BE SMOOTH AND FLAT, COPPER CONTACT PADS ARE TO BE OVERPLATED WITH 0.00127[.000050] MIN THK NICKEL FOLLOWED WITH 0.00102[.000040] MIN THK GOLD PLATING.
- CONTACT MATING AREA:
0.00076[.000030] MIN THICK GOLD OVER 0.00381[.000150] NICKEL
OR GOLD FLASH OVER 0.00051[.000020] MIN THK 80/20 PALLADIUM-NICKEL.
SOLDERTAILS: 0.00381[.000150] MIN THK TIN-LEAD UNDERPLATE:
0.00127[.000050] MIN THK NICKEL OVER ENTIRE CONTACT.
- MATERIAL:
HOUSING AND EXTRACTORS: GLASS FILLED, HIGH TEMPERATURE NYLON.
CONTACTS: PHOS BRONZE

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. ANY UNAUTHORIZED CHANGES AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN W. SORAH 26-APR-96	AMP Incorporated Harrisburg, PA 17103-3608	
DIMENSIONS: mm [INCHES]		CHK R. TALLEY 26-APR-96		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 9 PLC ±.13 [.005] 1 PLC ±. 5 PLC ±. 4 PLC ±. ANGLES ±°		APVD S. HOWELL 26-APR-96	NAME SOCKET ASSEMBLY, DUAL READ-OUT, VERSION II, 8 BYTE, 168 POSITION	
MATERIAL		PRODUCT SPEC	SIZE A1	
FINISH		APPLICATION SPEC	CAGE CODE 00779	
WEIGHT		WEIGHT	DRAWING NO. C390040	
CUSTOMER DRAWING		CUSTOMER DRAWING	SCALE 1:1	
			SHEET 1 OF 2	
			REV F	



LOC		DIST		REVISIONS			
GP				F	LTW	DESCRIPTION	DATE
				-	-	SEE SHEET 1	-

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. ANY DISCREPANCY IN DIMENSIONS AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				DWN W. SORAH	26-APR-96	AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]				CHK R. TALLEY	26-APR-96	NAME SOCKET ASSEMBLY, DUAL READ-OUT, VERSION II, 8 BYTE, 168 POSITION	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 9 PLC ± 1 PLC ± 5 PLC ±0.13 [0.005] 4 PLC ± ANGLES ±1°				APPRO S. HOWELL	26-APR-96	CAGE CODE 00779	
MATERIAL SEE SH 1				PRODUCT SPEC		DRAWING NO. 390040	
FINISH				APPLICATION SPEC		SCALE 4:1	
				WEIGHT		SHEET 2 OF 2	
				CUSTOMER DRAWING		REV F	