


Semco Packaging & Application Systems
PPG Industries (UK) Ltd
Darlington Road
Shildon
County Durham
DL4 2QP UK
T: +44 (0) 1388 770 222
F: +44 (0) 1388 770 288

less Park

TECHNICAL SERVICE INFORMATION

PRODUCT DESCRIPTION

SD 340 AUTOMATIC DISPENSER



NO.	PART NUMBER	DESCRIPTION	QTY.	NO.	PART NUMBER	DESCRIPTION	QTY.
11	560689	FUSE HOLDER	1	22	560680	JB SIDE PANEL	2
10	561403	BARB TEE	1	21	561398N	NYLON FITTING	2
9	561400	BLUE URETHANE TUBING	2	20	561413N	BARBED ELBOW	1
8	560031A	POTENTIOMETER	1	19	561399	GAGE, 0-100 PSI	1
7	561427	FEMALE QUICK CONNECT	1	18	560685R	REGULATOR, MOUNTING RING	1
6	560026(E)	POWER SWITCH	1	17	560685A	REGULATOR	1
5	560028	STEADY SWITCH	1	16	560032(E)	TRANSFORMER	1
4	560152	SOLENOID	1	15	560030-CE	PC BOARD	1
3	561402N	NYLON ELBOW	7	14	560765	PLUG	1
2	561422	VACUUM TRANSDUCER	1	13	560691	AC RECEPTACLE	1
1	560686	NEEDLE VALVE	1	12	561431	AIR INLET FITTING	1

NOTE: ALL TUBING IS THE SAME TUBING P/N 561400. THIS TUBING MUST BE ORDERED BY LENGTH (FEET)

Semco®


PPG PPG Industries
Semco® Packaging &
Application Systems

Semco Packaging & Application Systems
PPG Industries (UK) Ltd
Darlington Road
Shildon
County Durham
DL4 2QP UK
T: +44 (0) 1388 770 222
F: +44 (0) 1388 770 286

SD 340

AUTOMATIC LIQUID DISPENSER

OPERATING MANUAL



The **Semco® SD 340 precision** automatic liquid dispensers, with their versatile design, make them perfectly suited for a wide variety of dispensing applications, from micro-dot deposits to large potting and filling.

- Digital Timer Control
- No dripping on very low viscosity liquids
- Timing intervals from 0.01 - 31 seconds

SPECIFICATIONS

Digital Timer

Programmable

0.01-1, 0.1-10, 0.2-20 and

0.3-30 seconds

Maintained or Momentary

0.1%

22cm x 21cm x 6.7cm

Cycle Initiation

Repeat Tolerance

Size

Internal & Foot

Pedal Voltage

Cycle Speed

Air Input

Air Output

24vdc

600+/Minute

70-100psi(5-7 bar)

1-100psi (0.1-7 bar)


Barrel "Suck Back" feature

Dispensing Accessories Supplied With Unit

- | | |
|---|---|
| 2 | Power Cords 220v UK /European |
| 1 | Barrel Stand |
| 1 | Foot Pedal |
| 1 | Barrel Adaptor* |
| 1 | Selection of Semco Hybrid Syringe |
| | Barrels & Accessories |
| | (5,10,30 or 55cc, according to customers requirements) |
| 1 | Section of Dispensing Tips |
| | (Various gauges from both Tapered Tip & Blunt End Ranges) |


* Size of barrel adaptor will be 5,10 or 30/55cc as per customer's requirements


I. SETTING UP



1. Connect air hoses to filtered compressed air 70-100psi (5-7 bar) and connect fitting to dispenser.
2. Insert Foot Switch Plug.
3. Insert & Twist barrel adaptor on to syringe barrel.
4. Insert power cord female plug into dispenser and insert the male plug into the earthed outlet. **CHECK VOLTAGE LABEL** on back of unit.
5. Fill barrel (with Semco Spike Tip Cap on the barrel) with material to be dispensed and lock barrel to adaptor as shown.
6. **OR**, use Semco syringe filling adaptor, 310025, to fill directly from cartridges (this can be carried out with the piston fully inserted).

II. AIR & ELECTRICAL SET UP DIAGRAM





Understanding the Functions of your Dispenser Display

- A** Turn unit on
 - B** Turn amber light on; this will provide a continuous flow of material as long as the foot pedal is depressed.
 - C** Turning the pressure adjust knob (D) allows for adjustments of output air pressure.
 - E** Push foot pedal to start dispensing.
- The amount of liquid dispensed depends on air pressure, size of dispense tip (G), viscosity of material and time of pulse (F).
- To produce timed deposits, press (B) to turn amber light off.
- H** Vacuum control to prevent dripping of low viscosity or "run-on" of medium viscosity materials.

HELPFUL HINTS FOR MAKING DEPOSITS

FIG. 1






FIG. 1




1. Hold the barrel at approximately 60° (+ or -20°) angle (Fig.1)
2. After making deposit remove tip as shown (Fig.2)
3. Do not permit the liquid to flow back into the controller as shown in Fig.3

FIG. 3



4. Increase or decrease the size of dots by either,
Increasing or decreasing time only (F)
OR
Increasing or decreasing pressure only (C) (D)
OR
Increasing or decreasing size of tip (G)
OR
Increasing or decreasing and combination of time, pressure and size of tip.
5. For thin liquids, like water, you can prevent dripping by slowly turning the vacuum control (H) anti-clockwise. **CAUTION** - Too much vacuum will cause bubbles and suck liquid back into the controller, thus creating permanent damage to the unit.



LIMITED WARRANTY

Manufacturer warrants this product to the original purchaser for a period of **One (1)** year from date of purchase to be free of defects in material and workmanship, but not against damages by mis-use, negligence, accident, faulty installation, abrasion, corrosion, or by "not" operating in accordance with factory recommendations and instructions. Manufacturer will repair or replace (at factory's opinion), free of charge, any component of the equipment thus found to be defective, on return to the factory during the warranty period. In no event shall any liability or obligation of Manufacturer arising from this warranty exceed the purchase price of equipment. This warranty is valid "only" when 5 micron filtered air is used. The manufacturer's liability stated herein, cannot be altered or enlarged except by a written statement signed by a company officer. In no event shall manufacturer be liable for consequential or incidental damages.



PPG Industries
Semco Packaging &
Application Systems

Semco Packaging & Application Systems
PPG Industries (UK) Ltd

Darlington Road
Shildon
Co Durham
DL4 2QP - UK

T: 01388 770 222
F: 01388 770 288