



STRIP MATERIAL NUMBER	FINISH
84525-0017	SELECTIVE TIN 100μ INCH MINIMUM OVER NICKEL 80μ INCH MINIMUM OVERALL
84525-0039	SELECTIVE HARD GOLD 30μ INCH MINIMUM WITH SELECTIVE TIN 100μ INCH MINIMUM OVER NICKEL 50μ INCH MINIMUM OVERALL



WIRE INSULATION O.D. RANGE $\frac{.075-.130}{1.90-3.30}$

NOTES:

1. TERMINAL MATERIAL: COPPER ALLOY, .0118/0.300 THICK. FINISH: SEE CHART.
2. HOOD MATERIAL: STAINLESS STEEL, .006/0.15 THICK.
3. STRIP PARTS ARE REELED 3000 PARTS PER REEL AS SHOWN ABOVE.
4. TERMINAL FOR USE WITH SERIES XRC CONNECTOR ASSEMBLIES.
5. ALL MATERIALS AND FINISHES ARE ROHS COMPLIANT.



UPDATE LENGTH EC NO: IPG2012-0063 DRAWN: WLEUNG CHKD: APPR: DTITUS	DESCRIPTION 2011/12/06 2012/01/09	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY MODELL	DATE 2009/04/03	TITLE XRC SOCKET W/SNAP WINDOW 14-18AWG .075"-.130" WIRE DIA	MOLEX MOLEX INCORPORATED	SHEET NO. 1 OF 1
			4 PLACES	± ---	± ---	CHECKED BY RDEROSS	DATE 2009/04/03			
			3 PLACES	± ---	± .005	APPROVED BY DTITUS	DATE 2010/12/06	DOCUMENT NO. SD-84525-005		
			2 PLACES	± 0.13	± ---	MATERIAL NO. SEE CHART				
			1 PLACE	± ---	± ---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				
			ANGULAR ± ---°							
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			