




DESCRIPTION: .085" RIBBON DIP SOLDER



	A	B	C	D	E
14	1.729 43.92	.992 25.20	.502 12.75	.602 15.20	1.417 35.99
24	2.154 54.71	1.417 36.00	.502 12.75	.602 15.20	1.843 46.79
36	2.665 67.69	1.925 48.90	.502 12.75	.602 15.20	2.352 59.74
50	3.047 77.40	2.538 64.47	.502 12.75	.602 15.20	2.689 68.30

111-XXX-113-101

SERIES _____
POSITIONS _____
014
024
036
050

GENDER _____
1 = MALE

TERMINATION _____
1 = DIP SOLDER

SHELL PLATING _____
3 = NICKEL

HARDWARE OPTIONS _____
10 = BAIL LATCH RECEPTACLE

PLATING OPTIONS _____
01 = GOLD FLASH

MATERIALS:

INSULATOR: GLASS-FILLED THERMOPLASTIC
UL RATED 94V-0

CONTACTS: COPPER ALLOY
ELECTRICALS:

CONTACT CURRENT RATING: 5 AMPS

DIELECTRIC WITHSTANDING VOLTAGE: AC 1200 R.M.S.

INSULATION RESISTANCE: 1000 mohms MINIMUM AT 500V DC

CONTACT RESISTANCE: 30 mOHMS MAXIMUM

OPERATING TEMPERATURE: -55°C TO +125°C



THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF NorComp AND
SHALL NOT BE REPRODUCED, COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OF SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

DRAWN:
WAYNE ROBBINS

DATE:
9-21-98

CHECKED:

DATE:

SCALE:
1:1

SHEET
1 OF 1

REV
3

DWG NO.

111-XXX-113-101

NorComp