




LOC		DIST		REVISONS			
AD		47		DATE	DWN	APVD	
M1		REVISED PER ECO-11-004835		11MAR11	RK	HMR	

- 1 HOUSING: LIQUID CRYSTAL POLYMER, COLOR BLACK.
CONTACTS: HIGH RELIABILITY COPPER ALLOY.
GROUND BUSSES: PHOSPHOR BRONZE ALLOY, UNS C51100.
- 2 CONTACTS & GROUND BUSES: NICKEL UNDERPLATE ALL OVER, MATING SURFACE PLATED TO MEET LEVEL 2 PERFORMANCE REQUIREMENTS OF TE CONNECTIVITY PRODUCT SPECIFICATION 108-1422, SOLDER TAILS PLATED TIN-LEAD.
- 3 DATE CODE MARKED IN AREA INDICATED ON SIDE OPPOSITE POSITION #1.
- 4 ONE GROUND BUS WITH 5 TAILS PER EACH MODULE.
- 5 TOLERANCE NON-ACCUMULATIVE.
- 6 FOR SLIP-FIT APPLICATIONS, ORIENTATION HOLE TO BE $\phi .079 \pm .001 [2.00 \pm 0.03]$.

3.000[76.2]	6	3.450[87.63]	3.900[99.06]	4.000[101.6]	266	767054-7
2.500[63.5]	5	2.950[74.93]	3.400[86.36]	3.500[88.9]	228	767054-6
2.000[50.8]	4	2.450[62.23]	2.900[73.66]	3.000[76.2]	190	767054-5
1.500[38.1]	3	1.950[49.53]	2.400[60.96]	2.500[63.5]	152	767054-4
1.000[25.4]	2	1.450[36.83]	1.900[48.26]	2.000[50.8]	114	767054-3
.500[12.7]	1	.950[24.13]	1.400[35.56]	1.500[38.1]	76	767054-2
.000[0]	0	.450[11.43]	.900[22.86]	1.000[25.4]	38	767054-1
E	D	C	B	A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. GERACE 8-23-96	TE Connectivity	
DIMENSIONS: INCHES		CHK P. MATAR 8-23-96	NAME RECEPTACLE ASSEMBLY, VERTICAL, .025[0.64]CL, GULL WING LEADS, MICTOR	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. MONK 8-23-96	PRODUCT SPEC 108-1422	
0 PLC $\pm -$		APPLICATION SPEC 114-11004		RESTRICTED TO
1 PLC $\pm -$		SIZE A1		1 OF 1
2 PLC $\pm -$		CAGE CODE 00779		REV
3 PLC $\pm -$		DRAWING NO 767054		M1
4 PLC $\pm -$		WEIGHT -		
ANGLES $\pm -$		CUSTOMER DRAWING		SCALE 8:1