




 RoHS COMPATIBLE, SEE NOTE 5




 PIN STYLE, SEE SHEET 2

 PLATING SEE SHEET 2



- 1 - HOUSING MAT'L : GLASS FILLED
THERMOPLASTIC. UL94V-0 COLOR: BLUE
- 2 - PIN MATERIAL : PHOSPHOR BRONZE
- 3 - PACKAGING :
POLYBAGS FROM 2X02 TO 2X04 POSITIONS
TUBE FROM 2X05 TO 2X32 POSITIONS
- 4 - TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS $N \times 2.54 = 20.32\text{mm}$

- a – PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD–FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.
- b – MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.
- c – LABELLING:
 - MEETS PACKAGING SPECS AS PER GS–14–920
- d – LEGAL STATEMENT: SEE GS–47–0004



mat'l. code			surface		tolerance		projection		product family	
SEE NOTES			ISO 1302 ✓		ISO 406 ISO 1101				QUICKIE	
ltr	ecn	dr	date		tolerances unless otherwise specified		mm		title	
AJ	F06-0335	LMU	06.12.08		.X ±0.3				SHR.LP.HEADER RA DR TMT	
AK	F07-0198	LMU	07.05.30		.XX ±0.13					
AL	F08-0146	YOY	08.04.11		.XXX ±0.05					
AM	F10-0258	LMU	10.12.15	dr	D.LE	01.01.24			dwg no	
AN	B-19072	LMU	14.10.15	enfr	JM.C	01.01.24			sheet 1 of 2	
AP	B-19093	LMU	14.10.16	chr	JF.N	01.01.24			size	
				appl	JM.C	01.01.24			A3	
									type CUSTOMER Drawing	

1		2		3		4		5		6	
STANDARD APPLICATION											
PIN STYLE	Nbr OF POSITIONS	LEFT POLARIZATION	RIGHT POLARIZATION								
30	2 x 2	NO	NO								
31	2 x 3	NO	NO								
32	2 x 4	NO	NO								
01	2 x 5	NO	YES								
02	2 x 7	NO	YES								
03	2 x 8	YES	YES								
04	2 x 10	YES	YES								
05	2 x 13	YES	YES								
33	2 x 15	YES	YES								
06	2 x 17	YES	YES								
07	2 x 20	YES	YES								
08	2 x 25	YES	YES								
09	2 x 30	YES	YES								
10	2 x 32	YES	YES								
PLATING :											
1 = 0.76µm GOLD/GXT (PdNi WITH GOLD FLASH) ON CONTACT AREA 2µm MIN MATTE TIN ON TAIL											
2 = 2µm TIN MIN FULL PLATED											
3 = 0.38µm GOLD/GXT (PdNi WITH GOLD FLASH) ON CONTACT AREA 2µm MIN MATTE TIN ON TAIL											
UNDERPLATE : 1.27µm Ni MIN											
APPLICATION SPECIFIC											
PIN STYLE	Nbr OF POSITIONS	LEFT POLARIZATION	RIGHT POLARIZATION	OMIT PIN							
13	2 x 17	YES	YES	5							
14	2 x 20	YES	YES	19							
34	2 x 5	NO	YES	5							
35	2 x 10	YES	YES	19							
36	2 x 20	YES	YES	10							
37	2 x 20	YES	YES	11							
38	2 x 20	YES	YES	20							
PLATING :											
1 = 0.76µm GOLD/GXT (PdNi WITH GOLD FLASH) ON CONTACT AREA 2µm MIN MATTE TIN ON TAIL											
2 = 2µm TIN MIN FULL PLATED											
3 = 0.38µm GOLD/GXT (PdNi WITH GOLD FLASH) ON CONTACT AREA 2µm MIN MATTE TIN ON TAIL											
UNDERPLATE : 1.27µm Ni MIN											
mat'l. code											
surface ISO 1302 ✓ tolerance ISO 406 ISO 1101											
projection											
product family QUICKIE											
title											
SHR.LP.HEADER											
RA DR TMT											
dwg no 75867											
sheet 2 of - size A3											
type CUSTOMER Drawing											
sheet index											
revision sheet											
PDS: Rev :AP STATUS:Released Printed: Oct 23, 2014											