

TOSHIBA LED LAMP

TLRE1100 (T11), TLSE1100 (T11), TLOE1100 (T11)
TLYE1100 (T11), TLGE1100 (T11), TLPGE1100 (T11)


PANEL CIRCUIT INDICATOR

Unit in mm

- Surface Mount Device
- 3.2 (L) × 2.8 (W) × 1.9 (H) mm Size
- Flat-top Type
- InGaAlP LED
- Available of Automounting Machine Use
- Low Drive Current, High Intensity Light Emission
- Applications : Automotive use, Message Signboard, Backlight, etc.
- Standard embossed taping : T11 (2000 pcs / reel)
8 mm tape reel

LINE-UP

PRODUCT NAME	COLOR	MATERIAL
TLRE1100	Red	InGaAlP
TLSE1100	Red	InGaAlP
TLOE1100	Orange	InGaAlP
TLYE1100	Yellow	InGaAlP
TLGE1100	Green	InGaAlP
TLPGE1100	Pure Green	InGaAlP



Weight : 35 mg

MAXIMUM RATINGS (Ta = 25°C)

PRODUCT NAME	FORWARD CURRENT I _F (mA)	REVERSE VOLTAGE V _R (V)	POWER DISSIPATION P _D (mW)	OPERATING TEMPERATURE T _{opr} (°C)	STORAGE TEMPERATURE T _{stg} (°C)
TLRE1100	50	4	(120)	-40~100	-40~100
TLSE1100	50	4	(120)		
TLOE1100	50	4	(120)		
TLYE1100	50	4	(120)		
TLGE1100	50	4	(120)		
TLPGE1100	50	4	(120)		

961001EAC1

- TOSHIBA is continually working to improve the quality and the reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to observe standards of safety, and to avoid situations in which a malfunction or failure of a TOSHIBA product could cause loss of human life, bodily injury or damage to property. In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent products specifications. Also, please keep in mind the precautions and conditions set forth in the TOSHIBA Semiconductor Reliability Handbook.
- Gallium arsenide (GaAs) is a substance used in the products described in this document. GaAs dust and fumes are toxic. Do not break, cut or pulverize the product, or use chemicals to dissolve them. When disposing of the products, follow the appropriate regulations. Do not dispose of the products with other industrial waste or with domestic garbage.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.

ELECTRICAL CHARACTERISTICS (Ta = 25°C)

PRODUCT NAME	FORWARD VOLTAGE V _F				REVERSE CURRENT I _R	
	MIN	TYP.	MAX	I _F	MAX	V _R
TLRE1100	—	1.9	2.4	20	50	4
TLSE1100	—	1.9	2.4	20	50	4
TLOE1100	—	2.0	2.4	20	50	4
TLYE1100	—	2.0	2.4	20	50	4
TLGE1100	—	2.0	2.4	20	50	4
TLPGE1100	—	2.1	2.4	20	50	4
Unit	V			mA	μA	V

OPTICAL CHARACTERISTICS-1 (Ta = 25°C)

PRODUCT NAME	LUMINOUS INTENSITY I _V			
	MIN	TYP.	MAX	I _F
TLRE1100	(47.6)	100	—	20
TLSE1100	(47.6)	180	—	20
TLOE1100	(47.6)	180	—	20
TLYE1100	(47.6)	150	—	20
TLGE1100	(47.6)	100	—	20
TLPGE1100	(8.50)	25	—	20
Unit	mcd			mA







OPTICAL CHARACTERISTICS-2 (Ta = 25°C)

PRODUCT NAME	EMISSION SPECTRUM							
	Peak Emission Wavelength λ _p			Δλ TYP.	Dominant Wavelength λ _d			I _F
	MIN	TYP.	MAX		MIN	TYP.	MAX	
TLRE1100	—	(644)	—	(20)	—	630	—	20
TLSE1100	—	(623)	—	(20)	—	613	—	20
TLOE1100	—	(612)	—	(20)	—	605	—	20
TLYE1100	—	(590)	—	(17)	—	587	—	20
TLGE1100	—	(574)	—	(17)	—	571	—	20
TLPGE1100	—	(562)	—	(14)	—	558	—	20
UNIT	nm			nm	nm			mA


(Note) : This visible LED lamp also emits some IR light.

If a photodetector is located near the LED lamp, please ensure that it will not be affected by this IR light.







TLRE1100




TLSE1100




TLOE1100




TLYE1100



TLGE1100



TLPGE1100



RELATIVE LUMINOUS INTENSITY - WAVELENGTH

$I_F = 20\text{ mA}$
 $T_a = 25^{\circ}\text{C}$

RELATIVE LUMINOUS INTENSITY

1.0
0.8
0.6
0.4
0.2
0

WAVELENGTH λ (nm)

520 540 560 580 600

RADIATION PATTERN

$T_a = 25^{\circ}\text{C}$

0° 10° 20° 30° 40° 50° 60° 70° 80° 90°

0 0.2 0.4 0.6 0.8 1.0

$I_F - T_a$

ALLOWABLE FORWARD CURRENT I_F (mA)

80
60
40
20
0

AMBIENT TEMPERATURE T_a ($^{\circ}\text{C}$)

0 20 40 60 80 100 120

PACKAGING

This LED device is packed in an aluminum envelope with silica-gel to avoid moisture absorption. The optical characteristics may be affected by exposure to moisture in the air before soldering and storage at the following condition is recommended.

- Temperature : 5~30°C
- Relative Humidity : 60% or lower

Baking is required if the device have been stored unopened for more than 6 month or if the aluminum envelope has been opened for more than 168 h.
Recommended baking condition is 60°C for 12 h minimum in the dry atmosphere.

PRECAUTION FOR MOUNTING

Do not apply force to the plastic part of the LED in high temperature conditions.
Do not apply friction using hard materials for avoid injuring the plastic part of the LED.
Keep the LED away from any other parts when assembling boards into the set.

TAPING SPECIFICATIONS


1. Taping Number

- (1) Name : T11
- (2) Example : TLSE1100 (T11)
- Tape Specifications
- Device Identifier

2. Dimension of tape


(Unit in mm)

ITEM	DIMENSIONS	TOLERANCE	ITEM	DIMENSIONS	TOLERANCE
D	1.5	+0.1/ -0	P ₂	2.0	±0.05
E	1.75	±0.1	W	8.0	±0.3
P ₀	4.0	±0.1	P	4.0	±0.1
t	0.3	±0.05	A ₀	2.9	±0.1
F	3.5	±0.05	B ₀	3.7	±0.1
D ₁	(1.5)	(±0.1)	K ₀	2.3	±0.1




3. Dimension of reel

(Unit in mm)



4. Leading part


(Unit in mm)




SOLDERING

Reflow soldering

Temperature profile



Recommended soldering pattern



(Unit in mm)

RECOMMENDATION FOR MANUAL SOLDERING

Soldering iron	: Less than 25 W
Temperature	: Lower than 300°C
Time	: Within 3 s

POST SOLDERING CLEANING

When cleaning after soldering is needed, the following condition must be adhered to.

Cleaning solvents	: AK225 or Alcohol
Temperature	: 50°C (max) for 30 s (max) or 30°C (max) for 3 minutes (max)
Ultrasonic	: 300 W max

6. Packing Form

(1) Number of Devices per Reel and Carton

Reel	2000 devices
Carton	10000 devices

(2) Packing : Silica gel and reel are packed into sealed aluminum pack.


7. Notation Method

(1) Example : TLRE1100 (T11)

P/N :

TYPE	TLRE1100		
ADD. C	(T11)	Q'TY	2000 pcs
NOTE	(rank symbol) Lot Number		

(2) Label location :



Aluminum pack : Attached to center of one side