

## Features

- 600W Peak Pulse Power Dissipation
- Voltage Range 6.8V - 400V
- Constructed with Glass Passivated Die
- Uni- and Bidirectional Versions Available
- Excellent Clamping Capability
- Fast Response Time
- **Lead Free Finish, RoHS Compliant (Note 1)**

## Mechanical Data

- Case: DO-15
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Leads: Plated Leads, Solderable per MIL-STD-202, Method 208 
- Marking: Unidirectional - Type Number and Cathode Band
- Marking: Bidirectional - Type Number Only
- Ordering Information: See Page 4
- Weight: 0.4 grams (approximate)

## Maximum Ratings @T<sub>A</sub> = 25°C unless otherwise specified

| Characteristic                                                                                                               | Symbol           | Value                                            | Unit |
|------------------------------------------------------------------------------------------------------------------------------|------------------|--------------------------------------------------|------|
| Peak Power Dissipation, t <sub>p</sub> = 1.0 ms<br>(Non repetitive current pulse, derated above T <sub>A</sub> = 25°C)       | P <sub>pk</sub>  | 600                                              | W    |
| Peak Forward Surge Current, 8.3ms Single Half Sine Wave, Superimposed on Rated Load Duty Cycle = 4 pulses per minute maximum | I <sub>FSM</sub> | 100                                              | A    |
| Forward Voltage @ I <sub>F</sub> = 35A<br>300µs Square Wave Pulse, Unidirectional Only                                       | V <sub>F</sub>   | 3.5<br>5.0                                       | V    |
|                                                                                                                              |                  | V <sub>BR</sub> ≤ 200V<br>V <sub>BR</sub> > 200V |      |

## Thermal Characteristics







| Characteristic                                                                                                       | Symbol                            | Value       | Unit |
|----------------------------------------------------------------------------------------------------------------------|-----------------------------------|-------------|------|
| Steady State Power Dissipation at T <sub>L</sub> = 75°C<br>Lead Lengths 9.5 mm (Mounted on Copper Land Area of 40mm) | P <sub>D</sub>                    | 5.0         | W    |
| Typical Thermal Resistance, Junction to Case                                                                         | R <sub>θJC</sub>                  | 20          | °C/W |
| Typical Thermal Resistance, Junction to Lead                                                                         | R <sub>θJL</sub>                  | 15          | °C/W |
| Typical Thermal Resistance, Junction to Ambient                                                                      | R <sub>θJA</sub>                  | 75          | °C/W |
| Operating and Storage Temperature Range                                                                              | T <sub>J</sub> , T <sub>STG</sub> | -55 to +175 | °C   |

Notes: 1. EU Directive 2002/95/EC (RoHS). All applicable RoHS exemptions applied, see EU Directive 2002/95/EC Annex Notes.

## Electrical Characteristics @T<sub>A</sub> = 25°C unless otherwise specified

| Type Number<br>(Note 2) | Type Number<br>(Note 2) | Reverse Standoff Voltage | Breakdown Voltage<br>V <sub>BR</sub> @ I <sub>T</sub> |         | Test Current        | Max Reverse Leakage<br>(Note 3)<br>@ V <sub>R</sub> | Max Clamping Voltage<br>@ I <sub>pp</sub> | Max Peak Pulse Current |
|-------------------------|-------------------------|--------------------------|-------------------------------------------------------|---------|---------------------|-----------------------------------------------------|-------------------------------------------|------------------------|
| (UNI)                   | (BI)                    | V <sub>RWM</sub> (V)     | Min (V)                                               | Max (V) | I <sub>T</sub> (mA) | I <sub>R</sub> (μA)                                 | V <sub>C</sub> (V)                        | I <sub>PP</sub> (A)    |
| P6KE6V8A                | P6KE6V8CA               | 5.80                     | 6.45                                                  | 7.14    | 10                  | 1000                                                | 10.5                                      | 57.0                   |
| P6KE7V5A                | P6KE7V5CA               | 6.40                     | 7.13                                                  | 7.88    | 10                  | 500                                                 | 11.3                                      | 53.0                   |
| P6KE8V2A                | P6KE8V2CA               | 7.02                     | 7.79                                                  | 8.61    | 10                  | 200                                                 | 12.1                                      | 50.0                   |
| P6KE9V1A                | P6KE9V1CA               | 7.78                     | 8.65                                                  | 9.55    | 1.0                 | 50                                                  | 13.4                                      | 45.0                   |
| P6KE10A                 | P6KE10CA                | 8.55                     | 9.50                                                  | 10.50   | 1.0                 | 10                                                  | 14.5                                      | 41.0                   |
| P6KE11A                 | P6KE11CA                | 9.40                     | 10.50                                                 | 11.60   | 1.0                 | 5.0                                                 | 15.6                                      | 38.0                   |
| P6KE12A                 | P6KE12CA                | 10.20                    | 11.40                                                 | 12.60   | 1.0                 | 5.0                                                 | 16.7                                      | 36.0                   |
| P6KE13A                 | P6KE13CA                | 11.10                    | 12.40                                                 | 13.70   | 1.0                 | 5.0                                                 | 18.2                                      | 33.0                   |
| P6KE15A                 | P6KE15CA                | 12.80                    | 14.30                                                 | 15.80   | 1.0                 | 5.0                                                 | 21.2                                      | 28.0                   |
| P6KE16A                 | P6KE16CA                | 13.60                    | 15.20                                                 | 16.80   | 1.0                 | 5.0                                                 | 22.5                                      | 27.0                   |
| P6KE18A                 | P6KE18CA                | 15.30                    | 17.10                                                 | 18.90   | 1.0                 | 5.0                                                 | 25.2                                      | 24.0                   |
| P6KE20A                 | P6KE20CA                | 17.10                    | 19.00                                                 | 21.00   | 1.0                 | 5.0                                                 | 27.7                                      | 22.0                   |
| P6KE22A                 | P6KE22CA                | 18.80                    | 20.90                                                 | 23.10   | 1.0                 | 5.0                                                 | 30.6                                      | 20.0                   |
| P6KE24A                 | P6KE24CA                | 20.50                    | 22.80                                                 | 25.20   | 1.0                 | 5.0                                                 | 33.2                                      | 18.0                   |
| P6KE27A                 | P6KE27CA                | 23.10                    | 25.70                                                 | 28.40   | 1.0                 | 5.0                                                 | 37.5                                      | 16.0                   |
| P6KE30A                 | P6KE30CA                | 25.60                    | 28.50                                                 | 31.50   | 1.0                 | 5.0                                                 | 41.4                                      | 14.40                  |
| P6KE33A                 | P6KE33CA                | 28.20                    | 31.40                                                 | 34.70   | 1.0                 | 5.0                                                 | 45.7                                      | 13.20                  |
| P6KE36A                 | P6KE36CA                | 30.80                    | 34.20                                                 | 37.80   | 1.0                 | 5.0                                                 | 49.9                                      | 12.00                  |
| P6KE39A                 | P6KE39CA                | 33.30                    | 37.10                                                 | 41.00   | 1.0                 | 5.0                                                 | 53.9                                      | 11.20                  |
| P6KE43A                 | P6KE43CA                | 36.80                    | 40.90                                                 | 45.20   | 1.0                 | 5.0                                                 | 59.3                                      | 10.10                  |
| P6KE47A                 | P6KE47CA                | 40.20                    | 44.70                                                 | 49.40   | 1.0                 | 5.0                                                 | 64.8                                      | 9.30                   |
| P6KE51A                 | P6KE51CA                | 43.60                    | 48.50                                                 | 53.60   | 1.0                 | 5.0                                                 | 70.1                                      | 8.60                   |
| P6KE56A                 | P6KE56CA                | 47.80                    | 53.20                                                 | 58.80   | 1.0                 | 5.0                                                 | 77.0                                      | 7.80                   |
| P6KE62A                 | P6KE62CA                | 53.00                    | 58.90                                                 | 65.10   | 1.0                 | 5.0                                                 | 85.0                                      | 7.10                   |
| P6KE68A                 | P6KE68CA                | 58.10                    | 64.60                                                 | 71.40   | 1.0                 | 5.0                                                 | 92.0                                      | 6.50                   |
| P6KE75A                 | P6KE75CA                | 64.10                    | 71.30                                                 | 78.80   | 1.0                 | 5.0                                                 | 103.0                                     | 5.80                   |
| P6KE82A                 | P6KE82CA                | 70.10                    | 77.90                                                 | 86.10   | 1.0                 | 5.0                                                 | 113.0                                     | 5.30                   |
| P6KE91A                 | P6KE91CA                | 77.80                    | 86.50                                                 | 95.50   | 1.0                 | 5.0                                                 | 125.0                                     | 4.80                   |
| P6KE100A                | P6KE100CA               | 85.50                    | 95.00                                                 | 105.00  | 1.0                 | 5.0                                                 | 137.0                                     | 4.40                   |
| P6KE110A                | P6KE110CA               | 94.00                    | 105.00                                                | 116.00  | 1.0                 | 5.0                                                 | 152.0                                     | 4.00                   |
| P6KE120A                | P6KE120CA               | 102.00                   | 114.00                                                | 126.00  | 1.0                 | 5.0                                                 | 165.0                                     | 3.60                   |
| P6KE130A                | P6KE130CA               | 111.00                   | 124.00                                                | 137.00  | 1.0                 | 5.0                                                 | 179.0                                     | 3.30                   |
| P6KE150A                | P6KE150CA               | 128.00                   | 143.00                                                | 158.00  | 1.0                 | 5.0                                                 | 207.0                                     | 2.90                   |
| P6KE160A                | P6KE160CA               | 136.00                   | 152.00                                                | 168.00  | 1.0                 | 5.0                                                 | 219.0                                     | 2.70                   |
| P6KE170A                | P6KE170CA               | 145.00                   | 162.00                                                | 179.00  | 1.0                 | 5.0                                                 | 234.0                                     | 2.60                   |
| P6KE180A                | P6KE180CA               | 154.00                   | 171.00                                                | 189.00  | 1.0                 | 5.0                                                 | 246.0                                     | 2.40                   |
| P6KE200A                | P6KE200CA               | 171.00                   | 190.00                                                | 210.00  | 1.0                 | 5.0                                                 | 274.0                                     | 2.20                   |
| P6KE220A                | P6KE220CA               | 185.00                   | 209.00                                                | 231.00  | 1.0                 | 5.0                                                 | 328.0                                     | 1.83                   |
| P6KE250A                | P6KE250CA               | 214.00                   | 237.00                                                | 263.00  | 1.0                 | 5.0                                                 | 344.0                                     | 1.75                   |
| P6KE300A                | P6KE300CA               | 256.00                   | 285.00                                                | 315.00  | 1.0                 | 5.0                                                 | 414.0                                     | 1.45                   |
| P6KE350A                | P6KE350CA               | 300.00                   | 332.00                                                | 368.00  | 1.0                 | 5.0                                                 | 482.0                                     | 1.25                   |
| P6KE400A                | P6KE400CA               | 342.00                   | 380.00                                                | 420.00  | 1.0                 | 5.0                                                 | 548.0                                     | 1.10                   |

Notes: 2. Suffix 'C' denotes bidirectional device.  
3. For bidirectional devices having V<sub>R</sub> of 10 volts and under, the I<sub>R</sub> limit is doubled.




## Ordering Information (Note 4)

| Part Number      | Case  | Packaging               |
|------------------|-------|-------------------------|
| (Type Number)-B* | DO-15 | 500/Bulk                |
| (Type Number)-T* | DO-15 | 4K/Tape & Reel, 13-inch |

\* Add "-B" or "-T" to the appropriate type number in Table 1 for Bulk or Tape & Reel, respectively. Example: 6.40V VRWM = P6KE7V5A-B for Bulk, P6KE7V5A-T for Tape & Reel.

Notes: 4. For packaging details, go to our website at <http://www.diodes.com/datasheets/ap02008.pdf>.

## Package Outline Dimensions



| DO-15                |       |       |
|----------------------|-------|-------|
| Dim                  | Min   | Max   |
| A                    | 25.40 | —     |
| B                    | 5.50  | 7.62  |
| C                    | 0.686 | 0.889 |
| D                    | 2.60  | 3.60  |
| All Dimensions in mm |       |       |

#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

#### **LIFE SUPPORT**

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2009, Diodes Incorporated

[www.diodes.com](http://www.diodes.com)