

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

75784-0152

Status:

Active

Overview:

iPass™ Connector System

Description:

0.80mm Pitch, iPass™ I/O Surface Mount Receptacle, Vertical, Internal Assembly with Shell, 36 Circuit, 0.76µm Gold (Au), Through Hole Option, Tail Length 3.18mm, Universal Key



image - Reference only

Series

- Documents:
- 3D Model

Drawing (PDF)

Product Specification PS-75783-001 (PDF)

Application Specification AS-75783-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

I/O Connectors

Series

75784

Application

Wire-to-Board

Comments

Positive or passive latching cable available

Component Type

Receptacle

Electrical Model

Yes

Overview

iPass™ Connector System

Product Name

iPass™, PCI Express*, SAS, Serial ATA

Type

N/A

UPC

822350356008

Physical

Circuits (Loaded)

36

Circuits (maximum)

36

Color - Resin

Black

Durability (mating cycles max)

250

Flammability

94V-0

Gender

Female

Keying to Mating Part

Yes

Lock to Mating Part

None

Material - Metal

Copper-Nickel-Zinc, High Performance Alloy (HPA)

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

3.993/g

Number of Rows

2

Orientation

Vertical

PC Tail Length

3.18mm

PCB Locator

Yes

PCB Retention

Yes

PCB Thickness - Recommended

2.79mm

Packaging Type

Embossed Tape on Reel

Panel Mount

No

Pitch - Mating Interface

0.80mm

Pitch - Termination Interface

0.80mm

Plating min - Mating

0.762µm

Plating min - Termination

2.540µm

Polarized to Mating Part

Yes

Ports

1

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
75784Series

Use With
iPass™ Cable Assemblies, [79575](#) , [79576](#) , [74562](#) , [74563](#) , [79536](#) , [74573](#) , [74569](#) , [74586](#)

Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +80°C
Termination Interface: Style	Surface Mount, Through Hole
Waterproof / Dustproof	No
Wire Insulation Diameter	N/A
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	0.5A
Grounding to Panel	None
Voltage - Maximum	30V AC (RMS)/DC

Solder Process Data

Duration at Max. Process Temperature (seconds)	20
Lead-free Process Capability	Reflow Capable (SMT only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Application Specification	AS-75783-001
Electrical Model Document	EE-75577-001
Product Specification	PS-75783-001
Sales Drawing	SD-75784-001

This document was generated on 12/18/2014
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75784-0152](#)