








1. CONTACTS INCLUDED IN ASSEMBLY.
2. MATL: STEEL, PER ASTM-A-109.
3. FINISH: CADMIUM PER QQ-P-416.
4. CONTACT
BODY MATL: BERYLLIUM COPPER PER ASTM-B-197.
BODY FINISH: PLATED GOLD, .000050 MIN THK PER
MIL-G-45204 OVER NICKEL, .000050 MIN
THK PER QQ-N-290.
HOOD MATL: STAINLESS STEEL PER ASTM-A-167.
HOOD FINISH: PASSIVATED PER ASTM-A-380
5. FINISH: PLATED ZINC .00020 MIN THK PER ASTM-B-633.
YELLOW CHROMATE FINISH.
6. MATL: BRASS PER ASTM-B-36.
7. FINISH: PLATED GOLD, .000050 MIN THK PER MIL-G-45204
OVER COPPER, .000100 MIN THK PER MIL-C-14550.
8. CONTACT
BODY MATL: BERYLLIUM COPPER PER ASTM-B-197.
BODY AND HOOD FINISH: PLATED GOLD, .000050 MIN THK
PER MIL-G-45204 OVER COPPER, .000100 MIN THK
PER MIL-C-14550.
HOOD MATL: BRASS PER ASTM-B-36



	 	 		4U884 SOCN R10002677-0105	212563-6
	 	 		PT2-111-11	212563-5
OBSOLETE	 	 		-	212563-4
	 	 		(1J02-105)	212563-3
	 	 		-	212563-2
	 	 		-	212563-1
	EYELET	SHELLS	CONTACT	CUSTOMER P/N	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 27-May-15 MANJUNATH G M		 TE Connectivity	
		CHK 27-May-15 CHARLES THOMAS			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CONNECTOR SAVER, AMPLIMITE 50 POSITION, SIZE 5, SERIES 109 —	
		APVD 27-May-15 CHARLES THOMAS			
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 [0.13] 4 PLC ± — ANGLES ± ± —		PRODUCT SPEC —			
MATERIAL —		APPLICATION SPEC —			
FINISH —		WEIGHT 0.000000		SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO C-212563	RESTRICTED TO —
				SCALE 4:1	SHEET 1 of 1
				REV V	