

Product Name
Series
Type
Part Number

3-terminal Filters Array
MEA Series
1608PE Type
MEA1608PE540TA0G

Product Lifecycle Stage
PROD



Specification			
Mounting Method Flag		Yes	
Processing		multilayer type	
Shape		Chip-Array	
Circuit Type		Pi Type	
Number of Circuits		Nom	4
Size Code		1608	
Body Length(L)		Nom	1.6 mm
Body Breadth(W)		Nom	0.8 mm
Body Height(T)		Nom	0.5 mm
Cut-Off Frequency		Nom	200 MHz
Rated Capacitance		Nom	54 pF
Rated Voltage		Max	6.3 V
Rated Current		Max	0.1 A
Polarity Marking		No	
Soldering Method		Reflow,Iron Soldering	
Operating Temperature Range	Min	-40 Cel	
	Max	85 Cel	
Storage Temperature Range	Min	-40 Cel	
	Max	85 Cel	
Weight		Nom	0.003g

Summary/Applications/Features			
Summary	Pi-type 4line array EMC-terminal filters with magnetic shield and sharp attenuation characteristics.		
Applications	For LCD and camera signal lines in mobile phone.		
Features	4-line LC filter are built in a one chip for high density circuit design.		
	0.5mm low profile.		
	For improvement of the mobile phone frame(l error rate.		
	This product is suitable for the LCD signal line in mobile phone.		
Packaging			
Packing		Blister (Plastic)Taping [180mm Reel]	
Minumum Package Qty		Nom	4000 Pcs
Minimum Order Qty		Nom	4000 Pcs

- Details
- Catalog Info.

[Caution]

Specifications which provide more details for the proper and safe use of the described product are available upon request.

[Notice of Revision and Improve]

All specifications are subject to change without notice.