




Left Side

Connector(s): LC-Duplex Secure
Mode: MM
Housing Color: Red
Geom. Spec: N/A

Fiber Path

A - _____ - B
B - _____ - A

Right Side

Connector(s): SC-Duplex
Mode: MM
Housing Color: Beige
Geom. Spec: N/A

Notes:

- 1 IL tested at 1300nm.
- 2 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 3 Label 2 will not be present on any cable assembly less than 5 meters long.
- 4 Includes dust caps (not shown on print).

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS, INC. AND ITS SUBSIDIARIES. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

	B	Rev Per EC#	ECR-07-007111	3/27/2007	-	JD			
P	LTR	REVISION RECORD		DATE	DN	APVD			

DIMENSIONS:
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 P.L.C. ± .
1 P.L.C. ± .
2 P.L.C. ± .
3 P.L.C. ± .
4 P.L.C. ± .

Restricted To:

DN Cable Assy Configurator	MATERIAL	HEAT TREAT
OK Jeremy Duncan		
APVD Jeremy Duncan	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608	
NAME	FO C/A - 2 fiber, 62.5/125, OFNP (Plenum) jacket, LC-Duplex Secure to SC-Duplex	
SCALE NTS	SIZE A2	DRAWING NO C- 1828872
	SHEET 1 of 3	REV B

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

THIS DRAWING IS A CONTROLLED DOCUMENT.
REV NO

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Part #	L (meters)	L (feet)	LC-Duplex Secure, Red		SC-Duplex, Beige	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-1828872-1	0.950 - 1.050	3.11 - 3.44	0.5	-	0.5	-
0-1828872-2	1.950 - 2.050	6.39 - 6.72	0.5	-	0.5	-
0-1828872-3	2.950 - 3.050	9.67 - 10.00	0.5	-	0.5	-
0-1828872-4	3.920 - 4.080	12.86 - 13.38	0.51	-	0.51	-
0-1828872-5	4.920 - 5.080	16.14 - 16.66	0.51	-	0.51	-
0-1828872-6	5.920 - 6.080	19.42 - 19.94	0.51	-	0.51	-
0-1828872-7	6.920 - 7.080	22.70 - 23.22	0.51	-	0.51	-
0-1828872-8	7.920 - 8.080	25.98 - 26.50	0.51	-	0.51	-
0-1828872-9	8.850 - 9.150	29.03 - 30.01	0.51	-	0.51	-
1-1828872-0	9.850 - 10.150	32.31 - 33.30	0.52	-	0.52	-
1-1828872-1	10.850 - 11.150	35.59 - 36.58	0.52	-	0.52	-
1-1828872-2	11.850 - 12.150	38.87 - 39.86	0.52	-	0.52	-
1-1828872-3	12.850 - 13.150	42.15 - 43.14	0.52	-	0.52	-
1-1828872-4	13.850 - 14.150	45.43 - 46.42	0.52	-	0.52	-
1-1828872-5	14.850 - 15.150	48.72 - 49.70	0.52	-	0.52	-
1-1828872-6	15.840 - 16.160	51.96 - 53.01	0.52	-	0.52	-
1-1828872-7	16.830 - 17.170	55.21 - 56.33	0.53	-	0.53	-
1-1828872-8	17.820 - 18.180	58.46 - 59.64	0.53	-	0.53	-
1-1828872-9	18.810 - 19.190	61.71 - 62.95	0.53	-	0.53	-
2-1828872-0	19.800 - 20.200	64.96 - 66.27	0.53	-	0.53	-
2-1828872-1	20.790 - 21.210	68.20 - 69.58	0.53	-	0.53	-
2-1828872-2	21.780 - 22.220	71.45 - 72.90	0.53	-	0.53	-
2-1828872-3	22.770 - 23.230	74.70 - 76.21	0.53	-	0.53	-
2-1828872-4	23.760 - 24.240	77.95 - 79.52	0.54	-	0.54	-
2-1828872-5	24.750 - 25.250	81.20 - 82.84	0.54	-	0.54	-
2-1828872-6	25.740 - 26.260	84.44 - 86.15	0.54	-	0.54	-
2-1828872-7	26.730 - 27.270	87.69 - 89.46	0.54	-	0.54	-
2-1828872-8	27.720 - 28.280	90.94 - 92.78	0.54	-	0.54	-
2-1828872-9	28.710 - 29.290	94.19 - 96.09	0.54	-	0.54	-
3-1828872-0	29.700 - 30.300	97.44 - 99.40	0.55	-	0.55	-
3-1828872-1	30.690 - 31.310	100.68 - 102.72	0.55	-	0.55	-
3-1828872-2	31.680 - 32.320	103.93 - 106.03	0.55	-	0.55	-
3-1828872-3	32.670 - 33.330	107.18 - 109.35	0.55	-	0.55	-
3-1828872-4	33.660 - 34.340	110.43 - 112.66	0.55	-	0.55	-
3-1828872-5	34.650 - 35.350	113.68 - 115.97	0.55	-	0.55	-
3-1828872-6	35.640 - 36.360	116.92 - 119.29	0.55	-	0.55	-
3-1828872-7	36.630 - 37.370	120.17 - 122.60	0.56	-	0.56	-
3-1828872-8	37.620 - 38.380	123.42 - 125.91	0.56	-	0.56	-
3-1828872-9	38.610 - 39.390	126.67 - 129.23	0.56	-	0.56	-
4-1828872-0	39.600 - 40.400	129.92 - 132.54	0.56	-	0.56	-
5-1828872-0	49.500 - 50.500	162.40 - 165.68	0.58	-	0.58	-

Qty	U of M	Description	Item No.
2	piece	Trace Label	10
2	piece	CONN SUBASSY, MM, SC 1.6MM	9
4	piece	Eyelet/Shrink tube assembly - White	8
2	piece	SC Duplex Clip	7
2	piece	2.5mm ferrule cover	6
2	piece	SC Simplex Housing, Beige	5
AR	meter	2 fiber, 62.5/125, 1.8 mm, Twinzip, Orange, OFNP (Plenum)	4
2	piece	LC Connector Assy, 1.6mm-2.0mm, MM	3
1	piece	LC Duplex clip, black	2
4	piece	LC, SC, FC Straight Boot, Beige	1

	B	Rev Per EC#	ECR-07-007111	3/27/2007	-	JD			
P	LTR	REVISION RECORD		DATE	DIN	APVD			

DIMENSIONS: meters	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 P.L.C. ± - 1 P.L.C. ± - 2 P.L.C. ± - 3 P.L.C. ± - 4 P.L.C. ± -

Restricted To:

DIN		Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK		Jeremy Duncan				
APVD		Jeremy Duncan				
NAME						
SCALE	NTS	SIZE	A2	DRAWING NO	C- 1828872	
SHEET		2 of 3		REV		B

8 7 6 5 4 3 2 1

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

8

7

6

5

4

3

2

1

Label 1

Per specification 107-1645-1



Trace # - Bar Code
Trace # - Human Readable
Part Number
Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



Trace # - Bar Code
Trace # - Human Readable
Part Number
Country of Origin

This label is used on all lengths on this drawing.

DIMENSIONS:	
meters	

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 P.L.C.	± .
1 P.L.C.	± .
2 P.L.C.	± .
3 P.L.C.	± .
4 P.L.C.	± .

Restricted To:

DIN Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK	Jeremy Duncan	-	-	
APVD	Jeremy Duncan	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
NAME FO C/A - 2 fiber, 62.5/125, OFNP (Plenum) jacket, LC-Duplex Secure to SC-Duplex				
SCALE	SIZE	DRAWING NO	SHEET	REV
NTS	A2	C- 1828872	3 of 3	B