

Molded Parts Customer Drawing

IF THIS DOCUMENT IS PRINTED IT BECOMES UNCONTROLLED.
CHECK FOR THE LATEST REVISION.

Part Number : 234A011thru071

ECO No.: ECO-11-005139

NOTES

1. All dimensions are in inches ; lbs
[millimeters] ; [gms]
2. Dimensions appearing in table are as follows:
a - As Supplied
b - After Unrestricted Recovery
3. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.
4. Molding ports are optional. When -00 modification number is specified molding ports will be located as shown.
5. Weight shown in table of dimensions is based on polyolefin part.
- **6. /180 coating is only available on 234A011, 234A021 and 234A032. Contact factory for additional sizes.





TABLE OF DIMENSIONS

PART NUMBER	H		J		K		P ±10% b	R ±10% b	S ±10% b	W ±20% b	X ±20% b	Weight Nom b	This Boot Fits Cannon-Cinch
	±5% a	±5% b	±5% a	±5% b	Min a	Max b							
234A011	.80 [20.3]	.80 [20.3]	.42 [10.7]	.42 [10.7]	.31 [7.9]	.16 [4.1]	1.02 [25.9]	.85 [21.6]	.60 [15.2]	.04 [1.02]	.12 [3.05]	.0048 [2.18]	DE-9
234A021	1.11 [28.2]	1.11 [28.2]	.42 [10.7]	.42 [10.7]	.40 [10.2]	.21 [5.3]	1.21 [30.7]	.97 [24.6]	.73 [18.5]	.04 [1.02]	.12 [3.05]	.0059 [2.68]	DA-15
234A032	1.66 [42.2]	1.66 [42.2]	.42 [10.7]	.42 [10.7]	.55 [14.0]	.29 [7.4]	1.69 [42.9]	1.10 [27.9]	.87 [22.1]	.04 [1.02]	.12 [3.05]	.0102 [4.63]	DB-25
234A042	2.31 [58.7]	2.31 [58.7]	.42 [10.7]	.42 [10.7]	.68 [17.3]	.34 [8.6]	2.10 [53.3]	1.20 [30.5]	1.00 [25.4]	.04 [1.02]	.12 [3.05]	.0132 [5.99]	DC-37
234A052	2.28 [57.9]	2.28 [57.9]	.54 [13.7]	.54 [13.7]	.75 [19.1]	.42 [10.7]	2.20 [55.9]	1.27 [32.3]	1.00 [25.4]	.04 [1.02]	.12 [3.05]	.0152 [6.90]	DD-50
234A061	.80 [20.3]	.80 [20.3]	.42 [10.7]	.42 [10.7]	.31 [7.9]	.15 [3.8]	1.02 [25.9]	.73 [18.5]	.48 [12.2]	.04 [1.02]	.12 [3.05]	.0045 [2.04]	DE-9
234A071	1.11 [28.2]	1.11 [28.2]	.42 [10.7]	.42 [10.7]	.40 [10.2]	.20 [5.1]	1.21 [30.7]	.78 [19.8]	.53 [13.5]	.04 [1.02]	.12 [3.05]	.0056 [2.54]	DA-15

TE Raychem

TE Connectivity
Raychem Molded Parts
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Molded Parts Customer Drawing

Part Number : 234A011thru071
ECO No. : ECO-11-005139

COMPATABILITY CHART					
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.	COATING DESCRIPTION
-3	Polyolefin, Semi-rigid	RT-301	/42; /86,**/180, /184	S-1017; S-1048	Adhesive
-4	Polyolefin, Flexible	RT-1304	/42; /86,**/180, /184	S-1017; S-1048	Adhesive
-8	Polyolefin, Space	RT-1308	N/A		
-12	*VITON, Flexible	RT-1312	N/A		
-25	Elastomer, Fluid Resistant	RT-1325	/86; /225	S-1048; S-1206	Adhesive
-100	Polyolefin, Semi-flexible ZEROHAL™	RT-1323	/86 : **/180; /184	S-1048; S-1030	Adhesive

*VITON is a Registered Trademark of Dupont

ORDERING INFORMATION

234AOXX -X -XX /XXX -0

Base part number

Material dash number
(See Compatibility Chart)

Modification number

Adhesive slash number
(If necessary, see Compatibility Chart)

Color designator

THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR
NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION

TE
Raychem
TE Connectivity

Raychem Molded Parts
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

Revision : R1

Date : 20APR11

Page 2 of 2

© 2007,2011 Tyco Electronics Corporation, a TE Connectivity Ltd.
Company. All Rights Reserved.

IF THIS DOCUMENT IS PRINTED IT BECOMES UNCONTROLLED.
CHECK FOR THE LATEST REVISION.