





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
		A		REVISED PER ECO-12-018102	11OCT2012	MGM
		B		ECO-13-004759	01APR2013	KG



○ = SIGNAL
⊗ = GROUND
RECOMMENDED DIFFERENTIAL PAIR PC BOARD LAYOUT
COMPONENT SIDE SHOWN
SCALE 10:1



- 1 MATERIAL:
CONTACT AND SHIELD: COPPER ALLOY
HOUSING AND CHICKLET: LCP, COLOR: BLACK
- 2 FINISH:
CONTACT: MATING AREA: 1.27µm MIN GOLD OVER
1.27µm MIN NICKEL
SHIELD: 1.27µm MIN NICKEL
- 3 FINISH:
COMPLIANT PIN AREA: 0.5µm MIN BRIGHT TIN LEAD OVER
1.27µm MIN NICKEL
- 4 FINISH:
COMPLIANT PIN AREA: 0.5µm MIN MATTE TIN OVER
1.27µm MIN NICKEL
- 5 DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.
- 6 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 7 REFERENCE APPLICATION SPEC 114-13267 FOR RECOMMENDED
PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- 8 RECOMMENDED DIFFERENTIAL PAIR CONFIGURATION SHOWN.
THE CONNECTOR UTILIZES AN OPEN PIN FIELD AND
CAN BE LAID OUT IN A SINGLE-ENDED CONFIGURATION.

2	4	2012087-2
2	3	2012087-1
FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009		DWN D. BELACK CHK A. TSANG APVD W. McALONIS	24NOV2010	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME Fortis Zd. 2-PAIR, 10-COLUMN, R/A CENTER MODULE ASSEMBLY	
0 PLG 1 PLG 2 PLG 3 PLG 4 PLG		± ±0.13 ±0.05 ± ±		PRODUCT SPEC 108-2409	
ANGLES		±2°		APPLICATION SPEC 114-13267	
FINISH		-		SIZE ~6.52 g	
MATERIAL		-		CAGE CODE A100779	
DRAWING NO.		2102087		RESTRICTED TO -	
CUSTOMER DRAWING		SCALE 6:1		SHEET 1 OF 1	
				REV B	