



DIMENSIONS:

A	2.500" ±0.063
B	3.200" ±0.125
C	3.060" ±0.063
D	2.000" ±0.063
E	2.188" ±0.063
G	0.203" x 0.375" ±0.015



NOTE: ALL LEADS 6" OUT MIN. STRIPPED 0.5"



ELECTRICAL DATA:

TESTS	CONDITIONS	ACCEPTANCE CRITERIA	
I _{ex}	@ 125V, 60Hz, WHT - BLK	192mA	Max.
Sec. N.L.V	@ 125V, 60Hz, WHT - BLK		
	RED - RED =	557.8V	±2%
	RED - RED/YEL = RED/YEL - RED =	278.9V	±2%
	GRN - GRN =	7.009V	±2%
DCR	@ 20°C, WHT - BLK =	5.372 Ω	±20%
	@ 20°C, RED - RED =	177.8 Ω	±20%
	@ 20°C, GRN - GRN =	0.075 Ω	±20%
HIPOT	PRIMARY - SECONDARY	2000V, 60Hz, 1 SEC	

REV.#	REVISION	DATE	HAMMOND ELECTRONIC DIVISION			
0	RELEASED.	C.I. 11/08/12	52 RANKIN PLACE, WATERLOO, ONTARIO, N2J 3Z5			
			PH # (519) 886-6181		FAX # (519) 886-9540	
			DWG. BY: C. ILIE	CHK'D BY:	TITLE: POWER TRANSFORMER	DWG. NO. 270DAX
			DATE: 11/08/12	APP'D. BY:		
				DIMENSIONS: IN(X) MM()		