



EJECT-A-DIP™ Lock/Eject DIP Socket w/Collet Contacts & Solder Pin Tails

FEATURES


- Rugged, Solderable Socket with a Unique Ejector/Latch for Fast In-field Board Maintenance
- Latch Locks-in Connector or Device for High-vibration Environments
- Ejector/Latch removes DIP Packages without Damage

GENERAL SPECIFICATIONS

- **LATCH & BODY:** Black UL-94V-0 Glass-filled 4/6 Nylon
- **PIN BODY:** Brass 360 1/2-hard per UNS C36000 ASTM B16/B16M-05
- **PIN BODY PLATING:** 10μ [0.25μ] min. Au per MIL-G-45204 –OR– 200μ [5.08μ] min. 93/7 Sn/Pb per ASTM B545 –OR– 200μ [5.08μ] min. Sn per ASTM B545 Type 1 over 100μ [2.54μ] min. Ni per SAE AMS-QQ-N-290B
- **6-FINGER COLLECT CONTACTS:** BeCu per UNS C17200 ASTM B194-08
- **CONTACT PLATING:** 200μ [5.08μ] min. 93/7 Sn/Pb per ASTM B545 –OR– 200μ [5.08μ] min. Sn per ASTM B545 Type 1 –OR– 10μ [0.25μ] min. Au per MIL-G-45204 over 50μ [1.27μ] min. Ni per SAE AMS-QQ-N-290B. Heavy 30μ [0.76μ] Au plating on contacts also available.
- **CONTACT CURRENT RATING:** 3 amps
- **INSULATION RESISTANCE:** 10,000 MΩ at 500VDC
- **WITHSTANDING VOLTAGE:** 1000Vrms
- **OPERATING TEMPERATURE:** -67°F to 221°F [-55°C to 105°C] for Sn plating; -67°F to 257°F [-55°C to 125°C] for Au plating
- **INSERTION FORCE:** 67g/pin, based on 0.018 [0.46] dia. test lead
- **WITHDRAWAL FORCE:** 30g/pin, based on 0.018 [0.46] dia. test lead
- **NORMAL FORCE:** 45g/pin, based on 0.018 [0.46] dia. test lead

MOUNTING CONSIDERATIONS

- **SUGGESTED PCB HOLE SIZE:** 0.030 ±0.002 [0.76 ±0.05] dia.



ORDERING INFORMATION

XX-CXXX-X XXX XX

Optional Plating

H = Heavy Au Collet
T = Sn Collet & Shell
TL = Sn/Pb Collet & Shell

Plating

0 = Au Collet, Sn Shell
OTL = Au Collet, Sn/Pb Shell
1 = Au Collet & Shell

Termination

1 = Solder Pin Tail

Dim. "H"

(See Table)

No. of Pins

(See Table)

ALL DIMENSIONS: INCHES [MILLIMETERS]

ALL TOLERANCES: ±0.005 [0.13] UNLESS OTHERWISE SPECIFIED

FOR COLLECT SOCKETS w/SURFACE MOUNT PINS, SEE [DATA SHEET 12023](#)

FOR COLLET SOCKET w/WIRE WRAP PINS, SEE [DATA SHEET 12025](#)

CONSULT FACTORY FOR OTHER SIZES AND CONFIGURATIONS

CUSTOMIZATION: ARIES SPECIALIZES IN CUSTOM DESIGN AND PRODUCTION. SPECIAL MATERIALS, PLATINGS, SIZES, AND CONFIGURATIONS CAN BE FURNISHED, DEPENDING ON QUANTITY.

ARIES RESERVES THE RIGHT TO CHANGE PRODUCT GENERAL SPECIFICATIONS WITHOUT NOTICE

PRINTOUTS OF THIS DOCUMENT MAY BE OUT-OF-DATE AND SHOULD BE CONSIDERED UNCONTROLLED



ARIES
ELECTRONICS, INC.

2609 Bartram Road • Bristol, PA 19007-6810 USA

TEL 215-781-9956 • FAX 215-781-9845


WWW.ARIESELEC.COM • INFO@ARIESELEC.COM



12024
Rev. 7.2
1 of 2



EJECT-A-DIP™ Lock/Eject DIP Socket w/Collet Contacts & Solder Pin Tails



No. of pins	Catalog No.	Dim. "A"	Dim. "B"	Centers "C"	Dim. "D"	Dim. "E"	Dim. "F"	Dim "G"	Dim "H"
14	14-C280-XX	0.950 [24.10]	0.600 [15.24]	0.300 [7.62]	0.400 [10.16]	0.770 [19.56]	1.300 [33.02]	0.490 [12.45]	0.280 [7.11]
14	14-C195-XX	0.950 [24.10]	0.600 [15.24]	0.300 [7.62]	0.400 [10.16]	0.770 [19.56]	1.300 [33.02]	0.450 [11.43]	0.195 [4.95]
16	16-C280-XX	1.050 [26.70]	0.700 [17.78]	0.300 [7.62]	0.400 [10.16]	0.870 [22.10]	1.540 [39.12]	0.490 [12.45]	0.280 [7.11]
16	16-C195-XX	1.050 [26.70]	0.700 [17.78]	0.300 [7.62]	0.400 [10.16]	0.870 [22.10]	1.390 [35.31]	0.450 [11.43]	0.195 [4.95]
24	24-C300-XX	1.490 [37.85]	1.100 [27.94]	0.600 [15.24]	0.700 [17.78]	1.300 [33.02]	1.970 [50.04]	0.570 [14.48]	0.300 [7.62]
24	24-C212-XX	1.490 [37.85]	1.100 [27.94]	0.600 [15.24]	0.700 [17.78]	1.300 [33.02]	1.850 [47.00]	0.490 [12.45]	0.212 [5.39]
24	24-C182-XX	1.490 [37.85]	1.100 [27.94]	0.600 [15.24]	0.700 [17.78]	1.300 [33.02]	1.800 [45.72]	0.460 [11.68]	0.182 [4.62]
28	28-C300-XX	1.690 [42.90]	1.300 [33.02]	0.600 [15.24]	0.700 [17.78]	1.500 [38.10]	2.170 [55.12]	0.570 [14.48]	0.300 [7.62]
28	28-C212-XX	1.690 [42.90]	1.300 [33.02]	0.600 [15.24]	0.700 [17.78]	1.500 [38.10]	2.050 [52.07]	0.490 [12.45]	0.212 [5.39]
28	28-C182-XX	1.690 [42.90]	1.300 [33.02]	0.600 [15.24]	0.700 [17.78]	1.500 [38.10]	2.000 [50.80]	0.460 [11.68]	0.182 [4.62]
32	32-C300-XX	1.890 [48.00]	1.500 [38.10]	0.600 [15.24]	0.700 [17.78]	1.700 [43.18]	2.540 [64.52]	0.570 [14.48]	0.300 [7.62]
32	32-C212-XX	1.890 [48.00]	1.500 [38.10]	0.600 [15.24]	0.700 [17.78]	1.700 [43.18]	2.070 [52.58]	0.490 [12.45]	0.212 [5.39]
32	32-C182-XX	1.890 [48.00]	1.500 [38.10]	0.600 [15.24]	0.700 [17.78]	1.700 [43.18]	2.200 [55.88]	0.460 [11.68]	0.182 [4.62]
40	40-C300-XX	2.290 [58.20]	1.900 [48.26]	0.600 [15.24]	0.700 [17.78]	2.100 [53.34]	2.780 [70.61]	0.570 [14.48]	0.300 [7.62]
40	40-C212-XX	2.290 [58.20]	1.900 [48.26]	0.600 [15.24]	0.700 [17.78]	2.100 [53.34]	2.650 [67.31]	0.490 [12.45]	0.212 [5.39]
40	40-C182-XX	2.290 [58.20]	1.900 [48.26]	0.600 [15.24]	0.700 [17.78]	2.100 [53.34]	2.600 [66.04]	0.460 [11.68]	0.182 [4.62]

ALL DIMENSIONS: INCHES [MILLIMETERS]

ALL TOLERANCES: ± 0.005 [0.13] UNLESS OTHERWISE SPECIFIED

FOR COLLECT SOCKETS w/SURFACE MOUNT PINS, SEE DATA SHEET 12023

FOR COLLET SOCKET w/WIRE WRAP PINS, SEE DATA SHEET 12025

CONSULT FACTORY FOR OTHER SIZES AND CONFIGURATIONS

CUSTOMIZATION: ARIES SPECIALIZES IN CUSTOM DESIGN AND PRODUCTION. SPECIAL MATERIALS, PLATINGS, SIZES, AND CONFIGURATIONS CAN BE FURNISHED, DEPENDING ON QUANTITY.

ARIES RESERVES THE RIGHT TO CHANGE PRODUCT GENERAL SPECIFICATIONS WITHOUT NOTICE

PRINTOUTS OF THIS DOCUMENT MAY BE OUT-OF-DATE AND SHOULD BE CONSIDERED UNCONTROLLED



ARIES
ELECTRONICS, INC.

2609 Bartram Road • Bristol, PA 19007-6810 USA

TEL 215-781-9956 • FAX 215-781-9845

WWW.ARIESELEC.COM • INFO@ARIESELEC.COM



12024
Rev. 7.2
2 of 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Aries Electronics:

[40-C182-11](#) [40-C182-10](#) [32-C212-30](#) [32-C182-10](#) [16-C280-10](#) [24-C182-10](#) [14-C280-10](#) [14-C280-11](#) [24-C300-10](#)
[28-C182-10](#) [28-C182-11](#) [14-C280-10T](#) [28-C212-31](#) [28-C212-30](#) [28-C212-11](#) [28-C212-10](#) [28-C212-21](#) [28-C212-](#)
[20](#) [28-C212-00](#) [24-C212-10](#) [24-C212-11](#) [24-C212-30](#) [24-C212-31](#) [24-C212-20](#) [24-C212-21](#) [24-C212-00](#) [28-C300-](#)
[30](#) [28-C300-31](#) [28-C300-10](#) [28-C300-11](#) [28-C300-20](#) [28-C300-21](#) [28-C300-00](#) [24-C300-11](#) [24-C300-31](#) [24-C300-](#)
[30](#) [24-C300-21](#) [24-C300-20](#) [24-C300-00](#) [28-C182-20](#) [28-C182-21](#) [28-C182-00](#) [28-C182-30](#) [28-C182-31](#) [24-C182-](#)
[21](#) [16-C280-00](#) [24-C182-20](#) [24-C182-00](#) [16-C280-21](#) [16-C280-20](#) [24-C182-31](#) [16-C280-11](#) [24-C182-30](#) [16-C280-](#)
[31](#) [16-C280-30](#) [24-C182-11](#) [14-C280-30](#) [14-C280-31](#) [14-C280-00](#) [14-C280-20](#) [14-C280-21](#) [16-C195-10H](#) [40-](#)
[C182-11H](#) [32-C212-21](#) [32-C212-20](#) [32-C212-00](#) [32-C212-31](#) [32-C212-11](#) [32-C212-10](#) [40-C300-30](#) [40-C300-31](#)
[40-C300-10](#) [40-C300-11](#) [40-C300-00](#) [40-C300-20](#) [40-C300-21](#) [14-C195-10T](#) [40-C212-31](#) [40-C212-30](#) [40-C212-11](#)
[40-C212-10](#) [40-C212-00](#) [40-C212-21](#) [40-C212-20](#) [32-C182-31](#) [32-C182-30](#) [32-C182-11](#) [32-C182-00](#) [32-C182-21](#)
[32-C182-20](#) [28-C182-11H](#) [40-C182-00](#) [40-C182-21](#) [40-C182-20](#) [40-C182-31](#) [40-C182-30](#) [24-C182-10H](#) [24-C182-](#)
[11H](#) [28-C212-10T](#) [14-C195-11](#)