

S14K275 275Vrms 350Vdc Scheiben VDR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Overvoltage protection with individual components
with varistors in terminal design

The metal-oxide varistors can be used in terminal design.
They are approved for a maximum sine-wave-form power-
frequency operating voltage, which is printed on the
component. Any voltages greater than the permitted
maximum are discharged safely within 25 ns. Varistors
are used for medium to high power.

General ordering data

Order No.	4011070000
Type	S14K275 275Vrms 350Vdc Scheiben VDR
Version	Electronics, Miscellaneous
GTIN (EAN)	4008190205751
Qty.	1 pc(s).

S14K275 275Vrms 350Vdc Scheiben VDR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	2.85 g
------------	--------

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

General data

Protection degree	IP 20
-------------------	-------

technical data

Rated voltage (AC)	230 V	Max. continuous voltage, Uc (AC)	275 V
--------------------	-------	----------------------------------	-------

Classifications

ETIM 2.0	EC001473	ETIM 3.0	EC001473
UNSPSC	30-21-19-21	eClass 4.1	27-13-08-01
eClass 5.1	27-13-08-01	eClass 6.2	27-13-08-01
eClass 7.1	27-13-08-90		

Approvals

Approvals	
ROHS	Conform